

OMEGAETTE™ Mini Current Clamp Meter

HHM221
\$60



- ✓ Pocket Size
- ✓ DATA HOLD Function
- ✓ Autoranging

Specifications

Numerical Display: 3½ digital liquid crystal (LCD), maximum reading 1999

Battery Life: 300 hours approximately

Low Battery Indication: The low battery indicator light is displayed as needed

Sampling: 2 times/sec

Power Source: Two 1.5 V, “AAA” batteries (included)

Operation Temperature and Humidity:
0 to 40°C (32 to 104°F) below 80% RH

Storage Temperature and Humidity:
-10 to 60°C (14 to 140°F) below 70% RH

Rating: IEC 1010; 300 V CAT III; 600 V CAT II

Jaw Opening Diameter: Cables 25 mm (1")

Dimensions: 29 H x 50 W x 187 mm L
(1.14 x 1.97 x 7.36")

Weight: Approximately 210 g (0.46 lb)



Electrical Specifications

ACA Function (Autorange)		
Range	Resolution	Accuracy
200 A	0.1 A	±2% rdg + 5 digits
400 A	1 A	

ACV Function (Autorange)		
Range	Resolution	Accuracy
200 V	0.1 V	±1.5% rdg + 5 digits
600 V	1 V	

Ohm Function		
Range	Resolution	Accuracy
200 Ω	0.1 Ω	±1.9% rdg + 3 digits

Continuity	
Range	Active Sound Level
)))	≤100 Ω

AVAILABLE FOR FAST DELIVERY!

To Order (Specify Model)		
Model No.	Price	Description
HHM221	\$60	Mini current clamp meter
HHM-NIST	55	NIST-traceable calibration certificate
GE-2028	34	Reference Book: Elements of Electronics

Comes with carrying case, 2 “AAA” batteries, test leads, and complete operator’s manual.

Ordering Example: HHM221, mini current clamp meter, \$60.

omega.co.uk[®]

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

www.omega.co.uk



UNITED STATES

www.omega.com

1-800-TC-OMEGA
Stamford, CT.

UNITED KINGDOM

www.omega.co.uk

Manchester, England
0800-488-488
+44-(0)161-777-6611

CANADA

www.omega.ca

Laval(Quebec)
1-800-TC-OMEGA

FRANCE

www.omega.fr

0800-466-342

GERMANY

www.omega.de

Deckenfronn, Germany
0800-8266342

BENELUX

www.omega.nl

0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485, Ethernet and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters