

# OMEGAMARKER® Temperature Test Kit

- ✓ From 52 to 399°C  
(125 to 750°F) Range
- ✓ 3 Standard Kit Ranges:  
Low, High, Full Range
- ✓ 10 Markers Per Kit
- ✓ Individual Holders for  
Each Crayon
- ✓ 63 mm Long Crayons
- ✓ Sharpener and Case  
Included with Kit



Shown larger than actual size



For added convenience and versatility, OMEGA is introducing the OMEGAMARKER® Temperature Test Kits for those who must measure many different temperatures. Each kit includes 10 individual temperature-sensitive crayons plus a holder for each crayon and a crayon sharpener, all in a self-contained case.

The crayons indicate temperatures from 52 to 399°C (125 to 750°F) and are accurate to within  $\pm 1\%$ . Each crayon is 63 mm long.

The OMEGAMARKER® crayon is easy to use. Simply mark with the appropriate crayon the surface to be heated. When the desired temperature has been reached, the marker will liquefy. The crayons are suitable for testing most surfaces.

Typical applications include lab use, forging, heat treating and fabrication of metals, moulding of rubber and plastics, and general purpose use on any accessible heated surface.

## MOST POPULAR KITS

### Full Range Kit

°F	125	200	250	300	350	425	500	575	650	750
°C	52	93	121	149	177	218	260	302	343	399

There are ten crayons in each kit; one for each temperature (°F/°C).

### Low Range Kit

°F	125	150	175	200	225	250	275	300	325	350
°C	52	66	79	93	107	121	135	149	163	177

There are ten crayons in each kit; one for each temperature (°F/°C).

### High Range Kit

°F	300	350	400	450	500	550	600	650	700	750
°C	149	177	204	232	260	288	316	343	371	399

There are ten crayons in each kit; one for each temperature (°F/°C).

**ALL MODELS AVAILABLE  
FOR FAST DELIVERY!**

To Order, Specify:  
**OMEGAMARKER-FULL**

**£49<sup>50</sup>**

Kit includes  
10 crayons, holders,  
sharpener and case.

To Order, Specify:  
**OMEGAMARKER-LOW**

**£49<sup>50</sup>**

Kit includes  
10 crayons, holders,  
sharpener and case.

To Order, Specify:  
**OMEGAMARKER-HIGH**

**£49<sup>50</sup>**

Kit includes  
10 crayons, holders,  
sharpener and case.





# OMEGAMARKER® Custom Temperature Test Kit Select-A-Kit™

- ✓ Mix and Match  
User Selected  
Temperatures
- ✓ From 52 to 399°C  
(125 to 750°F) Range
- ✓ Kit of 10 Crayons  
Includes  
Sharpener and Case
- ✓ Individual Holders for  
Each Crayon
- ✓ 63 mm Long Crayons

The OMEGAMARKER® crayon is easy to use. Simply mark with the appropriate crayon the surface to be heated. When the desired temperature has been reached, the mark will be liquefy. The crayons are suitable for testing most surfaces.

The crayons indicate temperatures from 52 to 399°C (125 to 750°F) and are accurate to within  $\pm 1\%$ . Each crayon is 63 mm long.



Choose 1 or More of These Temperatures  
Total of 10 Crayons for £47 - Any Combination

Deg. F	Deg. C
125	52
131	55
138	59
144	62
150	66
156	69
163	73
169	76
175	79
182	83
188	87
194	90
200	93
206	97
213	101
219	104
225	107
231	111
238	114
244	118

Deg. F	Deg. C
250	121
256	124
263	128
269	132
275	135
282	139
288	142
294	146
300	149
306	152
313	156
319	159
325	163
331	166
338	170
344	173
350	177
363	184
375	191
388	198

Deg. F	Deg. C
400	204
413	212
425	218
438	226
450	232
463	239
475	246
488	253
500	260
525	274
550	288
575	302
600	316
650	343
700	371
750	399

An Invaluable Tool  
for the Person Who  
Has to Measure  
Many Different  
Temperatures

To Order Specify  
OMEGAMARKER-Custom-  
(List Ranges)

£49<sup>50</sup>

Kit includes 10 crayons,  
holder, sharpener  
and case

Ordering Example:  
OMEGAMARKER-CUSTOM-  
150/200/300/300/325/325/325/350/350/400F  
OMEGAMARKER® custom kit containing 10 crayons  
at specified temperatures in °F, £49.50.