




GENERAL PURPOSE COMPACT "ICE CUBE" PLUG-IN RELAYS

D2PR Series
\$9.60
All Models



D2PA6-10PK,
\$84/pack of 10,
shown smaller
than actual size.



D2PR4A, \$9.60,
shown smaller
than actual size.

- Ultra-High Sensitivity Relay with Quick Response
- Designed Small, 2-Pole Type Break 5 A Load and 4-Pole Type, 3 A Load
- High Reliability, Long Life
- Panel, DIN Rail and Flange Mounting
- Small Size



The D2PR series relays are general purpose plug-in style relays. These 4PDT relays are extremely compact and are available with coil voltage of 24 Vdc and 120 Vac.

SPECIFICATIONS

- Contact Configuration:** 4PDT
- Rated Load:** 240 Vac 3 A, 30 Vdc 3 A
- Carry Current:** 3 A
- Max Operating Voltage:** 250 Vac/125 Vdc
- Max Operating Current:** 3 A
- Contact Material:** Ag (Au flashed)
- Max Switching Capacity:** 660 VA 72 W with resistive load of (p.f. = 1), 176 VA 36 W with inductive load (p.f. = 0.4, L/R = 7 ms)
- Min Permissible Load:** 1 mA, 1 Vdc
- Pickup Voltage (Max):** 80%
- Drop Out Voltage (Min):** 30% AC, 10% DC
- Voltage (Max):** 110%
- Mechanical Life (Min):** 10,000,000 operations
- Electrical Life @ All Contact Ratings (Min):** 200,000 operations
- Maximum hp Ratings:** 1/10 hp (120/240 Vac)

D2PA6 SOCKET SPECIFICATIONS

- Socket Type:** Screw terminal
- Electrical Ratings:** 10 A, 300V
- Mounting Torque:** 0.79 to 0.90 Nm (7 to 8 in-lb)
- Hook-Up Wire Range:** 14 to 28 AWG solid or stranded
- Hold Down Clip:** PMC-A1 (when used with D2PR4 relay)



To Order (Specify Model Number)

AVAILABLE FOR FAST DELIVERY!

MODEL NO.	PRICE	DESCRIPTION
D2PR4A	\$9.60	4 PDT relay, 110 Vac coil voltage
D2PR4T1	9.60	4 PDT relay, 24 Vdc coil voltage
D2PA6-10PK	84.00	Screw terminal, socket for D2PR4A and D2PR4T1 relays (requires PMC-A1 hold down clip), 10 pack
PMC-A1-10PK	14.00	Hold down clip for D2PA6 screw terminals, 10 pack

Ordering Example: Ten D2PR4A, relay, D2PA6-10PK, 10 pack of relay sockets, PMC-A1-10PK, 10 pack of hold-down springs, \$9.60 x 10 + 84 + 14 = \$194.

omega.co.uk[®]

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

www.omega.co.uk



UNITED STATES

www.omega.com

1-800-TC-OMEGA
Stamford, CT.

UNITED KINGDOM

www.omega.co.uk

Manchester, England
0800-488-488
+44-(0)161-777-6611

CANADA

www.omega.ca

Laval(Quebec)
1-800-TC-OMEGA

FRANCE

www.omega.fr

0800-466-342

GERMANY

www.omega.de

Deckenfronn, Germany
0800-8266342

BENELUX

www.omega.nl

0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485, Ethernet and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters