

FAST ACTING FUSES



Starts at
£24
Pack of 10



Fast Acting 600V Fuse

- Compact Dimensions
- High Interrupting Rating
- Fast-Acting Design Responds Quickly to Both Overloads and Short-Circuit Current

A fast-acting, high-interrupting capacity, current-limiting type fuse. The MCL style fuse feature provides an excellent choice for applications such as: street lighting holders, HID lighting, control circuits, electronic equipment protection.

SPECIFICATIONS

Dimensions: 10 mm ferrule, 38 mm length

Weight: Approx 0.09 Kg

Voltage Rating: MCL - 600 Vac

Ampere Rating: 0.1 to 50 A

Interrupting Rating: 100 K RMS amps

Agency Approvals: (0.1 to 30) UL Listed to 198G, File E162443; (0.1 to 30) CSA Cert. C22.2 Part 59.2, LR700489

Fast Acting 250V Fuse

- Compact Dimensions
- Economical Laminated Paper Tube Design

The MOL is an economical solution for over current protection. The MOL style fuse feature provides an excellent choice for applications such as: supplemental protection for noninductive control and lighting circuits.

SPECIFICATIONS

Dimensions: 10 mm ferrule, 38 mm length

Weight: Approx 0.09 Kg

Voltage Rating: MOL - 250 Vac

Ampere Rating: 0.5 to 30 A

Interrupting Rating: 10 K RMS amps

Agency Approvals: (0.5 - 30) UL Listed to 198G, File E162443; (0.5 - 30) CSA Cert. C22.2 Part 59.2, LR700489



MCL10-10PK, £25, shown larger than actual size.

MEQ30-10PK, £29.50, shown larger than actual size.

To Order (Specify Model Number)			MOST POPULAR MODELS HIGHLIGHTED!		
MODEL NO.	PACK OF 10	AMP RATING	MODEL NO.	PACK OF 10	AMP RATING
MCL.5-10PK	£26.50	0.5	MCL8-10PK	£26	8
MCL1-10PK	25.00	1	MCL10-10PK	25	10
MCL1.5-10PK	27.50	1.5	MCL12-10PK	29	12
MCL2-10PK	25.00	2	MCL15-10PK	25	15
MCL2.5-10PK	30.50	2.5	MCL20-10PK	25	20
MCL3-10PK	25.00	3	MCL25-10PK	25	25
MCL3.5-10PK	32.00	3.5	MCL30-10PK	25	30
MCL4-10PK	26.00	4	MCL35-10PK	32	35
MCL5-10PK	25.00	5	MCL40-10PK	29	40
MCL6-10PK	24.00	6	MCL50-10PK	33	50
MODEL NO.	PACK OF 10	AMP RATING	MODEL NO.	PACK OF 10	AMP RATING
MEQ.25-10PK	£33.50	0.25	MEQ5-10PK	£29.50	5
MEQ.5-10PK	31.50	0.5	MEQ6-10PK	29.50	6
MEQ1-10PK	29.50	1	MEQ7-10PK	31.50	7
MEQ1.5-10PK	31.50	1.5	MEQ8-10PK	29.50	8
MEQ2-10PK	29.50	2	MEQ10-10PK	29.50	10
MEQ2.5-10PK	31.50	2.5	MEQ12-10PK	29.50	12
MEQ3-10PK	29.50	3	MEQ15-10PK	29.50	15
MEQ3.5-10PK	33.50	3.5	MEQ20-10PK	29.50	20
MEQ4-10PK	29.50	4	MEQ25-10PK	29.50	25
MEQ4.5-10PK	36.00	4.5	MEQ30-10PK	29.50	30

Comes with instruction sheet.

Ordering Example: MCL10-10PK, 10 A fuse, pack of 10, £25.



TIME DELAY FUSES

Starts at
£5.50
Pack of 10



Time-Delay 500V Fuses

- Compact Dimensions
- Fiber Tube Construction
- Time-Delay Allows Harmless Inductive Surges to Pass Without Needless Fuse Opening

The MEQ midget class time delay fuse is ideal for the many applications including supplemental protection of transformers, solenoids, and other high inrush circuits.

SPECIFICATIONS

Dimensions: 10 mm ferrule, 38 mm length

Weight: Approx 0.09 Kg

Voltage Rating: MEQ - 500 Vac

Ampere Rating: 0.1 to 30 A

Interrupting Rating: 10 K RMS amps

Agency Approvals: (0.1 - 30) UL Listed to 198G, File E162443; (0.1 - 30) CSA Cert. C22.2 Part 59.2, LR700489

Time-Delay 250V Fuses

- Compact Dimensions
- Fiber Tube Construction
- Dual-Element Construction Allows Harmless Inductive Surges to Pass Without Opening

The MEN midget class time delay fuse is ideal for the many applications including supplemental protection of small motors, transformers, solenoids, and other high inrush power electronic circuits.

SPECIFICATIONS

Dimensions: 10 mm ferrule, 38 mm length

Weight: Approx 0.09 Kg

Voltage Rating: MEN - 250 Vac

Ampere Rating: 0.5 to 30 A

Interrupting Rating: 10K RMS amps @ 125 V

Agency Approvals: UL Listed to 198G, File E162443; CSA Cert. C22.2 Part 59.2, LR700489



MEN10-10PK, £11, shown actual size.



MOL10-10PK, £5.50, shown larger than actual size.

To Order (Specify Model Number)			MOST POPULAR MODELS HIGHLIGHTED!		
MODEL NO.	PACK OF 10	AMP RATING	MODEL NO.	PACK OF 10	AMP RATING
MEN.5-10PK	£12.50	0.5	MEN5-10PK	£11.00	5
MEN.6-10PK	12.50	0.6	MEN6-10PK	11.75	6
MEN1-10PK	11.75	1	MEN7-10PK	11.00	7
MEN1.4-10PK	15.00	1.4	MEN8-10PK	11.00	8
MEN1.5-10PK	12.50	1.5	MEN10-10PK	11.00	10
MEN2-10PK	11.00	2	MEN12-10PK	12.50	12
MEN2.5-10PK	11.75	2.5	MEN15-10PK	11.25	15
MEN3-10PK	11.00	3	MEN20-10PK	11.75	20
MEN3.5-10PK	11.00	3.5	MEN25-10PK	12.50	25
MEN4-10PK	11.00	4	MEN30-10PK	11.75	30
MODEL NO.	PACK OF 10	AMP RATING	MODEL NO.	PACK OF 10	AMP RATING
MOL.5-10PK	£7.70	0.5	MOL6-10PK	£6.20	6
MOL1-10PK	6.20	1	MOL8-10PK	6.20	8
MOL1.5-10PK	7.70	1.5	MOL10-10PK	5.50	10
MOL2-10PK	6.20	2	MOL15-10PK	5.50	10
MOL2.5-10PK	7.70	2.5	MOL20-10PK	7.70	20
MOL3-10PK	6.20	3	MOL25-10PK	7.70	25
MOL4-10PK	7.70	4	MOL30-10PK	6.70	30
MOL5-10PK	6.20	5			

Comes with instruction sheet.

Ordering Example: MOL10-10PK, 10 A fuse, pack of 10, £5.50.



UNITED STATES

www.omega.com

1-800-TC-OMEGA

Stamford, CT.

CANADA

www.omega.ca

Laval(Quebec)

1-800-TC-OMEGA

GERMANY

www.omega.de

Deckenpfronn, Germany

0800-8266342

UNITED KINGDOM

www.omega.co.uk

Manchester, England

0800-488-488

FRANCE

www.omega.fr

088-466-342

CZECH REPUBLIC

www.omegaeng.cz

Karviná, Czech Republic

596-311-899

BENELUX

www.omega.nl

0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters