

OMG-USB-232-2, OMG-USB-232-4 and OMG-USB-232-8

Two, Four and Eight Port RS-232 to USB Adaptors



OMG-USB-232-4, \$209,
Shown smaller than actual size

Starts at
\$159



- ✔ Power Obtained from USB Cable - No External Power Required
- ✔ "Hot swapping"/ Auto Configuration
- ✔ High Speed UART with 128 byte TX FIFO and 384 byte RX FIFO Supporting Standard PC Data Rates up to 460.8K bps
- ✔ 1.8 M (6') High Quality USB Cable Provided
- ✔ Includes Driver and Utility Software

The OMG-USB-232 USB to serial I/O adaptors provide two, four or eight RS-232 serial ports for USB connectivity to legacy or non-USB compliant devices. OMB-USB-232 adaptors support standard PC data rates up to 460K bps.

Simply install the included software and connect the OMB-USB-232 adaptor to your USB port. The device is immediately recognized by the system. At that point, simply connect the adaptor to your target device (i.e. modem, serial printer, scale, bar code/mag stripe reader, etc.).

Now your non-USB peripherals can have the same connection simplicity and ease of use as USB aware peripherals. We include our Windows 98/ME/2000/XP and Linux drivers to simplify installation.

Specifications

Number of Ports: 2, 4 or 8

Max. Data Rate: 460K

Max. Data Distance:
up to 15 m (50')

Operating Temperature:
0 to 50°C (32 to 122°F)

Storage Temperature:
-50 to 105°C (-58 to 221°F)

Humidity Range: 10 to 90%
RH non-condensing

Power: USB cable

Connector(s): 2, 4 or 8 DB9P
(male)

Dimensions:

OMG-USB-232-2, -4;
17.78 L x 13.34 W x 3.81 cm H
(7.0 x 5.25 x 1.5"):

OMG-USB-232-8;
22.1 L x 15.5 W x 5.1 cm H
(8.7 x 6.1 x 2.0")



OMG-USB-232-2, \$159,
Shown smaller than actual size



OMG-USB-232-4, \$209,
Shown smaller than actual size



OMG-USB-232-8, \$399,
Shown smaller than actual size

IN STOCK FOR FAST DELIVERY!

To Order (Specify Model Number)

Model Number	Price	Description
OMG-USB-232-2	\$159	2 port RS-232 to USB adaptor
OMG-USB-232-4	209	4 port RS-232 to USB adaptor
OMG-USB-232-8	399	8 port RS-232 to USB adaptor
OMG-CA177	8	DB9F/25M 1.8 m (6') cable
OMG-CA179	8	1.8 m (6') USB A to B cable
OMG-DR102	10	DIN rail mounting kit

All **OMG-USB-232** converters include utility software and a complete user's manual on CD-ROM and an **OMG-CA179** USB cable.
Ordering example: **OMG-USB-232-2** 2 port RS-232 to USB adaptor, **\$159**.



OMG-CA179 USB cable, \$8
and software CD shown
smaller than actual size

omega.co.uk[®]

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

www.omega.co.uk



UNITED STATES

www.omega.com

1-800-TC-OMEGA

Stamford, CT.

CANADA

www.omega.ca

Laval(Quebec)

1-800-TC-OMEGA

GERMANY

www.omega.de

Deckenpfronn, Germany

0800-8266342

UNITED KINGDOM

www.omega.co.uk

Manchester, England

0800-488-488

FRANCE

www.omega.fr

088-466-342

CZECH REPUBLIC

www.omegaeng.cz

Karviná, Czech Republic

596-311-899

BENELUX

www.omega.nl

0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters