

OMG-USB-SER-2, OMG-USB-SER-4 and OMG-USB-SER-8 Port RS-232/422/485 to USB Adaptors



OMG-USB-SER-4, \$279,
Shown smaller than actual size

\$229
Basic Unit



- ✓ **Field Selectable Interface**
- ✓ **Power Obtained from USB Cable – No External Power Required**
- ✓ **Automatic RS-485 Data Enable/Disable**
- ✓ **“Hot Swapping”/Auto Configuration**
- ✓ **High Speed UART with 128 byte TX FIFO and 384 byte RX**
- ✓ **FIFO Supporting Standard PC Data Rates up to 921.6K bps**
- ✓ **1.8 M (6') High Quality USB Cable Included**
- ✓ **Includes Driver and Utility Software**

The OMG-USB-SER USB to serial I/O adaptors provide two, four or eight RS-232/422/485 serial ports for USB connectivity to legacy or non-USB compliant devices.

Each port is individually configurable for RS-232, RS-422 or RS-485 communications via internal dip switch settings.

OMB-USB-SER adaptors support standard PC data rates up to 921.6K bps. Simply install the included software and connect the OMB-USB-SER adaptor to your USB port.

The device is immediately recognized by the system. At that point, simply connect the adaptor to your target device (i.e. modem, serial printer, scale, bar code/mag stripe reader, etc.).

Now your non-USB peripherals can have the same connection simplicity and ease of use as USB aware peripherals. We include our Windows 98/ME/2000/XP and Linux drivers to simplify installation.

Specifications

Number of Ports: 2, 4 or 8

Interface: Field selectable RS-232/422/485

Max. Data Rate: 921.6K bps

Max. Data Distance: Up to 1219 m (4000')

Operating Temperature: 0 to 50°C (32 to 122 °F)

Storage Temperature: -50 to 105°C (-58 to 221°F)

Humidity Range: 10 to 90% RH non-condensing

Power: USB cable

Connector(s): 2, 4 or 8 DB9P (male)

Dimensions:

OMG-USB-SER-2, -4;
17.78 L x 13.34 W x 3.81 cm H
(7.0 x 5.25 x 1.5"):

OMG-USB-SER-8;
22.1 L x 15.5 W x 5.1 cm H
(8.7 x 6.1 x 2.0")



OMG-USB-SER-2, \$229,
Shown smaller than actual size



OMG-USB-SER-4, \$279,
Shown smaller than actual size



OMG-USB-SER-8, \$499,
Shown smaller than actual size

IN STOCK FOR FAST DELIVERY!



OMG-CA179 USB cable, \$8
and software CD shown
smaller than actual size

To Order (Specify Model No.)

Model No.	Price	Description
OMG-USB-SER-2	\$229	2 port RS-232/422/485 to USB adaptor
OMG-USB-SER-4	279	4 port RS-232/422/485 to USB adaptor
OMG-USB-SER-8	499	8 port RS-232/422/485 to USB adaptor
OMG-CA176	10	DB9F/25M RS-530 cable
OMG-CA177	8	DB9F/25M 1.8 m (6') cable
OMG-CA179	8	1.8 m (6') USB A to B cable
OMG-DR102	10	DIN rail mounting kit

All **OMG-USB-SER** converters include utility software and a complete user's manual on CD-ROM, and an **OMG-CA179** USB cable.

Ordering Example: **OMG-USB-SER-2** 2 port RS-232/422/485 to USB adaptor, \$229.

omega.co.uk[®]

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

www.omega.co.uk



UNITED STATES

www.omega.com

1-800-TC-OMEGA
Stamford, CT.

UNITED KINGDOM

www.omega.co.uk

Manchester, England
0800-488-488
+44-(0)161-777-6611

CANADA

www.omega.ca

Laval(Quebec)
1-800-TC-OMEGA

FRANCE

www.omega.fr

0800-466-342

GERMANY

www.omega.de

Deckenfronn, Germany
0800-8266342

BENELUX

www.omega.nl

0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485, Ethernet and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters