

# Compression Fittings OMEGALOK®

SSLK Series  
Starts at  
**£4.70**



- ✓ Ferrule Design for Positive Pressure Seal
- ✓ Heavy Duty Construction in Stainless Steel or Brass
- ✓ For Protection Tube Diameters 1/16" up to 1/2"

## BSP Threaded Fittings for Metric Tube/Probe Diameters

**MOST POPULAR MODELS HIGHLIGHTED!**

### To Order Compression Fittings (Specify Model Number)

BSP Parallel Thread	BSP Tapered Thread	Protection Tube OD (mm)	Male Thread (in)	Price
SSLK-M30-18P	SSLK-M30-18T	3.0	1/8	£4.70
SSLK-M45-18P	SSLK-M45-18T	4.5	1/8	4.70
SSLK-M60-18P	SSLK-M60-18T	6.0	1/8	4.70
SSLK-M30-14P	SSLK-M30-14T	3.0	1/4	6.90
SSLK-M45-14P	SSLK-M45-14T	4.5	1/4	6.90
SSLK-M60-14P	SSLK-M60-14T	6.0	1/4	6.90
SSLK-M30-12P	SSLK-M30-12T	3.0	1/2	9.75
SSLK-M45-12P	SSLK-M45-12T	4.5	1/2	9.75
SSLK-M60-12P	SSLK-M60-12T	6.0	1/2	9.75

SSLK-M60-14P,  
£6.90, shown  
smaller than  
actual size.



## BSP Threaded Fittings for Imperial Tube/Probe Diameters

**MOST POPULAR MODELS HIGHLIGHTED!**

### To Order Compression Fittings (Specify Model Number)

BSP Parallel Thread	BSP Tapered Thread	Protection Tube OD (")	Male Thread (in)	Price
SSLK-18-18P	SSLK-18-18T	1/8	1/8	£4.70
SSLK-316-18P	SSLK-316-18T	3/16	1/8	4.70
SSLK-14-18P	SSLK-14-18T	1/4	1/8	4.70
SSLK-18-14P	SSLK-18-14T	1/8	1/4	6.90
SSLK-316-14P	SSLK-316-14T	3/16	1/4	6.90
SSLK-14-14P	SSLK-14-14T	1/4	1/4	6.90
SSLK-18-12P	SSLK-18-12T	1/8	1/2	9.75
SSLK-316-12P	SSLK-316-12T	3/16	1/2	9.75
SSLK-14-12P	SSLK-14-12T	1/4	1/2	9.75

SSLK-14-14P,  
£6.90, shown  
smaller than  
actual size.



## BSP Threaded Fittings for Imperial Tube/Probe Diameters

**MOST POPULAR MODELS HIGHLIGHTED!**



Compression Fittings

### To Order (Specify Model Number)

Protection Tube O.D. in.	Male Th's NPT	Length mm (inches)	Brass		316 Stainless Steel	
			Model No.	Pr. Ea.	Model No.	Pr. Ea.
1/16	1/16	24.6 (0.97)	N/A	—	SSLK-116-116	£11.50
1/16	1/8	26.2 (1.03)	BRLK-116-18	£4.00	SSLK-116-18	10.75
1/8	1/8	30.0 (1.18)	BRLK-18-18	4.00	SSLK-18-18	8.00
1/8	1/4	44.2 (1.74)	BRLK-18-14	4.00	SSLK-18-14	9.40
3/16	1/8	31.0 (1.22)	BRLK-316-18	4.00	SSLK-316-18	8.00
3/16	1/4	46.0 (1.81)	BRLK-316-14	4.00	SSLK-316-14	9.40
1/4	1/8	32.8 (1.29)	BRLK-14-18	4.00	SSLK-14-18	7.40
1/4	1/4	37.6 (1.48)	BRLK-14-14	3.40	SSLK-14-14	7.40
5/16	1/4	39.1 (1.54)	N/A	—	SSLK-516-14	10.00
3/8	1/4	40.4 (1.59)	BRLK-38-14	3.40	SSLK-38-14	10.75
3/8	3/8	40.4 (1.59)	BRLK-38-38	3.40	SSLK-38-38	12.00
3/8	1/2	46.0 (1.81)	BRLK-38-12	6.70	SSLK-38-12	14.75
1/2	1/2	49.3 (1.94)	BRLK-12-12	4.70	SSLK-12-12	14.00

**NOTE:** PFA can only be used with stainless steel compression fittings.  
**Ordering Example:** BRLK-18-18, brass 1/8 NPT compression fitting for 1/8" OD protection tubes, £4.00.

### Replacement Ferrules - (pkg of 10)

Protection Tube OD	Brass (£6.70/pkg)*	Stainless Steel (£20/pkg)*	PFA (£27/pkg)*
1/16	B-FER-1/16 (£15.50)	SS-FER-1/16 (£33.50)	T-FER-1/16 (£50)
1/8	B-FER-1/8	SS-FER-1/8	T-FER-1/8
3/16	B-FER-3/16 (£8)	SS-FER-3/16	T-FER-3/16
1/4	B-FER-1/4	SS-FER-1/4	T-FER-1/4
5/16	B-FER-5/16	SS-FER-5/16	T-FER-5/16
3/8	B-FER-3/8	SS-FER-3/8	T-FER-3/8
1/2	B-FER-1/2 (£10)	SS-FER-1/2	T-FER-1/2

\* Exceptions noted.