

OMEGAFLEX®

NATURAL LATEX, GUM RUBBER TUBING

TYGR-18116-50

\$19

Basic 50' Spool

OMEGAFLEX® latex tubing features superior flexibility and elasticity, maintaining its shape memory even after repeated stretching. No coagulants or fillers are added to the tubing, which minimizes migration into your fluid. This natural latex tubing has 0.87% trace sulphur.

SPECIFICATIONS*

Hardness, Shore A: 35 ±5

Specific Gravity: 0.95

Tensile Strength, PSI: 3500

Elongation at Break, %: 750

Brittle Temperature: -57°C (-70°F)

Operating Temperature Range: -54°C to 82°C
(-65°F to 180°F)

**Values listed are typical. Field testing should be done to find the actual values for the application.*



ALL MODELS AVAILABLE FOR FAST DELIVERY!

To Order (Specify Model Number)

½ to 1" OD Tubing

| Model No. | Price | Std Length (ft) | Wall (in) | OD (in) | ID (in) | lbs./100 ft. Length | psi @70°F |
|-----------------|-------|-----------------|-----------|---------|---------|---------------------|-----------|
| TYGR-18116-100 | \$ 37 | 100 | 1/32 | 1/8 | 1/16 | 1.00 | 15 |
| TYGR-18116-50 | 19 | 50 | 1/32 | 1/8 | 1/16 | 1.00 | 15 |
| TYGR-31618-100 | 37 | 100 | 1/32 | 3/16 | 1/8 | 1.50 | 10 |
| TYGR-31618-50 | 19 | 50 | 1/32 | 3/16 | 1/8 | 1.50 | 10 |
| TYGR-1418-100 | 47 | 100 | 1/16 | 1/4 | 1/8 | 2.00 | 15 |
| TYGR-1418-50 | 24 | 50 | 1/16 | 1/4 | 1/8 | 2.00 | 15 |
| TYGR-516316-100 | 48 | 100 | 1/16 | 5/16 | 3/16 | 2.50 | 12 |
| TYGR-516316-50 | 24 | 50 | 1/16 | 5/16 | 3/16 | 2.50 | 12 |
| TYGR-38316-100 | 69 | 100 | 3/32 | 3/8 | 3/16 | 4.25 | 15 |
| TYGR-38316-50 | 35 | 50 | 3/32 | 3/8 | 3/16 | 4.25 | 15 |
| TYGR-716316-100 | 94 | 100 | 1/8 | 7/16 | 3/16 | 6.00 | 17 |
| TYGR-716316-50 | 48 | 50 | 1/8 | 7/16 | 3/16 | 6.00 | 17 |
| TYGR-3814-100 | 56 | 100 | 1/16 | 3/8 | 1/4 | 3.25 | 10 |
| TYGR-3814-50 | 28 | 50 | 1/16 | 3/8 | 1/4 | 3.25 | 10 |
| TYGR-71614-100 | 74 | 100 | 3/32 | 7/16 | 1/4 | 5.00 | 12 |
| TYGR-71614-50 | 37 | 50 | 3/32 | 7/16 | 1/4 | 5.00 | 12 |
| TYGR-1214-100 | 100 | 100 | 1/8 | 1/2 | 1/4 | 7.00 | 15 |
| TYGR-1214-50 | 50 | 50 | 1/8 | 1/2 | 1/4 | 7.00 | 15 |
| TYGR-5814-50 | 103 | 50 | 3/16 | 5/8 | 1/4 | 12.00 | 18 |
| TYGR-716516-100 | 62 | 100 | 1/16 | 7/16 | 5/16 | 4.00 | 8 |
| TYGR-716516-50 | 31 | 50 | 1/16 | 7/16 | 5/16 | 4.00 | 8 |
| TYGR-12516-100 | 87 | 100 | 3/32 | 1/2 | 5/16 | 6.00 | 11 |
| TYGR-12516-50 | 44 | 50 | 3/32 | 1/2 | 5/16 | 6.00 | 11 |
| TYGR-916516-50 | 68 | 50 | 1/8 | 9/16 | 5/16 | 8.50 | 13 |
| TYGR-1116516-50 | 119 | 50 | 3/16 | 1 1/16 | 5/16 | 13.00 | 16 |
| TYGR-1238-100 | 84 | 100 | 1/16 | 1/2 | 3/8 | 9.00 | 7 |
| TYGR-91638-50 | 60 | 50 | 3/32 | 9/16 | 3/8 | 7.00 | 10 |
| TYGR-5838-50 | 80 | 50 | 1/8 | 5/8 | 3/8 | 9.00 | 12 |
| TYGR-111612-50 | 82 | 50 | 3/32 | 1 1/16 | 1/2 | 9.50 | 8 |
| TYGR-3412-50 | 96 | 50 | 1/8 | 3/4 | 1/2 | 12.00 | 10 |
| TYGR-134-50 | 153 | 50 | 1/8 | 1 | 3/4 | 17.00 | 7 |

Note: Minimum continuous length: 6 feet.

Ordering Example: TYGR-1418-50, 50' of tubing, 1/16" wall, 1/4" OD, 1/8" ID, \$24.

omega.co.uk[®]

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

www.omega.co.uk



UNITED STATES

www.omega.com

1-800-TC-OMEGA
Stamford, CT.

UNITED KINGDOM

www.omega.co.uk

Manchester, England
0800-488-488
+44-(0)161-777-6611

CANADA

www.omega.ca

Laval(Quebec)
1-800-TC-OMEGA

FRANCE

www.omega.fr

0800-466-342

GERMANY

www.omega.de

Deckenfronn, Germany
0800-8266342

BENELUX

www.omega.nl

0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485, Ethernet and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters