


OMEGAFLEX® CHEMICAL TUBING
Teflon® PFA Formulation,
Metric Diameters



Thermocouple Wire
 Encased in PFA Tubing. See
 Pages L-71 and L-72 for
 details on Specialty Tubing

4 mm to 16 mm OD Metric Diameters

Model No.	Price	Std Length (ft)	Wall (mm)	OD (mm)	ID (mm)	psi @ 23°C/73°F
TYTP-42-50	\$107	50	1	4	2	400
TYTP-42-100	213	100	1	4	2	400
TYTP-64-25	65	25	1	6	4	265
TYTP-64-50	130	50	1	6	4	265
TYTP-64-100	260	100	1	6	4	265
TYTP-86-25	100	25	1	8	6	200
TYTP-86-50	200	50	1	8	6	200
TYTP-86-100	400	100	1	8	6	200
TYTP-108-25	134	25	1	10	8	160
TYTP-108-50	268	50	1	10	8	160
TYTP-108-100	536	100	1	10	8	160
TYTP-1210-25	157	25	1	12	10	130
TYTP-1210-50	314	50	1	12	10	130
TYTP-1210-100	628	100	1	12	10	130
TYTP-1412-25	175	25	1	14	12	110
TYTP-1412-50	350	50	1	14	12	110
TYTP-1412-100	700	100	1	14	12	110
TYTP-1614-25	245	25	1	16	14	100
TYTP-1614-50	490	50	1	16	14	100
TYTP-1614-100	980	100	1	16	14	100

Sold in standard lengths of 25, 50, and 100 ft.

Ordering Example: TYTP-86-50, 50 feet of tubing, 1 mm wall, 8 mm OD, 6 mm ID, \$200

**To Order, Specify
 Model Number**



Specialty Tubing Available!
 See Pages L-71 and L-72 for details

omega.co.uk[®]

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

www.omega.co.uk



UNITED STATES

www.omega.com

1-800-TC-OMEGA
Stamford, CT.

UNITED KINGDOM

www.omega.co.uk

Manchester, England
0800-488-488
+44-(0)161-777-6611

CANADA

www.omega.ca

Laval(Quebec)
1-800-TC-OMEGA

FRANCE

www.omega.fr

0800-466-342

GERMANY

www.omega.de

Deckenfronn, Germany
0800-8266342

BENELUX

www.omega.nl

0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485, Ethernet and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters