

OMEGAFLEX® VINYL TUBING



TYVY-3814-50
\$15
Basic 50' Spool



By Individual
Model No.†

Vinyl tubing is clear and flexible providing an economical means of fluid transfer in a variety of applications. Intermittent exposure to hydrocarbons, such as gasoline, kerosene, diesel fuel, etc. will cause premature hardening and failure of the tubing.

SPECIFICATIONS*

Hardness, Shore A ± 5 : 68

Specific Gravity: 1.20

Tensile Strength, psi: 2000

Elongation at Break: 400%

Brittle Temperature: -40°C (-40°F)

Maximum Operating Temperature:
 80°C (175°F)

Minimum Bend Radius:

ALL MODELS AVAILABLE FOR FAST DELIVERY!

To Order (Specify Model Number)

1/8 to 3/4" OD TUBING

Model No.	Price	Std Length (ft)	Wall (in)	OD (in)	ID (in)	Working psi at 68°F	lbs/100 ft
TYVY-18116-500	\$45	500	1/32	1/8	1/16	33	0.51
TYVY-532332-500	45	500	1/32	5/32	3/32	42	0.68
TYVY-170120-200	20	200	0.025	0.17	120	15	0.64
TYVY-31618-500	65	500	1/32	3/16	1/8	44	0.85
TYVY-1418-100	15	100	1/16	1/4	1/8	68	2.10
TYVY-1132532-100	35	100	3/32	1 1/32	3/32	73	4.10
TYVY-14170-100	15	100	0.04	1/4	170	42	1.50
TYVY-14316-100	20	100	1/32	1/4	3/16	33	1.20
TYVY-516316-100	20	100	1/16	3/16	3/16	55	2.70
TYVY-38316-100	35	100	3/32	3/8	3/16	70	4.60
TYVY-716316-50	15	100	1/8	7/16	3/16	80	6.90
TYVY-716316-100	30	100	1/8	7/16	3/16	80	6.90
TYVY-3814-50	15	50	1/16	3/8	1/4	55	3.40
TYVY-3814-100	25	100	1/16	3/8	1/4	55	3.40
TYVY-71614-100	35	100	3/32	7/16	1/4	60	5.70
TYVY-1214-100	60	100	1/8	1/2	1/4	70	8.30
TYVY-716516-100	30	100	1/16	7/16	3/16	50	4.20
TYVY-12516-100	45	100	3/32	1/2	3/16	60	6.80
TYVY-916516-100	60	100	1/8	3/4	3/16	70	9.70
TYVY-1238-100	35	100	1/16	1/2	3/8	40	4.80
TYVY-91638-100	55	100	3/32	3/4	3/8	50	7.80
TYVY-5838-100	70	100	1/8	5/8	3/8	65	11.10
TYVY-3438-100	195	100	3/16	3/4	3/8	66	18.70
TYVY-916716-100	40	100	1/16	3/4	7/16	40	5.50
TYVY-116716-100	95	100	1/8	1 1/16	7/16	50	12.50
TYVY-5812-100	45	100	1/16	5/8	1/2	30	6.20


*Specifications shown are typical and meant only as a guide. Field testing is recommended to find the actual values in the given application.

† Visit omega.com/rohs to determine specific RoHS compliance.

Note: The listed working pressures are based on short term burst using a 4 to 1 safety factor.

Ordering Example: TYVY-3438-100, 100' of tubing, 3/16" wall, 3/4" OD, 3/8" ID, \$195.

OMEGAFLEX® VINYL TUBING



ALL MODELS AVAILABLE FOR FAST DELIVERY!

To Order (Specify Model Number)							
1/16" to 4 3/4" OD TUBING							
Model No.	Price	Std Length (ft)	Wall (in)	OD (in)	ID (in)	Working psi at 68°F	lbs/100 ft
TYVY-111612-100	\$75	100	3/32	1 1/16	1/2	40	9.90
TYVY-3412-100	85	100	1/8	3/4	1/2	45	13.90
TYVY-34916-100	75	100	3/32	3/4	9/16	40	11.00
TYVY-3458-100	60	100	1/16	3/4	5/8	48	7.60
TYVY-131658-100	80	100	3/32	1 9/16	5/8	35	12.00
TYVY-7858-50	55	50	1/8	7/8	5/8	40	16.60
TYVY-7858-100	105	100	1/8	7/8	5/8	40	16.60
TYVY-7834-100	105	100	1/16	7/8	3/4	19	9.00
TYVY-134-50	65	50	1/8	1	3/4	35	19.40
TYVY-134-100	120	100	1/8	1	3/4	35	19.40
TYVY-11834-100	235	100	3/16	1 1/8	3/4	44	31.20
TYVY-11434-100	345	100	1/4	1 1/4	3/4	44	44.30
TYVY-11878-50	75	50	1/8	1 1/8	7/8	30	22.10
TYVY-11878-100	145	100	1/8	1 1/8	7/8	30	22.10
TYVY-1141-100	175	100	1/8	1 1/4	1	28	25.00
TYVY-1381-100	245	100	3/16	1 1/8	1	45	39.40
TYVY-1121-50	123	50	1/4	1 1/2	1	50	55.00
TYVY-1121-100	345	100	1/4	1 1/2	1	50	55.00
TYVY-112114-100	245	100	1/8	1 1/2	1 1/4	22	30.50
TYVY-158114-50	195	50	3/16	1 5/8	1 1/4	31	47.80
TYVY-158114-100	375	100	3/16	1 5/8	1 1/4	31	47.80
TYVY-134114-50	195	50	1/4	1 3/4	1 1/4	45	66.50
TYVY-134112-100	375	100	1/8	1 3/4	1 1/2	19	36.00
TYVY-178112-100	425	100	3/16	1 7/8	1 1/2	26	56.10
TYVY-2112-50	240	50	1/8	2	1 1/2	40	77.50
TYVY-2134-50	215	50	1/8	2	1 3/4	16	41.50
TYVY-214134-50	325	50	1/4	2 1/4	1 3/4	29	80.00
TYVY-2142-50	245	50	1/8	2 1/4	2	14	47.10
TYVY-2122-50	345	50	1/4	2 1/2	2	35	99.70
TYVY-234214-50	375	50	1/4	2 3/4	2 1/4	24	111.00
TYVY-3212-50	425	50	1/4	3	2 1/2	22	122.00
TYVY-3123-50	495	50	1/4	3 1/2	3	19	144.00
TYVY-4344-50	2500	50	3/8	4 3/4	4	21	300.00

Ordering Example: TYVY-1121-100, 100' of tubing, 1/4" wall, 1 1/2" OD, 1" ID, \$345.

Accessory

Model No.	Price	Description
FW-307	\$125	Reference Book: Handbook of Industrial Chemicals

Stainless steel overbraided, coiled, and other specialty tubing available! Contact OMEGA's Flow Engineering Department.



omega.co.uk[®]

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

www.omega.co.uk



UNITED STATES

www.omega.com

1-800-TC-OMEGA
Stamford, CT.

UNITED KINGDOM

www.omega.co.uk

Manchester, England
0800-488-488
+44-(0)161-777-6611

CANADA

www.omega.ca

Laval(Quebec)
1-800-TC-OMEGA

FRANCE

www.omega.fr

0800-466-342

GERMANY

www.omega.de

Deckenfronn, Germany
0800-8266342

BENELUX

www.omega.nl

0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485, Ethernet and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters