

ECONOMICAL MINIATURE TENSION OR COMPRESSION LOAD CELLS

19 TO 25 mm DIAMETER

LCMFL Series
Tension/Compression
Calibrated in Tension
0-10 to 0-500 N

All Models
\$595



Small and capable of highly accurate readings, the LCMFL subminiature load cells are suitable for precision industrial applications. They are all stainless steel, measure either tension or compression loads, and have male thread studs for load attachment. The exclusive internal design provides superior long-term stability and minimizes the effects of small off-axis loads.

SPECIFICATIONS

Excitation:

10 to 50 N: 5 Vdc
≥100 N: 10 Vdc

Output:

10 N: 1.0 mV/V (nom.)
20 to 500 N: 2 mV/V (nom.)

Accuracy (Linearity and Hysteresis Combined): ±0.50% FSO

Repeatability: ±0.20% FSO

5-Point Calibration (in Tension):

0%, 50%, 100%, 50%, 0%

Zero Balance: ±2% FSO

Operating Temp Range:

-53 to 121°C (-65 to 250°F)

Compensated Temp Range:

16 to 71°C (60 to 160°F)

Thermal Effects:

Span: ≥1 kg: ±0.009% rdg/°C

Zero: ≥1 kg: 0.009% FSO/°C

Deflection FS: 0.03 to 0.08 mm (0.001 to 0.003")

Safe Overload: 150% of capacity

Ultimate Overload: 300% of capacity

Bridge Resistance: 350 Ω minimum

Construction: Stainless steel

Electrical Connection: 1.5 m (5')


4-conductor, shielded TFE cable

Protection Rating: IP54

LCMFL-50N, \$595,
shown larger than
actual size.



LCMFL-500N, \$595,
shown larger than
actual size.



Dimensions: mm (in)

CAPACITY	A	B	C	D	E
10 to 50 N	19.1 (0.75)	10.1 (0.40)	6.4 (0.25)	9.7 (0.38)	3.8 (0.15)
≥100 N	25.4 (1.00)	9.9 (0.39)	9.7 (0.38)	7.0 (0.26)	5.0 (0.20)

MOST POPULAR MODELS HIGHLIGHTED!

To Order (Specify Model Number)

CAPACITY		MODEL NO.	PRICE	COMPATIBLE METERS*
N	lb			
10	2.2	LCMFL-10N	\$595	DP25B-S, DP41-S, DPiS
20	4.5	LCMFL-20N	595	DP25B-S, DP41-S, DPiS
50	11	LCMFL-50N	595	DP25B-S, DP41-S, DPiS
100	22	LCMFL-100N	595	DP25B-S, DP41-S, DPiS
200	45	LCMFL-200N	595	DP25B-S, DP41-S, DPiS
500	112	LCMFL-500N	595	DP25B-S, DP41-S, DPiS

Comes with 5-point NIST-traceable calibration.

* See section D for compatible meters. DPiS meter suitable for one direction measurement only.

Ordering Examples: LCMFL-10N, 10 N load cell, \$595, MREC-M5F, matching rod end, \$25. LCMFL-200N, 200 N load cell, \$595, MREC-M6F, matching rod end, \$25.

ACCESSORIES

MODEL NO.	PRICE	DESCRIPTION
MREC-M5F	\$25	M5 x 0.8 female-thread rod end
MREC-M6F	25	M6 x 1.00 female-thread rod end
ME-1746	190	Reference Book: Handbook of Machinery Dynamics



omega.co.uk[®]

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

www.omega.co.uk



UNITED STATES

www.omega.com

1-800-TC-OMEGA
Stamford, CT.

UNITED KINGDOM

www.omega.co.uk

Manchester, England
0800-488-488
+44-(0)161-777-6611

CANADA

www.omega.ca

Laval(Quebec)
1-800-TC-OMEGA

FRANCE

www.omega.fr

0800-466-342

GERMANY

www.omega.de

Deckenfronn, Germany
0800-8266342

BENELUX

www.omega.nl

0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485, Ethernet and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters