

CHART-TEMP® Temperature Recorders

CT-300F-1H,
\$709, shown
smaller than
actual size.

CT-100 Series
Starts at
\$675



**Comes with
Extra Charts!**



- ✓ **Accurate Swiss-Made Movement with Jeweled Bearings (Low-Temperature Model)**
- ✓ **From -40 to 260°C (-40 to 500°F)**
- ✓ **Low-Temperature Recorders with Ranges Up to 104°C (220°F) and Either 1- or 7-Day Charts and 2% Accuracy**
- ✓ **Oven Recorders with Ranges Up to 260°C (500°F) and Either 1- or 24-Hour Charts with 3% Accuracy**

OMEGA® CHART-TEMP® recorders are dry-stylus, spring-wound, clock-driven circular chart recorders. Simply rewind the drive when replacing the chart. These recorders are excellent for recording temperatures inside buildings, refrigerators, or ovens. Units with ranges up to 260°C (500°F) are available.

Specifications

Dimensions: 82.5 H x 100 mm Dia. (3.26 x 3.94")

Weight:

High-Temp Models: 397 g (14 oz)

Low-Temp Models: 600 g (21 oz)



Low-Temperature Recorders

**MOST POPULAR
MODELS HIGHLIGHTED!**

To Order (Specify Model Number)

Model No.	Price	Temperature Range	Charts Model No.	Price per 100 Charts
CT-100AF-(*)	\$675	0 to 100°F	(*)-100F	\$23
CT-120AF-(*)	675	20 to 120°F	(*)-120F	23
CT-160AF-(*)	675	-40 to 160°F	(*)-160F	23
CT-220AF-(*)	675	20 to 220°F	(*)-220F	23
CT-70AF-(*)	675	-30 to 70°F	(*)-70F	23

* Insert "1" for 1-day or "7" for 7-day recorder. Units with "-7" suffix are 7-day recorders. Comes with 100 charts.

OMEGACARESM extended warranty program is available for models shown on this page. OMEGACARESM covers parts, labor and equivalent loaners. Ask your sales representative for full details when placing an order.

Ordering Examples: CT-100AF-1, 1 hr recorder with 0 to 100°F temperature range, \$675. OCW-3, OMEGACARESM extends standard 1-year warranty to a total of 4 years (\$168), \$675 + 168 = \$843. CT-500F-1, 1-hr recorder with 70 to 500°F temperature range, \$709. OCW-3, OMEGACARESM extends standard 1-year warranty to a total of 4 years (\$177), \$709 + 177 = \$886.

High-Temperature Recorders

To Order (Specify Model Number)

Model No.	Price	Temperature Range	Charts Model No.	Price per 10 Charts
CT-300F-(*)	\$709	70 to 300°F	(*)-300F-CHART	\$65
CT-400F-1H	709	70 to 400°F	(*)-400F-CHART	65
CT-500F-(*)	709	70 to 500°F	(*)-500F-CHART	65
CT-150C-1H	709	20 to 150°F	1H-150C-CHART	65
CT-200C-1H	709	20 to 200°C	1H-200C-CHART	65
CT-260C-1H	709	20 to 260°C	1H-260C-CHART	65
GE-0661	190	Reference Book: Handbook of Reliability Engineering		

Comes with 10 charts each.

* Insert "1H" for 1 hr or "24H" for 24-hr recorder. Units with "-1H" suffix are 1-hr recorders.

omega.co.uk[®]

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

www.omega.co.uk



UNITED STATES

www.omega.com

1-800-TC-OMEGA
Stamford, CT.

UNITED KINGDOM

www.omega.co.uk

Manchester, England
0800-488-488
+44-(0)161-777-6611

CANADA

www.omega.ca

Laval(Quebec)
1-800-TC-OMEGA

FRANCE

www.omega.fr

0800-466-342

GERMANY

www.omega.de

Deckenfronn, Germany
0800-8266342

BENELUX

www.omega.nl

0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485, Ethernet and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters