

# Circular Chart Temperature Recorders

CT88 Series Starts at

£88



Recorders Can Be Placed Directly into the Measurement Environment!

Ideal for Monitoring and Recording Temperature in Critical Applications.

- ✓ 152 mm (6") Chart
- ✓ Built-In Bi-Metal Temperature Sensor
- ✓ On/Off Switch
- ✓ Portable, Wall Mount, or Free-Standing
- ✓ Durable Polycarbonate Case
- ✓ Blinking "ON" Light and Low Battery Indicator
- ✓ Large LCD Display (CT88D)
- ✓ 9 Volt Battery Operation
- ✓ AC Power Adaptor Furnished for 115 Vac 50/60 Hz Operation with Battery Back-Up, (208/240V Optional) 50/60 Hz



CT88D, £111.

■ MOST POPULAR MODELS HIGHLIGHTED!

To Order (Specify Model Number)		
Model No.	Price	Description
CT88D-(* )	£111.00	6" chart recorder with digital display
CT88N-(* )	88.00	6" chart recorder without digital display
CT88CH-(* )	12.25	Replacement charts (box of 60)
CTH89-PEN-RED	5.70	Replacement pen (red)
MN1604	2.00	Spare 9V battery

Comes complete with package of 60 charts, pen, two 9V batteries, AC adaptor and operator's manual.

\* Insert range code from chart below.

To order for 208/240V, 50/60 Hz operation, add "-220" to model number and £6.70 to price.

\* Select range code

Ordering Examples: CT88D--30-50C/24H, 6" circular chart recorder with display, 24-hour chart, -30 to 50°C range, £111.

OCW-3, OMEGACARE<sup>SM</sup> extends standard 1-year warranty to a total of 4 years (£25.50), £111 + 25.50 = £136.50

■ MOST POPULAR RANGE HIGHLIGHTED!

## Specifications

Accuracy: ±2% FS

Chart Size: 152 mm (6") diameter

Dimensions:

23.5 H x 18.4 W x 7.0 cm D  
(9 1/4 x 7 1/4 x 2 3/4")

Shipping Weight: 2.25 kg (5 lb)

Power: 115 Vac power adaptor or two 9V alkaline batteries (included)

Battery Only Operation: 1 year

Sensor Type: Bi-metal



OMEGACARE<sup>SM</sup> extended warranty program is available for models shown on this page. Ask your sales representative for full details when placing an order. OMEGACARE<sup>SM</sup> covers parts, labor and equivalent loaners.

Range Code	Temperature Range	Recording Time
-20-120F/7D	-20 to 120°F	7 days
0-100F/7D	0 to 100°F	
45-90F/7D	45 to 90°F	
-30-50C/7D	-30 to 50°C	
0-45C/7D	0 to 45°C	24-hr
-20-120F/24H	-20 to 120°F	
0-100F/24H	0 to 100°F	
45-90F/24H	45 to 90°F	
-30-50C/24H	-30 to 50°C	
0-45C/24H	0 to 45°C	

# omega.co.uk<sup>®</sup>

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

[www.omega.co.uk](http://www.omega.co.uk)



#### UNITED STATES

[www.omega.com](http://www.omega.com)

1-800-TC-OMEGA  
Stamford, CT.

#### CANADA

[www.omega.ca](http://www.omega.ca)

Laval(Quebec)  
1-800-TC-OMEGA

#### GERMANY

[www.omega.de](http://www.omega.de)

Deckenfronn, Germany  
0800-8266342

#### UNITED KINGDOM

[www.omega.co.uk](http://www.omega.co.uk)

Manchester, England  
0800-488-488  
+44-(0)161-777-6611

#### FRANCE

[www.omega.fr](http://www.omega.fr)

0800-466-342

#### BENELUX

[www.omega.nl](http://www.omega.nl)

0800-099-33-44



## More than 100,000 Products Available!

### • Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

### • Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

### • pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

### • Data Acquisition

Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485, Ethernet and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

### • Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

### • Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters