

Economical, Reversible Humidity Indicating Cards

HC Series Starts at **£20**

Basic Package of 100 to 500 Cards, Depending on Model



Economically Priced!

Humidity Indicating cards allow a low cost method of indicating humidity conditions for various types of barrier packaging, including Mil Spec (MIL-I-8835) applications. The 30%-40%-50% card complies with MS 20003-2.

Reversible!

Humidity Indicating Cards

HUMIDITY INDICATOR

EXAMINE ITEM IF PINK

CHANGE DESICCANT IF PINK

WARNING IF PINK

DISCARD IF CIRCLES OVERRUN

AVOID METAL CONTACT

HC-30/50-125

HUMIDITY INDICATOR

60%

50%

40%

30%

20%

10%

Danger if Pink - Change Desiccant
Read at Lavender Between Pink and Blue

HC-10/60-200

HUMIDITY INDICATOR

Desiccant active if spot matches panel or is a darker shade of Blue

HC-8-500

Shown close to actual size.

HUMIDITY INDICATOR

Examine Item If Pink

Change Desiccant if Pink

Warning if Pink

Discard if Circles Overrun
Avoid Metal Contact

HC-10/30-125

HUMIGAUGE

Discard if Circles Overrun Avoid Metal Contact

Read at Lavender

HC-10/40-100

ALL MODELS AVAILABLE FOR FAST DELIVERY!

To Order (Specify Model Number)				
Model Number	Price	Humidity Range	Quantity	Card Dimensions (in)
HC-10/30-125	£20	10 to 30%	125	3 3/8 x 2
HC-30/50-125	20	30 to 50%	125	3 3/8 x 2
HC-10/40-100	21.50	10 to 40%	100	3 3/8 x 2
HC-10/60-200	54	10 to 60%	200	4 1/16 x 1 1/2
HC-8-500	63	8%	500	2 3/16 x 1 1/2

Ordering Example: HC-10/30-125, humidity indicating cards, 10 to 30% RH, package of 125, £20.



UNITED STATES

www.omega.com

1-800-TC-OMEGA

Stamford, CT.

CANADA

www.omega.ca

Laval(Quebec)

1-800-TC-OMEGA

GERMANY

www.omega.de

Deckenpfronn, Germany

0800-8266342

UNITED KINGDOM

www.omega.co.uk

Manchester, England

0800-488-488

FRANCE

www.omega.fr

088-466-342

CZECH REPUBLIC

www.omegaeng.cz

Karviná, Czech Republic

596-311-899

BENELUX

www.omega.nl

0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters