

Handheld Light Meter



HHLM1337, £67,
shown actual size.

HHLM1337
£67



- ✓ 3½-Digit LCD Display LUX, FC, Low-Battery
- ✓ Max/Min Button
- ✓ Data Hold Button
- ✓ Auto Power-Off
- ✓ Easy-to-Use
- ✓ Pocket-Sized and Lightweight

The HHLM1337 has a large display for easy viewing of light levels. It can measure a wide range of either LUX or footcandles. Applications include indoor light and work area lighting monitoring and verification. Useful for facilities engineers, building maintenance personnel and anyone who wants to measure illuminance.

Specifications

Range: 20/200/2000/20,000 LUX/FC

Accuracy: ±3% rdg ±0.5% FS; ±4% rdg ±10 digits for >10,000 LUX/FC

Resolution: 0.01 LUX

Dimensions:

Sensor: 114.3 x 61.0 x 25.4 mm (4.5 x 2.4 x 1")

Unit: 188.0 x 63.5 x 25.4 mm (7.4 x 2.5 x 1")

Power Source: 6 "AAA" batteries (included)

Weight: 5.6 oz (0.5 lb)

AVAILABLE FOR FAST DELIVERY!

To Order (Specify Model Number)		
Model No.	Price	Description
HHLM1337	£67.00	Handheld light meter
GE-2064	43.50	Reference Book: Osha Inspections, Preparation and Response

Comes with operator's manual, light sensor with cover and 6 "AAA" batteries.

Ordering Example: HHLM1337, handheld light meter, £67.



UNITED STATES

www.omega.com

1-800-TC-OMEGA

Stamford, CT.

CANADA

www.omega.ca

Laval(Quebec)

1-800-TC-OMEGA

GERMANY

www.omega.de

Deckenpfronn, Germany

0800-8266342

UNITED KINGDOM

www.omega.co.uk

Manchester, England

0800-488-488

FRANCE

www.omega.fr

088-466-342

CZECH REPUBLIC

www.omegaeng.cz

Karviná, Czech Republic

596-311-899

BENELUX

www.omega.nl

0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters