

Economical Non-Contact Pocket Optical Tachometer



HHT12
£107



- ✓ Operating Range Up to 915 mm (Red LED)
- ✓ Rugged Ergonomic Rubberised Housing
- ✓ Lock "ON"
- ✓ Tripod Mounting Bushing for Hands-Free Operation
- ✓ Auto-Ranging or Fixed-Decimal User Selectable

The HHT12 is a digital, battery-powered portable optical tachometer with a no-slip rubber housing. The unique design allows users to view the target and the display at the same time. The HHT12 is the value-leader of the world-class Pocket Tachometer Series from OMEGA®.

Specifications

Display: 5-digit alphanumeric LCD
Range: 5 to 99,999 rpm
Accuracy: 0.01% of reading or ±1 digit
Resolution:
 Auto-Ranging: 0.001 to 1.0 rpm
 Fixed: ±1 digit rpm
Operating Range: 50 to 915 mm (2 to 36")
Memory: Maximum, minimum and last
Power: 2 "AA" 1.5 Vdc batteries (included)
Environmental: 5 to 40°C (0 to 100°F), 80% RH up to 30°C (86°F)
Dimensions: 176 x 61 x 41 mm (6.9 x 2.4 x 1.6")
Weight: 210 g (7 oz)



HHT12, £107, shown smaller than actual size.



ALL MODELS AVAILABLE FOR FAST DELIVERY!

To Order (Specify Model Number)		
Model No.	Price	Description
HHT12	£107	Basic tachometer with 300 mm reflective tape
HHT13-CC10	16.75	Padded pouch fits tachometer
HHT-RT-5	8.70	Reflective tape 1.5 m roll, 12 mm wide
PE-1410	47	Reference Book: Practical Optics

Comes with two 150 x 12 mm strips of reflective tape, 2 "AA" batteries and complete operator's manual.

Ordering Examples: HHT12, basic tachometer, HHT13-CC10, padded pouch, HHT-RT-5, spare reflective tape, £107 + 16.75 + 8.70 = £132.45.

OCW-3, OMEGACARESM extends standard 1-year warranty to a total of 4 years (£27), £107 + 27 = £134.

OMEGACARESM extended warranty programme is available for models shown on this page. Ask your sales representative for full details when placing an order. OMEGACARESM covers parts, labour and equivalent loaners.

omega.co.uk[®]

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

www.omega.co.uk



UNITED STATES

www.omega.com

1-800-TC-OMEGA

Stamford, CT.

CANADA

www.omega.ca

Laval(Quebec)

1-800-TC-OMEGA

GERMANY

www.omega.de

Deckenpfronn, Germany

0800-8266342

UNITED KINGDOM

www.omega.co.uk

Manchester, England

0800-488-488

FRANCE

www.omega.fr

088-466-342

CZECH REPUBLIC

www.omegaeng.cz

Karviná, Czech Republic

596-311-899

BENELUX

www.omega.nl

0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters