

TFE and Kapton® Insulated Thermocouple Wire

TFE Insulated Thermocouple Wire



"SLE" Special Limits of Error Available

ANSI color code shown
To order IEC color code see omega.com

Color-coded TFE tape applied to conductors and jacket. Superior abrasion, moisture, and chemical resistance.



MOST POPULAR MODELS HIGHLIGHTED!

Calibration ANSI Code	AWG No.	Model Number	Price/1000*	SLE/1000**	Type Wire	Insulation		Max Temp		Nominal Size mm (in)	Wt./1000' kg (lb)
						Conductor	Overall	°C	°F		
J Iron - Constantan	20	TFE-J-20	\$450	\$510	Solid	Fused TFE Tape	Fused TFE Tape	260	500	1.5 x 2.5 (0.060 x 0.100)	5 (11)
	20S	TFE-J-20S	570	650	7 x 28	Fused TFE Tape	Fused TFE Tape	260	500	1.5 x 2.7 (0.060 x 0.105)	5 (11)
	24	TFE-J-24	315	350	Solid	Fused TFE Tape	Fused TFE Tape	260	500	1.3 x 1.9 (0.050 x 0.075)	3 (6)
	24S	TFE-J-24S	370	415	7 x 32	Fused TFE Tape	Fused TFE Tape	260	500	1.3 x 2.2 (0.050 x 0.085)	3 (6)
K CHROMEKA® - ALOMEGA®	20	TFE-K-20	\$620	\$695	Solid	Fused TFE Tape	Fused TFE Tape	260	500	1.5 x 2.5 (0.060 x 0.100)	5 (11)
	20S	TFE-K-20S	955	1085	7 x 28	Fused TFE Tape	Fused TFE Tape	260	500	1.5 x 2.7 (0.060 x 0.105)	5 (11)
	24	TFE-K-24	420	470	Solid	Fused TFE Tape	Fused TFE Tape	260	500	1.3 x 1.9 (0.050 x 0.075)	3 (6)
	24S	TFE-K-24S	570	650	7 x 32	Fused TFE Tape	Fused TFE Tape	260	500	1.3 x 2.2 (0.050 x 0.085)	3 (6)
T Copper - Constantan	20	TFE-T-20	\$450	\$510	Solid	Fused TFE Tape	Fused TFE Tape	260	500	1.5 x 2.5 (0.060 x 0.100)	5 (11)
	20S	TFE-T-20S	570	650	7 x 28	Fused TFE Tape	Fused TFE Tape	260	500	1.5 x 2.7 (0.060 x 0.105)	5 (11)
	24	TFE-T-24	315	350	Solid	Fused TFE Tape	Fused TFE Tape	260	500	1.3 x 1.9 (0.050 x 0.075)	3 (6)
	24S	TFE-T-24S	370	415	7 x 32	Fused TFE Tape	Fused TFE Tape	260	500	1.3 x 2.2 (0.050 x 0.085)	3 (6)
E CHROMEKA® - Constantan	20	TFE-E-20	\$715	\$815	Solid	Fused TFE Tape	Fused TFE Tape	260	500	1.5 x 2.5 (0.060 x 0.100)	5 (11)
	20S	TFE-E-20S	955	1085	7 x 28	Fused TFE Tape	Fused TFE Tape	260	500	1.5 x 2.7 (0.060 x 0.105)	5 (11)
	24	TFE-E-24	510	570	Solid	Fused TFE Tape	Fused TFE Tape	260	500	1.3 x 1.9 (0.050 x 0.075)	3 (6)
	24S	TFE-E-24S	625	700	7 x 32	Fused TFE Tape	Fused TFE Tape	260	500	1.3 x 2.2 (0.050 x 0.085)	3 (6)

* Weight of spool and wire rounded up to the next highest lb.; does not include packing material.

* Spool lengths 25', 50', 100', 200', 500' and 1000'. Other calibrations and lengths available; consult Sales for pricing.

** To order special limits of error wire, add "-SLE" to model number before spool length.

Ordering Example: TFE-J-24-SLE-1000, 1000' (300 m) of Type J Iron-CONSTANTAN special limits of error duplex insulated wire, \$320.

Kapton® Duplex Insulated Thermocouple Wire

Fused Kapton tape applied to conductors and jackets. Excellent moisture and abrasion resistance, high dielectric strength (7 kV/mil), retains much physical integrity after gamma radiation. FEP is used as adhesive binding agent [melts at approx. 260°C (500°F)]



Calibration Color Code†	AWG No.	Model Number	Price/1000*	SLE/1000**	Type Wire	Insulation		Max. Temp		Nominal Size mm (in)	Wt./1000' kg (lb)
						Conductor	Overall	°C	°F		
J Iron - Constantan	20	KK-J-20	\$870	\$990	Solid	Fused Polyimide Tape	Fused Polyimide Tape	316	500	1.5 x 2.5 (0.060 x 0.100)	5 (11)
	20S	KK-J-20S	1110	1270	7 x 28	Fused Polyimide Tape	Fused Polyimide Tape	316	500	1.5 x 2.7 (0.060 x 0.105)	5 (11)
	24	KK-J-24	660	755	Solid	Fused Polyimide Tape	Fused Polyimide Tape	316	500	1.3 x 1.9 (0.050 x 0.075)	3 (6)
	24S	KK-J-24S	825	945	7 x 32	Fused Polyimide Tape	Fused Polyimide Tape	316	500	1.3 x 2.2 (0.050 x 0.085)	3 (6)
	30	KK-J-30	650	750	Solid	Fused Polyimide Tape	Fused Polyimide Tape	316	500	1.0 x 1.4 (0.040 x 0.055)	3 (6)
K CHROMEKA® - ALOMEGA®	20	KK-K-20	\$1010	\$1150	Solid	Fused Polyimide Tape	Fused Polyimide Tape	316	500	1.5 x 2.5 (0.060 x 0.100)	5 (11)
	20S	KK-K-20S	1270	1450	7 x 28	Fused Polyimide Tape	Fused Polyimide Tape	316	500	1.5 x 2.7 (0.060 x 0.105)	5 (11)
	24	KK-K-24	750	850	Solid	Fused Polyimide Tape	Fused Polyimide Tape	316	500	1.3 x 1.9 (0.050 x 0.075)	3 (6)
	24S	KK-K-24S	930	1060	7 x 32	Fused Polyimide Tape	Fused Polyimide Tape	316	500	1.3 x 2.2 (0.050 x 0.085)	3 (6)
	30	KK-K-30	650	750	Solid	Fused Polyimide Tape	Fused Polyimide Tape	316	500	1.0 x 1.4 (0.040 x 0.055)	3 (6)
T Copper - Constantan	20	KK-T-20	\$870	\$990	Solid	Fused Polyimide Tape	Fused Polyimide Tape	316	500	1.5 x 2.5 (0.060 x 0.100)	5 (11)
	20S	KK-T-20S	1110	1270	7 x 28	Fused Polyimide Tape	Fused Polyimide Tape	316	500	1.5 x 2.7 (0.060 x 0.105)	5 (11)
	24	KK-T-24	660	755	Solid	Fused Polyimide Tape	Fused Polyimide Tape	316	500	1.3 x 1.9 (0.050 x 0.075)	3 (6)
	24S	KK-T-24S	825	945	7 x 32	Fused Polyimide Tape	Fused Polyimide Tape	316	500	1.3 x 2.2 (0.050 x 0.085)	3 (6)
	30	KK-T-30	650	750	Solid	Fused Polyimide Tape	Fused Polyimide Tape	316	500	1.0 x 1.4 (0.040 x 0.055)	3 (6)
E CHROMEKA® - Constantan	20	KK-E-20	\$1155	\$1325	Solid	Fused Polyimide Tape	Fused Polyimide Tape	316	500	1.5 x 2.5 (0.060 x 0.100)	5 (11)
	20S	KK-E-20S	1455	1665	7 x 28	Fused Polyimide Tape	Fused Polyimide Tape	316	500	1.5 x 2.7 (0.060 x 0.105)	5 (11)
	24	KK-E-24	865	990	Solid	Fused Polyimide Tape	Fused Polyimide Tape	316	500	1.3 x 1.9 (0.050 x 0.075)	3 (6)
	24S	KK-E-24S	1070	1225	7 x 32	Fused Polyimide Tape	Fused Polyimide Tape	316	500	1.3 x 2.2 (0.050 x 0.085)	3 (6)
	30	KK-E-30	735	850	Solid	Fused Polyimide Tape	Fused Polyimide Tape	316	500	1.0 x 1.4 (0.040 x 0.055)	3 (6)

† Note: Kapton® wire is neither ANSI nor IEC color-coded.

* Spool lengths 25', 50', 100', 200', 500' and 1000'. Other calibrations and lengths available; consult Sales for pricing.

** To order special limits of error wire, add "-SLE" to model number before spool length.

Ordering Example: KK-K-20-SLE-1000, 1000' (300 m) of Type K CHROMEKA®-ALOMEGA® special limits of error duplex insulated wire, \$885.

Note: Published prices are based on market value at time of printing and are subject to change due to Nickel surcharges, Chromium and precious-metal market fluctuations.

OMEGA can cover any insulated wire with metal overbraiding to protect against wear and abrasion. Overbraiding adds durability and electrical shielding for improved performance. See page H-43 for details.



UNITED STATES

www.omega.com
1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca
Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de
Deckenpfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk
Manchester, England
0800-488-488

FRANCE

www.omega.fr
Guyancourt, France
088-466-342

CZECH REPUBLIC

www.omegaeng.cz
Karviná, Czech Republic
596-311-899

BENELUX

www.omega.nl
Amstelveen, NL
0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters