


Flag-Mount Thermistor Sensor



ON-930 Series
Starts at
£29.50



- ✓ Aluminium Housing Provides Rapid Heat Transfer Between the Sensor and Mounting Surface for Accurate Measurements
- ✓ Available in 5 Resistance Values To Fit Your Instrumentation Needs

MOST POPULAR MODEL HIGHLIGHTED!

To Order (Specify Model Number)						
Model Number	Price	Resistance @ 25°C	Interchangeability @ 0 to 70°C	Temperature Rating	Cable Length mm	Cable Termination
ON-930-44004	£29.50	2252	±0.2°C	100°C	300 mm	Stripped
ON-930-44005	29.50	3000	±0.2°C	100°C	300 mm	Stripped
ON-930-44007	29.50	5000	±0.2°C	100°C	300 mm	Stripped
ON-930-44006	29.50	10000	±0.2°C	100°C	300 mm	Stripped
ON-930-44008	29.50	30000	±0.2°C	100°C	300 mm	Stripped
ON-930-44004-1M	30.00	2252	±0.2°C	100°C	1 m	Stripped
ON-930-44005-1M	30.00	3000	±0.2°C	100°C	1 m	Stripped
ON-930-44007-1M	30.00	5000	±0.2°C	100°C	1 m	Stripped
ON-930-44006-1M	30.00	10000	±0.2°C	100°C	1 m	Stripped
ON-930-44008-1M	30.00	30000	±0.2°C	100°C	1 m	Stripped

Notes: For additional cable length, add required length (in metres) to end of the model number and £1.75/m to the price. For a ¼" jack plug, add "-PP" to the model number and £4.70 to the price. For tighter interchangeability, substitute the thermistor part number from the table below and add the price listed to the sensor price.

Ordering Examples: ON-930-44004, flag-mount thermistor sensor with a resistance of 2252 at 25°C and an interchangeability of ±0.2°C, 300 mm of cable, £29.50. ON-930-44034-1M-PP, flag-mount thermistor sensor with a resistance of 5000 at 25°C and an interchangeability of ±0.1°C, 1 m of cable and a ¼" jack plug connector, £30 + 7.40 + 4.70 = £42.10.

Optional Thermistors

Model Number	Additional Price	Resistance @ 25°C ()	Maximum Working Temp	Interchangeability @ 0 to 70°C	Storage and Working Temp for Best Stability
44033	£7.40	2252	75°C	±0.1°C	-80 to 75°C
44030	7.40	3000	75°C	±0.1°C	-80 to 75°C
44034	7.40	5000	75°C	±0.1°C	-80 to 75°C
44031	7.40	10,000	75°C	±0.1°C	-80 to 75°C
44032	7.40	30,000	75°C	±0.1°C	-80 to 75°C

omega.co.uk[®]

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

www.omega.co.uk



UNITED STATES

www.omega.com

1-800-TC-OMEGA

Stamford, CT.

CANADA

www.omega.ca

Laval(Quebec)

1-800-TC-OMEGA

GERMANY

www.omega.de

Deckenpfronn, Germany

0800-8266342

UNITED KINGDOM

www.omega.co.uk

Manchester, England

0800-488-488

FRANCE

www.omega.fr

088-466-342

CZECH REPUBLIC

www.omegaeng.cz

Karviná, Czech Republic

596-311-899

BENELUX

www.omega.nl

0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters