

OMEGAETTE™ Digital Infrared Thermometer

OS-FS



- Adjustable Emissivity
- Easy-to-Use
- Built-In "Lock" Mode
- °C/°F Switchable

The OS-FS is a compact, lightweight, easy-to-use pocket infrared thermometer. Features include adjustable emissivity, °C/°F switchability, and built-in lock mode. It is ideal for quick temperature measurement between -33°C (-27°F) and 220°C (428°F). For best results, operate the OS-FS within 1 to 2 cm (≈0.75") of the target. Distance to spot ratio is approximately 1:1.3. Spot size is approximately 4 mm @ 5 mm and 9 mm @ 11 mm.

Specifications

Measurement Range:
-33 to 220°C (-27 to 428°F)
Operating Temperature:
0 to 40°C (32 to 104°F)

Storage Temperature:
-20 to 50°C (-4 to 122°F)
Accuracy: ±2% or 2°C
(when ambient temperature is between 0 and 40°C)
Time Between Measurements:
<1 second
Scale Selection: Celsius or Fahrenheit, switchable
Activation: Measurement button
Measure Mode: Min/max/lock
Sensor Type: Thermopile
Power Source: CR2032 battery (2 included)
Battery Low Warning:
~¼ battery life remaining
Battery Empty Warning:
Battery is excessively low
Auto Power-Off:
After 15 seconds of idleness
Casing: Plastic
Carrying Case: Metal
Dimensions:
18.0 H x 36.7 W x 67.8 mm L
(0.71 x 1.44 x 2.67")
Weight: 32 g (1.1 oz)

⚠ CAUTION! – This product is not intended for medical use or use on humans

Comes with batteries, wrist strap, metal carrying case and manual.



OS-FS, £33, shown smaller than actual size.

AVAILABLE FOR FAST DELIVERY!

To Order (Specify Model Number)

Model No.	Price	Description
OS-FS	£33	Infrared thermometer

Comes with 2 batteries (1 spare), wrist strap, metal carrying case and manual.

Ordering Example: OS-FS, infrared thermometer, £33.