

Reversible Temperature Indicators

RLC-60 Series Thermometers (Multi Temp Liquid Crystal Strips)

- ✓ Features Wide Range—16 Indicating Levels in 2-Degree Increments (°F)
- ✓ Excellent Visibility and Presentation of Environmental Changes
- ✓ Temperature Square Becomes Highlighted for Indicated Reading

MOST POPULAR MODELS HIGHLIGHTED!

RLC-60-58/88(*)

- ✓ 58 to 88°F/14 to 31°C (2°F increments)
- ✓ Includes corresponding °C scale

Price
pkg of 10 **£870**
pkg of 30 **£24**

RLC-60-26/56(*)

- ✓ 26 to 56°F/-3°C to 13°C (2°F increments)
- ✓ Includes corresponding °C scale

Price
pkg of 10 **£870**
pkg of 30 **£24**

RLC-60-14/31(*)

- ✓ 14 to -31°C/58 to 88°F (16 indicating levels)
- ✓ Includes corresponding °F scale in 2°F increments

Price
pkg of 10 **£870**
pkg of 30 **£24**

RLC-60-3/13(*)

- ✓ -3 to 13°C/26 to 56°F (16 indicating levels)
- ✓ Includes corresponding °F scale in 2°F increments

Price
pkg of 10 **£870**
pkg of 30 **£24**

RLC-60-90/120(*)

- ✓ 90 to 120°F/32 to 49°C (2°F increments)
- ✓ Includes corresponding °C scale

Price
pkg of 10 **£870**
pkg of 30 **£24**

RLC-60-32/49(*)

- ✓ 32 to 49°C/90 to 120°F (16 indicating levels)
- ✓ Includes corresponding °F scale in 2°F increments

Price
pkg of 10 **£870**
pkg of 30 **£24**

* Insert "-10" for package of 10 or "-30" for package of 30.
Ordering Example:
RLC-60-58/88-30,
16 temperature range label,
58 to 88°F (2°F increments),
package of 30, **£24.**

Discount Schedule (Packs)

1 to 9Net
10 to 4910%
50 to 9920%
100 to 49930%
500+Consult Sales

All models shown smaller than actual size.
12.7 W x 127 L x 0.25 mm thick (½ x 5 x 0.01")



UNITED STATES

www.omega.com

1-800-TC-OMEGA

Stamford, CT.

CANADA

www.omega.ca

Laval(Quebec)

1-800-TC-OMEGA

GERMANY

www.omega.de

Deckenpfronn, Germany

0800-8266342

UNITED KINGDOM

www.omega.co.uk

Manchester, England

0800-488-488

FRANCE

www.omega.fr

088-466-342

CZECH REPUBLIC

www.omegaeng.cz

Karviná, Czech Republic

596-311-899

BENELUX

www.omega.nl

0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters