

IN-LINE FLOWMETERS WITH HALF UNION ADAPTORS

FL45100 Series
Starts at

\$274



Optional †

- ✓ Available in In-Line and Panel Mount Styles
- ✓ Models with Optional Protective Shield for Harsh Environments
- ✓ One-Piece Meter Body of Injection-Molded Polysulfone
- ✓ Floats Made of 316 SS, TFE, or Hastelloy C

FL45100 Series flowmeters feature a rugged, one-piece meter body of heat- and chemical-resistant injection-molded polysulfone. A precision-textured light-admitting surface at the rear of the meter body diffuses ambient light and creates a softly illuminated background to enhance readability. These meters are not recommended for applications involving direct sunlight. Additional features include a stainless steel float guide and float, 1 FPT polysulfone adaptors, and FKM O-ring seals. For harsh applications, units may be ordered with Hastelloy® C float guide and float of either Hastelloy or TFE (depending on flow range).

Flowmeters available with optional protective shield (shown) or 90° adaptors for panel mounting (not shown)

FL45103-SH, with protective shield \$417, shown smaller than actual size.

Caution: Polysulfone should not be used in direct sunlight or any other significant sources of ultraviolet light.

MOST POPULAR MODELS HIGHLIGHTED!

To Order (Specify Model Number)					
Model No.	Price	GPM	LPM	Float Material	Connection, NPT
FL45101	\$274	1 to 10	4 to 40	316 SS	1 FNPT
FL45102	288	2 to 20	7.5 to 75	316 SS	1 FNPT
FL45103	314	3 to 30	12 to 115	316 SS	1 FNPT
FL45104	331	4 to 40	15 to 155	316 SS	1 FNPT

Comes complete with operator's manual.

For Hastelloy C float material for harsh environments, add suffix "-HL" to model number and \$275 to price.

For units with protective shield, add suffix "-SH" to model number, consult flow engineering for price.


For units with 90° adaptors for panel mount installations, add suffix "-PM" to model number, consult flow engineering for price. Models with 90° adaptors have a 1 MNPT connection.

† For 5-point NIST calibration, add suffix "-NIST" to model number and \$375 to price.

Ordering Examples: FL45102-HL, meter with 2.0 to 20 GPM, 7.5 to 75 LPM ranges with Hastelloy C float for harsh environments, \$288 + 275 = \$563.

FL45101, water flowmeter, 1 to 10 GPM or 4 to 40 LPM, \$274.

Recommended Reference Book: A Dictionary of Chemistry, CH-5527, \$16. See Section Y for Additional Books



FL45102, \$288, shown smaller than actual size.

omega.co.uk[®]

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

www.omega.co.uk



UNITED STATES

www.omega.com

1-800-TC-OMEGA
Stamford, CT.

UNITED KINGDOM

www.omega.co.uk

Manchester, England
0800-488-488
+44-(0)161-777-6611

CANADA

www.omega.ca

Laval(Quebec)
1-800-TC-OMEGA

FRANCE

www.omega.fr

0800-466-342

GERMANY

www.omega.de

Deckenfronn, Germany
0800-8266342

BENELUX

www.omega.nl

0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485, Ethernet and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters