

CUSTOM-LEVEL SWITCH STARTER KIT

Assemble a Custom-Level Control in Minutes

LVK-120
Starts at
\$256



- Starter Kit is Expandable Up to 6 Level Stations
- Customized for Individual Applications
- Features a Normally Open or Normally Closed SPST 20 VA Switch

To determine fluid specific gravity, add 0.1 to float specific gravity for clean liquids and 0.3 to float specific gravity for dirty or viscous liquids. The LVK-120 Series OMEGA® starter kit can be assembled and installed vertically in your tank in minutes. Each kit contains all the components for complete assembly of a 1- or 2-station level switch for pipe-plug mounting. Additional level stations may be added (see accessories).

SPECIFICATIONS

Temperature Range:

LVK-120: 1 to 82°C (34 to 180°F) in water, 0 to 106°C (0 to 225°F) in oil

LVK-121: 0 to 149°C (0 to 300°F)

Pressure Rating: 150 psi for LVK-120 or 500 psi for LVK-121

Float Diameter:

LVR-120: 47.7 mm (1.8")

LVR-121: 53.3 mm (2.1")

Mounting:

Tube/Fitting Size: 12.7 mm (½") OD tube

Mounting Attitude:

Vertical up to 30°

Lead Wire: 152.4 mm (60"), 20 AWG, insulated

Fittings:

Coated with zinc gold chromate


Max Assembly Length:

Approximately 760 mm (30")



LVK-121, \$530, shown smaller than actual size.

Includes mounting plug, 2 switch/float assemblies, 2 extension tubes, tube end fitting, 3 tube unions, and tube connector.



LVK-121

AVAILABLE FOR FAST DELIVERY!

To Order (Specify Model Number)

Model No.	Price	Stem/Float	Float Specific Gravity
LVK-120	\$256	Brass/Buna	0.45
LVK-121	530	316 SS	0.63

OMEGA® Starter Kit Replacement Parts

Model No.	Price	Description
LVK-125	\$44	Brass/Buna float station
LVK-126	59	316 SS float station
BRK-U-12	27	½" tube union, brass
SSK-U-12	72	½" tube union, 316 SS
BRK-12-10-0	17	½" OD tubing, 12" length, brass
SSK-12-10-0	20	½" OD tubing, 12" length, 316 SS

Accessory

Model No.	Price	Description
CE-1917	\$29	Reference Book: Introduction to Design for Civil Engineers

Comes complete with 1 mounting plug, 2 switch/float assemblies, two 30.5 cm (12") extension tubes, 1 tube end fitting, 3 tube unions, 1 tube connector and operator's manual.

Ordering Examples: LVK-120, brass/Buna level switch kit, \$256.

LVK-121, 316 SS brass/Buna level switch kit, \$530

omega.co.uk[®]

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

www.omega.co.uk



UNITED STATES

www.omega.com

1-800-TC-OMEGA
Stamford, CT.

UNITED KINGDOM

www.omega.co.uk

Manchester, England
0800-488-488
+44-(0)161-777-6611

CANADA

www.omega.ca

Laval(Quebec)
1-800-TC-OMEGA

FRANCE

www.omega.fr

0800-466-342

GERMANY

www.omega.de

Deckenfronn, Germany
0800-8266342

BENELUX

www.omega.nl

0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485, Ethernet and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters