

MANUAL TEST STAND FOR DFG FORCE GAGES

DFG-TS Series

All Models
\$725



Reliable inspection is essential to successful quality control. OMEGA's DFG-TS manual test stand ensures consistent, identical measuring conditions by eliminating human error. In addition, the stand shortens inspection time, thereby greatly increasing work efficiency. DFG60, DFG70, or DFG80 force gages are easily mounted to the test stand. The combination of OMEGA force gages and test stand creates a high-precision, compact load tester for a wide range of applications.

SPECIFICATIONS

Maximum Load: 220 lb

Stroke: 4" max

Maximum Clearance: 5"

Function:


DFG-TS-C: Push

DFG-TS-T: Pull

DFG-TS-T, \$725,
shown smaller
than actual size.



Dimensions: mm (in)



MOST POPULAR MODELS HIGHLIGHTED!

To Order (Specify Model Number)

MODEL	PRICE	FUNCTION
DFG-TS-C	\$725	Push
DFG-TS-T	725	Pull

Comes with operator's manual.

Ordering Example: DFG-TS-T, manual test stand with pull function, \$725.

ACCESSORY

MODEL NO.	PRICE	DESCRIPTION
GE-2103	\$61	Reference Book: Quality Auditor's Handbook

LOAD CELLS
F

omega.co.uk[®]

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

www.omega.co.uk



UNITED STATES

www.omega.com

1-800-TC-OMEGA
Stamford, CT.

UNITED KINGDOM

www.omega.co.uk

Manchester, England
0800-488-488
+44-(0)161-777-6611

CANADA

www.omega.ca

Laval(Quebec)
1-800-TC-OMEGA

FRANCE

www.omega.fr

0800-466-342

GERMANY

www.omega.de

Deckenfronn, Germany
0800-8266342

BENELUX

www.omega.nl

0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485, Ethernet and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters