

# ELECTRICAL HOUSING

## with Terminal Strip

LVCN-11, \$60, shown larger than actual size.

LVCN-12  
**\$50**



The housing swivels on its base, allowing easy alignment for conduit installation. The housing is made of rugged reinforced polypropylene and meets NEMA 4X (IP65) ratings. The LVCN-12 compact version provides termination for up to 2 sensors.

- ✔ Mounts Directly to a Single Sensor or OMEGA's Sensor Track System
- ✔ NEMA 4X (IP65) Rated Enclosure
- ✔ Rugged Reinforced Plastic Body
- ✔ Best Choice for Easy Conduit Termination
- ✔ Provides Termination for Up to Four Sensors
- ✔ Swivel Mounting Base Allows Easy Conduit Alignment

This durable electrical housing conveniently mounts on top of an OMEGA® sensor or on OMEGA's sensor track system. It provides termination for up to four sensors.

### SPECIFICATIONS

**Rating:** NEMA 4X (IP65)

**Terminal Strip:**

Socket terminals self bridging

**Conduit Connection:** ½" NPT

**Material:** PP, flame retardant

**Dimensions:** 8.9 H x 7.1 cm Dia.

(3.5 x 2.8) x ¾" NPT (LVCN-12);

11.4 x 7.1 cm (4.5 x 2.8) x ¾" NPT (LVCN-11)

**MOST POPULAR MODEL HIGHLIGHTED!**

### To Order (Specify Model No.)

Model No.	Price	Description	Mat'l	Size
LVCN-11	\$60	Electrical housing with terminal strip (4 sensors)	PP	2.8 x 4.5 x ¾" NPT
LVCN-12	50	Electrical housing with terminal strip (2 sensors)	PP	2.8 x 3.5 x ¾" NPT

Comes with complete operator's manual.

**Ordering Examples:** LVCN-11 electrical housing with terminal strip for four sensors, \$60. LVCN-12 electrical housing with terminal strip for two sensors, \$50.

### Accessory

Model No.	Price	Description
CM-1200	\$210	Reference Book: Handbook of Chlorination and Alternative Disinfectants



# omega.co.uk<sup>®</sup>

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

[www.omega.co.uk](http://www.omega.co.uk)



#### UNITED STATES

[www.omega.com](http://www.omega.com)

1-800-TC-OMEGA  
Stamford, CT.

#### UNITED KINGDOM

[www.omega.co.uk](http://www.omega.co.uk)

Manchester, England  
0800-488-488  
+44-(0)161-777-6611

#### CANADA

[www.omega.ca](http://www.omega.ca)

Laval(Quebec)  
1-800-TC-OMEGA

#### FRANCE

[www.omega.fr](http://www.omega.fr)

0800-466-342

#### GERMANY

[www.omega.de](http://www.omega.de)

Deckenfronn, Germany  
0800-8266342

#### BENELUX

[www.omega.nl](http://www.omega.nl)

0800-099-33-44



## More than 100,000 Products Available!

### • Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

### • Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

### • pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

### • Data Acquisition

Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485, Ethernet and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

### • Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

### • Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters