

search by: Part Number All Omega

Electronic Distance Measurement Tool

HH-DM



\$ 75.00 HH-DM

- 0.9 to 9m(3 to 30ft.) Range
- Measures in Meters or Feet Switchable Via Keypad
- Highly Accurate
- Mounts Directly on OMEGA's OS530 Series Infrared Pyrometer

[View related products - Infrared Temperature Measurement Instruments](#)

Click for [larger image](#).



The HH-DM electronic distance measurement tool sends out narrow beams of sound waves that "bounce" off solid objects back to the hand-held receiver. Custom electronics and a microprocessor then convert elapsed time into a distance measurement and display it on the LCD.

The HH-DM is the perfect accessory for OMEGA's OS530 infrared pyrometer. The HH-DM mounts directly on top of the HH-DM to provide one complete solution for non-contact temperature and distance measurement. (See the related links section below for more details on the OS530 infrared pyrometer).

- Specifications Range:** 0.9 to 9 m (3 to 30')
- Accuracy:** 0.5% of Rdg or 1.3 cm (0.5"), whichever is greater
- Unit of Measurement:** Meter or feet, switchable via keypad
- Power:** 9V Alkaline (included)
- Sensor:** Ultrasonic transducer
- Dimensions:** 130 L x 70 W x 28.5 mm H (5 1/8 L x 2 3/4 W x 1 1/8" H)

To Order (Specify Model Number)					<input type="button" value="Add to Cart"/>
Part Number	Availability	Price	Description	RoHS	Qty.
HH-DM	In Stock	\$75.00	Electronic Distance Measurement Tool	✓	0
					<input type="button" value="Add to Cart"/>

† All dollar amounts on this site are shown in US currency.

Ordering Example: (1) **HH-DM** Electronic distance measurement tool = **\$75.00**

Related Links - Related Products

Related Products

[OS530L, OS531, OS530HR, OS532, OS533, OS534](#): OMEGASCOPE® Handheld Infrared Thermometer

Keywords: Electronic Distance Measurement Tool, Distance Measuring Device

[Back to top](#) ^



omega.co.uk[®]

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

www.omega.co.uk



UNITED STATES

www.omega.com

1-800-TC-OMEGA
Stamford, CT.

UNITED KINGDOM

www.omega.co.uk

Manchester, England
0800-488-488
+44-(0)161-777-6611

CANADA

www.omega.ca

Laval(Quebec)
1-800-TC-OMEGA

FRANCE

www.omega.fr

0800-466-342

GERMANY

www.omega.de

Deckenfronn, Germany
0800-8266342

BENELUX

www.omega.nl

0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485, Ethernet and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters