

PORTABLE PRESSURE CALIBRATORS WITH INTERNAL PRESSURE SOURCE



A

PRESSURE INSTRUMENTS

PCL-5000 Series 20 to 2000 psi

PCL-5000C, \$7995, shown smaller than actual size.

All Models
\$7995



offers 5 independent selectable ranges. Designed for field use, this rugged calibrator weighs less than 25 lb and has its own built-in pressure and vacuum source. For immediate on-site use, it comes with with hose and couplings. Its internal microcircuitry automatically maintains zero and span calibration data to ensure long-term stability and accuracy. A pressure limit control provides overpressure protection.



- ✓ 0.05% FS Accuracy
- ✓ Gage and Absolute Pressure Ranges
- ✓ Portable and Lightweight
- ✓ NIST Certificate Provided
- ✓ Hoses, Fittings, Connectors Included
- ✓ Voltage/Current Display Mode for Transducer Testing
- ✓ Overpressure Protection

For rapid on-site calibration of transducers, transmitters, gages, and many other pressure-sensitive devices, OMEGA® PCL-5000 Series portable pressure calibrators provide high accuracy, reliability, and pushbutton operation. OMEGA's PCL-5000 covers the higher pressure ranges (20 to 2000 psi) with a self-contained 2000 psi nitrogen cylinder. Its pressure modes—gage or absolute—are switch selectable. An extremely accurate instrument ($\pm 0.05\%$ FS), the PCL-5000 comes with quick-disconnect fittings and hoses for input and output pressure.

The PCL-5100, a low-pressure unit with ranges from 30 inHg to 100 psi,



K-79 pocket thermometer is included at no extra charge. To order extra pocket thermometers visit omega.com

PORTABLE PRESSURE CALIBRATORS

0.05% ACCURACY, 30 inH₂O to 2000 psi

RECHARGEABLE BATTERIES—STANDARD



Hoses and couplings included.

PCL-5100C, \$7995, shown smaller than actual size.

SPECIFICATIONS

Overall Accuracy: ±0.05% FS max; accuracy statement includes all effects of linearity, hysteresis, repeatability and ambient temperature

Operating Temperature: 5 to 43°C (41 to 109°F)

Internal Pressure Cylinder:

Capacity: 9.0 standard cubic feet

Volume: 80 cubic inches

Rating: 2015 psi

Overpressure Rupture Disk Rating: 3000 psig, nominal

Pressure Media Filter:

Rating: 7 microns, nominal

Type: Field-replaceable filter cartridge

Control Valves: Micrometering with positive shut-off, adjustable stop and replaceable seat; non-destructible.

Fill and Test Ports:

Rating: 3000 psig, min (connected or disconnected)

Type: Quick-disconnect

Pressure Hoses: 2 (1 input, 1 output) 1.5 m (5'), nominal each

Built-In Carrying Case: Rugged aluminum case with sealed cover and carrying handle

Weight: 11 kg (24 lb) (including all hoses and cables)

Dimensions: 250 W x 410 L x 290 mm D (10 x 16 x 11.5")

MOST POPULAR MODEL HIGHLIGHTED!

To Order Complete Kit (Specify Model Number)

MODEL NO.	PRICE	TYPE	RANGES	RESOLUTION
PCL-5000A	\$7995	psig and psia	2000/1000/400	0.5/0.2/0.05
PCL-5000B	7995	psig and psia	1000/500/200	0.2/0.1/0.05
PCL-5000C	7995	psig and psia	500/250/100	0.1/0.05/0.002
PCL-5000D	7995	psig	100/50/20	0.02/0.01/0.005
PCL-5000DB	7995	psia	100/50/20	0.02/0.01/0.005
PCL-5100	7995	5 ranges: ±30 inHg to 100 psi		0.5/0.1/0.01

Come complete with hoses, couplings, K-79 pocket thermometer, and operator's manual.

Ordering Examples: PCL-5000D-2, 100/50/20 psig range calibrator with second scale option, \$7995 + 200 = \$8195.

PCL-5100, 5 range, ±30 inHg to 100 psi calibrator, \$7995.

OPTION

SUFFIX	PRICE	DESCRIPTION
-2	\$200	Second scale on PCL-5000D and DB inH ₂ O

ACCESSORY

MODEL NO.	PRICE	DESCRIPTION
CM-4339	\$135	Reference Book: Flow Measurement Methods



omega.co.uk[®]

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

www.omega.co.uk



UNITED STATES

www.omega.com

1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca

Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de

Deckenfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk

Manchester, England
0800-488-488
+44-(0)161-777-6611

FRANCE

www.omega.fr

0800-466-342

BENELUX

www.omega.nl

0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485, Ethernet and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters