



INDUCTIVE PROXIMITY SENSORS

SMALL DIAMETER—5 AND 8 mm

E57 Series Starts at £39

- Small 5 and 8 mm Diameters for Use in Applications with Limited Space for Mounting Sensors
- Stainless Steel or Ni-Brass Housings
- All Models Include an LED Indicator to Show Output Status
- Short Circuit and Reverse Polarity Protection
- Rated IP67, NEMA 4, 4X, 6, 6P, 12 and 13 for High Resistance to Environmental Factors

Applications


- Automation Equipment
- Robotics
- Machine Tool
- Counting
- Sorting

These unique Cutler-Hammer® Inductive Proximity Sensors are designed to be used in extremely small spaces. A wide variety of models are available with housing diameters of 8 mm and a very small 5 mm, allowing you to choose the one that best fits your application. The sensors are 3-wire devices that operate from 10 to 30 Vdc. Both shielded and unshielded versions are available.

SPECIFICATIONS

Operating Voltage: 10 to 30 Vdc
Maximum Load Current: 200 mA
Switching Frequency: 2 kHz
Leakage Current: 0.01 mA maximum
Voltage Drop: 1.5V maximum
Burden Current: 10 mA maximum
Protection Transient: Power on false pulse suppression, auto-reset short circuit

Manufactured by Cutler-Hammer for OMEGA




Dimensions: mm

DIA A	LENGTH B	C	D	THREAD E	NUT WIDTH F	CONNECTOR DIA G	LED LOCATION
5 mm	25	—	21	M5 x 1	SW8	—	L1
8 mm cable	30	—	30	M8 x 1	SW13	—	L2
8 mm micro-con.	50	40	25	M8 x 1	SW13	1.2	L2

Switching Hysteresis: <15% rated sensing distance
Repeat Accuracy: <1% sensing distance
Time Delay Before Availability: <50 mS
Output Indicator LED: Lights when output is ON
Operating Temperature: -25 to 70°C

Enclosure Ratings: IP67, NEMA 4, 4X, 6, 6P, 12 and 13
Housing Material: Stainless steel or Ni plated brass
Cable: PVC high flex, oil/water resistant, 22 AWG



E57EAL5T110SP, £56, shown larger than actual size.

E57-08GS01-CDB, £40, shown larger than actual size.

Wiring Diagrams (Pin Numbers Are for Reference, Rely on Pin Location When Wiring)

OPERATING VOLTAGE 3-WIRE SENSORS	OUTPUT	CABLE MODELS	MICRO CONNECTOR MODELS (FACE VIEW MALE SHOWN)
10 to 30 Vdc	NO (NPN)		
	NO (PNP)		

To Order (Specify Model Number)

AVAILABLE FOR FAST DELIVERY!

TYPE	MODEL NO.	PRICE	OPERATING VOLTAGE	SENSING RANGE mm	SHIELDING	CONNECTION TYPE metre
5 mm Dia. End Sensing NO Output SS Case	E57EAL5T110SP	£56.00	10 to 30 Vdc	0.8	Shielded NPN	2 cable
	E57EAL5T111SP	56.00			Shielded PNP	
8 mm Dia. End Sensing NO Output Ni-Brass Case	E57-08GS01-C	39.00	10 to 30 Vdc	1	Shielded NPN	2 cable
	E57-08GS01-CDB	40.00			Shielded PNP	4-pin micro DC connector
	E57-08GS01-G	39.00			Shielded PNP	2 cable
	E57-08GS01-GDB	40.00				4-pin micro DC connector
	E57-08GU02-C	39.00		2	Unshielded NPN	2 cable
	E57-08GU02-CDB	42.00				4-pin micro DC connector
	E57-08GU02-G	39.00			Unshielded PNP	2 cable
	E57-08GU02-GDB	42.00				4-pin micro DC connector
	E57-08GE03-C	45.50		3 Extended Range	Shielded NPN	2 cable
	E57-08GE03-CDB	47.50				4-pin micro DC connector
	E57-08GE03-G	45.50			Shielded PNP	2 cable
	E57-08GE03-GDB	47.50				4-pin micro DC connector

Ordering Example: E57EAL5T110SP, 5 mm diameter prox, shielded, NPN output, 2 m cable, £56. E57-08GU02-C, 8 mm unshielded NPN output with 2 m cable, £39.

Accessories

MODEL NO.	PRICE	DESCRIPTION
CSDS4A4CY2202	£10.75	DC cable, 4-pin, 22 AWG, 2 m PVC jacket
E57KM8	4.70	Bracket for 8 mm tubular sensors



UNITED STATES

www.omega.com

1-800-TC-OMEGA

Stamford, CT.

CANADA

www.omega.ca

Laval(Quebec)

1-800-TC-OMEGA

GERMANY

www.omega.de

Deckenpfronn, Germany

0800-8266342

UNITED KINGDOM

www.omega.co.uk

Manchester, England

0800-488-488

FRANCE

www.omega.fr

088-466-342

CZECH REPUBLIC

www.omegaeng.cz

Karviná, Czech Republic

596-311-899

BENELUX

www.omega.nl

0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters