

SENSORLESS VECTOR ADJUSTABLE FREQUENCY AC DRIVES



**MVX9000
Series
Starts at
\$360**



- Sensorless Vector Control with Auto Tuning
- Easy to Understand Keypad
- PID Control of a Process Variable Such as Pressure, Flow, Temperature, Liquid Level, etc.
- Built-In Dynamic Braking Chopper
- RS485 Serial Communication Port
- Single-Phase or 3-Phase Input Capability on 240 Vac Rated Units, 3 hp and Below

The Cutler-Hammer® MVX9000 Series sensorless vector adjustable frequency AC Drives from Eaton's electrical business are designed to provide adjustable speed control of 3-phase motors. These microprocessor-based, sensorless vector drives have standard features that can be programmed to tailor the drive's performance to suit a wide variety of application requirements. The MVX9000 sensorless vector series utilizes a 32-bit microprocessor and insulated gate bipolar transistor (IGBTs) which provides quiet motor operation, high motor efficiency and smooth low speed performance. The size and simplicity of the MVX9000 Series makes it ideal for hassle free installation where size is a primary concern. Models rated at 480V, 3-phase, 50/60 Hz are available in sizes ranging from 1 to 10 hp. Models rated at 240V, single- or 3-phase, 50/60 Hz are available in sizes ranging from 0.5 to 7½ hp. Models rated at 115V, single-phase, 50/60 Hz are available in the ¼ to 1 hp size range. The standard drive includes a digital



MVX005A0-2, \$735, shown smaller than actual size.

MVXF25A0-1, \$360, shown smaller than actual size.

DESCRIPTION HORSEPOWER	VOLTS	DIMENSIONS IN MM (IN)			SHIPPING WEIGHT KG (LBS)
		WIDTH	HEIGHT	DEPTH	
¼ to 1	100 - 120	100 (3.9)	151 (5.9)	145 (5.7)	2.8 (6.2)
½ to 2	200 - 240	100 (3.9)	151 (5.9)	145 (5.7)	2.8 (6.2)
3 to 7½	200 - 240	125 (4.9)	220 (8.6)	193 (7.6)	5.5 (12.1)
1 to 3	380 - 480	100 (3.9)	151 (5.9)	145 (5.7)	2.8 (6.2)
5 to 10	380 - 480	125 (4.9)	220 (8.6)	193 (7.6)	5.5 (12.1)

display, operating and programming keys on a removable keypad. The display provides drive monitoring as well as adjustment and diagnostic information. The keys are utilized for digital adjustment and programming of the drive and for operator control. Separate terminal blocks for control and power wiring are provided for customer connections. Other features provided as standard include built-in DC braking, RS485 serial communications and PID control.

SPECIFICATIONS

OUTPUT RATINGS

Horsepower: 90 to 132V, ¼ to 1 hp
200 to 240V: ½ to 7½ hp
380 to 480V: 1 to 10 hp
425 to 660V: 1 to 10 hp
Frequency Range: 0.1 to 400 Hz

Overload Rating: 150% for 60 sec

Frequency Resolution:

Digital: 0.1 Hz

Analog: Max (set frequency/1000) Hz

Frequency Accuracy:

Digital: ±0.01% of max frequency

Analog: ±0.2% of max frequency

Undervoltage Carryover Limit:

0.3 to 25 sec

MOTOR PERFORMANCE

Motor Control: Sensorless vector

Constant and Variable Torque: Standard

Speed Regulation: 0.5% of base speed

INPUT POWER

Voltage: 50/60 Hz ±3 Hz

100 to 120V: -10% +10%/1-phase

200 to 240V: -10% +5%/1-phase

200 to 240V: -10% +5%/3-phase

380 to 480V: -10% +10%/3-phase

500 to 600V: -15% +10%/3-phase



Displacement Power Factor:

Better than 0.95

Efficiency: Typically greater than 95%

DESIGN TYPE

Microprocessor: 32-Bit

Converter Type: Diode

Inverter Type: Insulated gate bipolar transistor

Waveform: Sensorless vector

ENVIRONMENT

Operating Temperature: -10 to 50°C (14 to 122°F), -10 to 40°C (14 to 104°F); above 7½ hp)

Humidity: 20 to 90%, non-condensing

Max Elevation: 1000 m (3281')

Codes and Standards: NEMA, IEEE, NEC, design standards, UL Listed, cUL listed, CE marked (requires EMI filter)

Enclosure: Standard, protected chassis (IP20)

PROTECTIVE FEATURES

Ground Fault: Standard

Overload Protection: Standard

Overcurrent: Standard

Overvoltage: Standard

Undervoltage: Standard

Overtemperature: Standard

Overload Limit: Standard

SET UP ADJUSTMENTS, PERFORMANCE FEATURES, OPERATOR CONTROL AND EXTERNAL INTERFACE KEYPAD

Alphanumeric Display: Standard, 1 x 4 character

Digital Indications: Frequency (Hz), Motor Current (amps), User-Defined RUN/STOP, FORWARD/REVERSE and parameters

Diagnostics: Last 3 trips with cause
LED Status Indicators: 8; RUN/STOP, FORWARD/REVERSE, Hz, amps, user defined, and input speed

Operator Functions: START/STOP, speed control (digital or potentiometer), RESET, SETUP keys and ENTER

I/O TERMINAL BLOCK

Analog Inputs: 2 Inputs; 0 to 10 Vdc, 4 to 20 mA

Potentiometer: 1 to 2 KΩ

Analog Voltage: Nominal 10 Vdc, 10K Ω input impedance

Analog Current: Nominal 4 to 20 mA, 250 Ω

Digital Inputs: 6 programmable inputs

Digital Outputs: 1 programmable open collector and 1 form C relay contact

Analog Monitor Output: Analog meter; frequency or output current dynamic brake chopper

PROGRAMMABLE PARAMETERS

Out of the Box: Factory settings loaded for quick start-up

Accel. and Decel.: 2 separately adjustable linear or S curve times; 0.1 to 3000 sec

Auto Restart: Overcurrent, overvoltage and undervoltage with 4 selectable retry restart modes

DC Injection Braking:

External Fault: Terminal input

Jog: Terminal input

Fault Reset: STOP/RESET or terminal input

I/O: NO/NC Selectable

Jump Frequencies: 3; with adjustable width

Parameter Security: Programmable software lock

Preset Speeds: 7 preset speeds

PID Controller: PID process control

Reversing: Keypad or terminal

Speed Setting: Keypad, terminal or pot

START/STOP Control: Keypad or terminal

Stop Modes: Decel, coast or DC injection

RELIABILITY

Pretested Components: Standard

Surface Mount Technology:

Standard (PCBs) Computerized

Testing: Standard

Final Test with Full Load: Standard

Eaton's Cutler-Hammer Engineering Systems and Service: National network of AF drive specialists

To Order (Specify Model Number)

MOST POPULAR MODELS HIGHLIGHTED!

MODEL NO.	PRICE	DESCRIPTION	INPUT AMP. SINGLE/ 3 PH RATING	CONT. OUTPUT AMP RATING	WATT LOSS AT 9 KHZ
115 VOLT					
MVXF25A0-1	\$360	0.25 hp AC drive, 1 ph input, 230V, 3 ph output	6.3/*	1.6	20.0
MVXF50A0-1	390	0.5 hp AC drive, 1 ph input, 230V, 3 ph output	9.0/*	2.5	20.0
230 VOLT					
MXVF50A0-2	\$378	0.5 hp AC drive, 1 ph/3 ph input, 3 ph output	6.3/2.9	2.5	20.0
MXV001A0-2	420	1 hp AC drive, 1 ph/3 ph input, 3 ph output	11.5/6.3	5.0	38.0
MXV002A0-2	540	2 hp AC drive, 1 ph/3 ph input, 3 ph output	15.7/8.8	7.0	75.0
MXV003A0-2	630	3 hp AC drive, 1 ph/3 ph input, 3 ph output	27.5/12.5	10	110
MXV005A0-2	735	5 hp AC drive, 3 ph input, 3 ph output	*/19.6	17.0	185.0
MXV007A0-2	1200	7.5 hp AC drive, 3 ph input, 3 ph output	*/31.5	25.0	275.0
460 VOLT					
MXV001A0-4	\$550	1 hp AC drive, 3 ph input 460V, 3 ph output	*/4.2	3.0	38.0
MXV002A0-4	580	2 hp AC drive, 3 ph input 460V, 3 ph output	*/5.7	4.0	75.0
MXV003A0-4	735	3 hp AC drive, 3 ph input 460V, 3 ph output	*/7.0	5.0	110.0
MXV005A0-4	855	5 hp AC drive, 3 ph input 460V, 3 ph output	*/10.5	8.2	185.0
MXV007A0-4	1305	7.5 hp AC drive, 3 ph input 460V, 3 ph output	*/14.0	13.0	275.0
MXV010A0-4	1640	10 hp AC drive, 3 ph input 460V, 3 ph output	*/20.6	18.0	375.0

Comes complete with operator's manual.

* Not applicable.

Horsepower ratings are based on the use of a 240 or 480V NEMA B, 4- or 6-pole squirrel cage induction motor and are for reference only. Units are to be selected such that the motor current is less than or equal to the MVX9000 rated continuous output current.

For 208V, 380V or 415V applications, select the unit such that the motor current is less than or equal to the MVX9000 rated continuous output current.

Ordering Examples: MVXF25A0-1, 0.25 hp AC drive, 115V 1 ph input, 230V 3 ph output, \$360. MVX003A0-2, 3 hp AC drive, 230V 1 ph/3 ph input, 230V 3 ph output, \$630.

omega.co.uk[®]

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

www.omega.co.uk



UNITED STATES

www.omega.com

1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca

Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de

Deckenfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk

Manchester, England
0800-488-488
+44-(0)161-777-6611

FRANCE

www.omega.fr

0800-466-342

BENELUX

www.omega.nl

0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485, Ethernet and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters