



1/16, 1/8, AND 1/4 DIN TEMPERATURE/PROCESS CONTROLLERS

WITH FUZZY LOGIC

CN4000 Series
Starts at
\$69



Visit
omega.com
for our complete
line of
controllers

CN4116-R1-R2, \$69.



CN418H-R1-R2, \$79.



CN418V-R1-R2, \$79.



CN414-R1-R2, \$99.



- Dual Display
- Single Control Output
- Fuzzy Logic
- Autotune
- Dual 4-Digit LED Display and Indicators for Output and Alarm Status
- Single Alarm Output
- Universal Power Supply
- Isolated Analog Control Output (Selected Models)
- 10 Segments of Ramp/Soak (Selected Models)

The CN4000 Series temperature/process controllers set a new standard for ease-of-use and value. Units feature dedicated input models with thermocouple and RTD inputs, and models with universal inputs for both temperature and process inputs. Standard features include autotune, fuzzy logic, fully adjustable PID or on/off single control output with one alarm. Selected thermocouple and RTD input models can show whole or tenth of degree display resolution. Output types include relay, dc pulse, or an isolated analog 0 to 20 mA output.

All models shown smaller than actual size.

SPECIFICATIONS

Selectable Inputs: Thermocouple, RTD, DC voltage, DC current, resistance (dependent on model)

Display: Two 4-digit, 7 segment, LED (red PV, green SV)

Resolution: 1.0, 0.1 (dependent on model)

Accuracy: ±0.3% FS (thermocouple and RTD dedicated models), ±0.2% FS (universal input models)

Supply Voltage: 100 to 240 Vac (-15%, +10%); 50 to 60Hz or Optional 24 Vdc

Power Consumption: 3 W (thermocouple and RTD dedicated models), 6 W (universal input models)

Operating Temperature: -10 to 60°C (14 to 140°F)

Humidity: 0 to 90 RH%

Control Output Ratings:

Relay: SPDT, 30 Vdc/1A, 250 Vac/1A (1/8 and 1/4 DIN models)

Relay: SPST, 30 Vdc/1A, 250 Vac/1A (1/8 DIN models)

Proportional Current (Isolated): 0 to 20 mA DC,

DC Pulse: 12 Vdc/30 mA

Alarm Output Ratings:

Relay: SPDT, 30 Vdc/1A, 250 Vac/1A

DC Pulse: 12 Vdc/30 mA

Universal Input Models

	K	S	R	E	J	N
T/C	0 to 1300°C 32 to 2372°F	0 to 1700°C 32 to 3092°F	0 to 1700°C 32 to 3092°F	0 to 1000°C 32 to 1832°F	0 to 1200°C 32 to 2192°F	0 to 1300°C 32 to 2372°F
RTD	PT100	Cu50				
	-200 to 800°C -328 to 1472°F	-50 to 150°C -58 to 302°F				
Current	0 to 20 mA	4 to 20 mA				
Voltage	0 to 20 mV 1 to 5 V	0 to 100 mV 0 to 5 V	0 to 60 mV 0 to 10 V	0 to 500 mV 2 to 10 V	100 to 500 mV 0 to 20 V	
Resistor	0 to 80 Ω	0 to 400 Ω				

Inputs

Dedicated Thermocouple/RTD Models

Input Type	THERMOCOUPLE						RTD
	K	S	R	E	J	N	PT100
Range	0 to 1300°C (32 to 2372°F)	0 to 1700°C (32 to 3092°F)	0 to 1600°C (32 to 2412°F)	0 to 1000°C (32 to 1832°F)	0 to 1200°C (32 to 2192°F)	0 to 1300°C (32 to 2372°F)	-200 to 800°C (-328 to 1472°F)

Dimensions

SIZE	FRONT PANEL W x H mm (in)	CUT OUT W x H mm (in)	DEPTH BEHIND MOUNTING SURFACE mm (in)
1/6 DIN	48 x 48 (1.89 x 1.89)	45 x 45 (1.77 x 1.77)	95 (3.74)
1/6 DIN Vertical	48 x 96 (1.89 x 3.77)	45 x 92 (1.77 x 3.62)	100 (3.94)
1/6 DIN Horizontal	96 x 48 (3.77 x 1.89)	92 x 45 (3.62 x 1.77)	100 (3.94)
1/4 DIN	96 x 6 (3.77 x 0.23)	92 x 92 (3.62 x 3.62)	100 (3.94)

To Order *(Specify Model Number)*

MOST POPULAR MODELS HIGHLIGHTED!

MODEL NO.	PRICE	DESCRIPTION	INPUT TYPE/RESOLUTION
1/6 DIN MODELS (SINGLE CONTROL OUTPUT WITH ONE ALARM)			
CN4116-R1-R2	\$69	Relay/relay	T/C, RTD/1.0
CN4116-R1-R2-LV	75	Relay/relay, low voltage	T/C, RTD/1.0
CN4116-DC1-R2	69	DC pulse/relay	T/C, RTD/1.0
CN4116-DC1-DC2	69	DC pulse/DC pulse	T/C, RTD/1.0
CN4216-R1-R2	69	Relay/relay	T/C, RTD/0.1
CN4216-R1-R2-LV	75	Relay/relay, low voltage	T/C, RTD/0.1
CN4216-DC1-R2	69	DC pulse/relay	T/C, RTD/0.1
CN4216-DC1-DC2	69	DC pulse/DC pulse	T/C, RTD/0.1
CN4316-R1-R2	69	Relay/relay	Universal/0.1
CN4316-R1-R2-LV	75	Relay/relay, low voltage	Universal/0.1
CN4316-DC1-R2	69	DC pulse/relay	Universal/0.1
CN4316-DC1-DC2	69	DC pulse/DC pulse	Universal/0.1
CN4316-F1-R2	69	0 to 20 mA/relay	Universal/0.1
CN4416-R1-R2	128	Ramp and soak, relay/relay	Universal/0.1
CN4416-R1-R2-LV	134	Ramp and soak, relay/relay, low voltage	Universal/0.1
CN4416-DC1-R2	127	Ramp and soak, DC pulse/relay	Universal/0.1
CN4416-DC1-DC2	126	Ramp and soak, DC pulse/DC pulse	Universal/0.1
CN4416-F1-R2	134	Ramp and soak, 0 to 20 mA/relay	Universal/0.1
1/6 DIN HORIZONTAL MODELS (SINGLE CONTROL OUTPUT WITH ONE ALARM)			
CN418H-R1-R2	\$79	Relay/relay	T/C, RTD/1.0
CN418H-R1-R2-LV	85	Relay/relay, low voltage	T/C, RTD/1.0
CN418H-DC1-R2	79	DC pulse/relay	T/C, RTD/1.0
CN418H-DC1-DC2	79	DC pulse/DC pulse	T/C, RTD/1.0
CN428H-R1-R2	79	Relay/relay	T/C, RTD/0.1
CN428H-R1-R2-LV	85	Relay/relay, low voltage	T/C, RTD/0.1
CN428H-DC1-R2	79	DC pulse/relay	T/C, RTD/0.1
CN428H-DC1-DC2	79	DC pulse/DC pulse	T/C, RTD/0.1
CN438H-R1-R2	79	Relay/relay	Universal/0.1
CN438H-R1-R2-LV	85	Relay/relay, low voltage	Universal/0.1
CN438H-DC1-R2	79	DC pulse/relay	Universal/0.1
CN438H-DC1-DC2	79	DC pulse/DC pulse	Universal/0.1
CN438H-F1-R2	79	0 to 20 mA/relay	Universal/0.1
CN448H-R1-R2	133	Ramp and soak, relay/relay	Universal/0.1
CN448H-R1-R2-LV	139	Ramp and soak, relay/relay, low voltage	Universal/0.1
CN448H-DC1-R2	132	Ramp and soak, DC pulse/relay	Universal/0.1
CN448H-DC1-DC2	131	Ramp and soak, DC pulse/DC pulse	Universal/0.1
CN448H-F1-R2	139	Ramp and soak, 0 to 20 mA/relay	Universal/0.1

Comes complete with operator's manual.

Ordering Example: CN4116-R1-R2-LV, 1/6 DIN universal input controller, single control relay output with one alarm relay, ramp and soak, low voltage, and operator's manual, \$75. CN428H-DC1-R2, 1/6 DIN horizontal universal input controller, single DC pulse control output with one alarm relay, low voltage, \$79.



1/16, 1/8, AND 1/4 DIN TEMPERATURE/PROCESS CONTROLLERS WITH FUZZY LOGIC

To Order (Specify Model Number)

MOST POPULAR MODELS HIGHLIGHTED!

MODEL NO.	PRICE	DESCRIPTION	INPUT TYPE/RESOLUTION
1/8 DIN VERTICAL MODELS (SINGLE CONTROL OUTPUT WITH ONE ALARM)			
CN418V-R1-R2	\$79	Relay/relay	T/C, RTD/1.0
CN418V-R1-R2-LV	85	Relay/relay, low voltage	T/C, RTD/1.0
CN418V-DC1-R2	79	DC pulse/relay	T/C, RTD/1.0
CN418V-DC1-DC2	79	DC pulse/DC pulse	T/C, RTD/1.0
CN428V-R1-R2	79	Relay/relay	T/C, RTD/0.1
CN428V-R1-R2-LV	85	Relay/relay, low voltage	T/C, RTD/0.1
CN428V-DC1-R2	79	DC pulse/relay	T/C, RTD/0.1
CN428V-DC1-DC2	79	DC pulse/DC pulse	T/C, RTD/0.1
CN438V-R1-R2	79	Relay/relay	Universal/0.1
CN438V-R1-R2-LV	85	Relay/relay, low voltage	Universal/0.1
CN438V-DC1-R2	79	DC pulse/relay	Universal/0.1
CN438V-DC1-DC2	79	DC pulse/DC pulse	Universal/0.1
CN438V-F1-R2	79	0 to 20 mA/relay	Universal/0.1
CN448V-R1-R2	133	Ramp and soak, relay/relay	Universal/0.1
CN448V-R1-R2-LV	139	Ramp and soak, relay/relay, low voltage	Universal/0.1
CN448V-DC1-R2	132	Ramp and soak, DC pulse/relay	Universal/0.1
CN448V-DC1-DC2	131	Ramp and soak, DC pulse/DC pulse	Universal/0.1
CN448V-F1-R2	139	Ramp and soak, 0 to 20 mA/relay	Universal/0.1
1/4 DIN MODELS (SINGLE CONTROL OUTPUT WITH ONE ALARM)			
CN414-R1-R2	\$99	Relay/relay	T/C, RTD/1.0
CN414-R1-R2-LV	105	Relay/relay, low voltage	T/C, RTD/1.0
CN414-DC1-R2	99	DC pulse/relay	T/C, RTD/1.0
CN414-DC1-DC2	99	DC pulse/DC pulse	T/C, RTD/1.0
CN424-R1-R2	99	Relay/relay	T/C, RTD/0.1
CN424-R1-R2-LV	99	Relay/relay, low voltage	T/C, RTD/0.1
CN424-DC1-R2	99	DC pulse/relay	T/C, RTD/0.1
CN424-DC1-DC2	99	DC pulse/DC pulse	T/C, RTD/0.1
CN434-R1-R2	99	Relay/relay	Universal/0.1
CN434-R1-R2-LV	105	Relay/relay, low voltage	Universal/0.1
CN434-DC1-R2	99	DC pulse/relay	Universal/0.1
CN434-DC1-DC2	99	DC pulse/DC pulse	Universal/0.1
CN434-F1-R2	99	0 to 20 mA/relay	Universal/0.1
CN444-R1-R2	149	Ramp and soak, relay/relay	Universal/0.1
CN444-R1-R2-LV	155	Ramp and soak, relay/relay, low voltage	Universal/0.1
CN444-DC1-R2	149	Ramp and soak, DC pulse/relay	Universal/0.1
CN444-DC1-DC2	149	Ramp and soak, DC pulse/DC pulse	Universal/0.1
CN444-F1-R2	155	Ramp and soak, 0 to 20 mA/relay	Universal/0.1

Comes complete with operator's manual.

Ordering Examples: CN444-F1-R2, 1/4 DIN universal input controller, single 0 to 20 mA control output with one alarm relay, \$99.

CN448V-R1-R2-LV, 1/8 DIN vertical universal input controller, ramp and soak, single control relay output with one alarm relay, low voltage, \$139.

Accessory (Field Installable)

MODEL NUMBER	PRICE	DESCRIPTION
CNQUENCHARC	\$8	Noise suppression kit, 110 to 230 Vac

omega.co.uk[®]

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

www.omega.co.uk



UNITED STATES

www.omega.com

1-800-TC-OMEGA
Stamford, CT.

UNITED KINGDOM

www.omega.co.uk

Manchester, England
0800-488-488
+44-(0)161-777-6611

CANADA

www.omega.ca

Laval(Quebec)
1-800-TC-OMEGA

FRANCE

www.omega.fr

0800-466-342

GERMANY

www.omega.de

Deckenfronn, Germany
0800-8266342

BENELUX

www.omega.nl

0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485, Ethernet and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters