



# TYPE 12 FREE-STANDING SINGLE-DOOR, DUAL-ACCESS ENCLOSURES

Starts at  
**\$1476**



- 0.104" Carbon Steel or Stainless Steel
- Seams Continuously Welded and Ground Smooth, No Holes or Knockouts
- Strong, Rigid Construction
- Lifting Eyes for Easy Handling
- Black Zinc Die Cast Keylocking/ Padlocking Handle
- 3-Point Latching Mechanism
- Latch Rods Have Rollers for Easier Door Closing
- Concealed Hinge
- Flange Trough Collar Around All Sides of Door Opening
- Removable Print Pocket Provided On Door with 3-Point Latch
- Mounting Channels Welded Horizontally On Sides of Interior Body At Top, Bottom and Middle for Mounting Optional Panels or Rack Mounting Angles
- Oil Resistant Gasket
- Ground Stud On Door
- Removable and Interchangeable Doors

## Application

Designed to house a variety of electrical and electronic controls and instruments. Provisions for optional surface mounting or rack mounting of almost any type of equipment. Provides protection from dust, dirt, water and oil. The enclosures are extra deep for applications requiring more interior space.

## Finish


White powder coating inside and ANSI-61 recoatable gray finish outside over phosphatized surfaces. Stainless steel enclosures are Type 304 stainless with #4 brushed finish. Optional panels are powder coated white.

## Industry Standards

NEMA Type 12 & Type 13  
UL Listed Type 12  
CSA Type 12  
IEC 60529 IP 55



SCE-722424FSDA, \$1476,  
shown smaller than actual size.



Dimensions: in (mm)

**To Order (Specify Model Number)**

**MOST POPULAR MODELS HIGHLIGHTED!**

| MODEL NO.                                     | PRICE  | DESCRIPTION                       | HEIGHT (in) (A) | WIDTH (in) (B) | DEPTH (in) (C) |
|---|--------|-----------------------------------|-----------------|----------------|----------------|
| <b>DUAL ACCESS CARBON STEEL ENCLOSURES</b>    |        |                                   |                 |                |                |
| SCE-722424FSDA                                | \$1476 | Type 12 free-standing single-door | 72.00           | 24.00          | 24.00          |
| SCE-722430FSDA                                | 1623   | Type 12 free-standing single-door | 72.00           | 24.00          | 30.00          |
| SCE-722436FSDA                                | 1772   | Type 12 free-standing single-door | 72.00           | 24.00          | 36.00          |
| SCE-723024FSDA                                | 1624   | Type 12 free-standing single-door | 72.00           | 30.00          | 24.00          |
| SCE-723624FSDA                                | 1772   | Type 12 free-standing single-door | 72.00           | 36.00          | 24.00          |
| SCE-723636FSDA                                | 2104   | Type 12 free-standing single-door | 72.00           | 36.00          | 36.00          |
| SCE-903624FSDA                                | 2049   | Type 12 free-standing single-door | 90.00           | 36.00          | 24.00          |
| SCE-903636FSDA                                | 2438   | Type 12 free-standing single-door | 90.00           | 36.00          | 36.00          |
| <b>DUAL ACCESS STAINLESS STEEL ENCLOSURES</b> |        |                                   |                 |                |                |
| SCE-722424SSFSDA                              | \$5312 | Type 12 free-standing single-door | 72.00           | 24.00          | 24.00          |
| SCE-722430SSFSDA                              | 5841   | Type 12 free-standing single-door | 72.00           | 24.00          | 30.00          |
| SCE-722436SSFSDA                              | 6378   | Type 12 free-standing single-door | 72.00           | 24.00          | 36.00          |
| SCE-723024SSFSDA                              | 5845   | Type 12 free-standing single-door | 72.00           | 30.00          | 24.00          |
| SCE-723624SSFSDA                              | 6378   | Type 12 free-standing single-door | 72.00           | 36.00          | 24.00          |
| SCE-723636SSFSDA                              | 7573   | Type 12 free-standing single-door | 72.00           | 36.00          | 36.00          |
| SCE-903624SSFSDA                              | 7375   | Type 12 free-standing single-door | 90.00           | 36.00          | 24.00          |
| SCE-903636SSFSDA                              | 8777   | Type 12 free-standing single-door | 90.00           | 36.00          | 36.00          |

Ordering Example: SCE-722424FSDA Type 12 free standing, single-door, dual access, carbon steel enclosure, \$1476.



#### UNITED STATES

[www.omega.com](http://www.omega.com)  
1-800-TC-OMEGA  
Stamford, CT.

#### CANADA

[www.omega.ca](http://www.omega.ca)  
Laval(Quebec)  
1-800-TC-OMEGA

#### GERMANY

[www.omega.de](http://www.omega.de)  
Deckenpfronn, Germany  
0800-8266342

#### UNITED KINGDOM

[www.omega.co.uk](http://www.omega.co.uk)  
Manchester, England  
0800-488-488

#### FRANCE

[www.omega.fr](http://www.omega.fr)  
Guyancourt, France  
088-466-342

#### CZECH REPUBLIC

[www.omegaeng.cz](http://www.omegaeng.cz)  
Karviná, Czech Republic  
596-311-899

#### BENELUX

[www.omega.nl](http://www.omega.nl)  
Amstelveen, NL  
0800-099-33-44



## More than 100,000 Products Available!

### • Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

### • Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

### • pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

### • Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

### • Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

### • Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters