

# TEMPERATURE, PROCESS AND STRAIN WALL MOUNT PANEL METER/CONTROLLER



**CNi8C-EN**



- Easy-to-Use Digital Controller with PID and Ramp/Soak
- Bright Programmable 3-Color Changing Display
- Universal Inputs: Thermocouple, RTD, Process Voltage/Current, Strain
- 2 Control or Alarm Outputs, Choice of: Mechanical Relays  
Solid State Relays  
Analog Voltage and Current
- Sealed Enclosure, NEMA 4 (IP65)
- Fuses for SSR or Relay Outputs
- 120/240 Vac Operation



**CNi8C33-EN**  
Shown smaller than actual size.



The CNi8C-EN is a compact, wall-mountable meter/controller that can be used for applications that need a fixed location, when a control panel is not required. The meter/controller supports a variety of temperature and process, or strain and process inputs. The flip-top enclosure makes programming and wire access easy to use. For more complete specifications of the meter/controller refer to the iSeries common specifications at [omega.com/iseriess](http://omega.com/iseriess).

## SPECIFICATIONS

**Weight:** 1.22 kg (2.7 lb)

**Dimensions:** 206 H x 183 W x 124 mm D (8.1 x 7.2 x 4.9")

**Operating Temperature:** 0 to 50°C (32 to 122°F)

**To Order Visit [omega.com/cni8c-en](http://omega.com/cni8c-en) for Pricing and Details**

Model No.	Description
<b>CNi8C22-EN</b>	Wall mount enclosure with temperature/process controller with two SSR outputs, 120 Vac power cord
<b>CNi8C33-EN</b>	Wall mount enclosure with temperature/process controller with two form C relay outputs, 120 Vac power cord
<b>CNi8C52-C24-EN</b>	Wall mount enclosure with temperature/process controller with one analog and one SSR outputs, RS232 and RS485 serial communication, 120 Vac power cord
<b>CNi8C53-EN</b>	Wall mount enclosure with temperature/process controller with analog and one form C relay outputs, 120 Vac power cord
<b>CNi8C33-EN</b>	Wall mount enclosure with strain/process controller with two form C relay outputs, 120 Vac power cord
<b>CNi8C52-EN</b>	Wall mount enclosure with strain/process controller with one analog and one SSR outputs, 120 Vac power cord
<b>DPi8C-EN</b>	Wall mount enclosure with temp/process meter, no outputs, 120 Vac power cord

*Comes complete with meter/controller, one power fuse, output fuses as required, power cord (country specific), cable glands for wiring.*

**Ordering Example:** **CNi8C33-C24-EN**, temperature/process controller, with dual form C SPDT relays, one control fuse, two output fuses, 120 Vac power cord, isolated RS232 and RS485 serial communication; **DPi8C-EN**, strain/process meter with one power fuse and 120 Vac power cord.

# omega.co.uk<sup>®</sup>

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

[www.omega.co.uk](http://www.omega.co.uk)



#### UNITED STATES

[www.omega.com](http://www.omega.com)

1-800-TC-OMEGA  
Stamford, CT.

#### UNITED KINGDOM

[www.omega.co.uk](http://www.omega.co.uk)

Manchester, England  
0800-488-488  
+44-(0)161-777-6611

#### CANADA

[www.omega.ca](http://www.omega.ca)

Laval(Quebec)  
1-800-TC-OMEGA

#### FRANCE

[www.omega.fr](http://www.omega.fr)

0800-466-342

#### GERMANY

[www.omega.de](http://www.omega.de)

Deckenfronn, Germany  
0800-8266342

#### BENELUX

[www.omega.nl](http://www.omega.nl)

0800-099-33-44



## More than 100,000 Products Available!

### • Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

### • Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

### • pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

### • Data Acquisition

Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485, Ethernet and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

### • Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

### • Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters