

Ultra Low Temperature Data Logger

OM-CP-CRYO-TEMP
Starts at

\$199



- ✓ Ultra Low Operating Temperature: -86°C (-122°F)
- ✓ May be Placed in Direct Contact with Dry Ice
- ✓ No External Probes or Wiring
- ✓ High Accuracy
- ✓ Programmable Alarm and Warning Ranges With Alarm Delay
- ✓ LED Status Indicators for Instant Alarm Notification
- ✓ Magnetic Start
- ✓ Optional Password Protection
- ✓ Splash Resistant (IP64)

The OM-CP-CRYO-TEMP ultra low temperature data logger records temperatures as low as -86°C (-122°F). The OM-CP-CRYO-TEMP can be used in a broad line of applications such as monitoring blood plasma, vaccines, pharmaceutical, frozen foods and shipping containers. This stand-alone device does not require any additional probes. The enclosure is designed with a handle for easy attachment and is IP64 splash resistant.

It utilizes a USB docking station (sold separately), to communicate with a personal computer or laptop. The OM-CP-CRYO-TEMP provides date and time stamped temperature readings. Our easy-to-use Windows® software does the rest.

The user can view the data in graphical or tabular form. High and low alarm limits and high and low warning limits can be programmed through the software.



OM-CP-CRYO-TEMP, \$199, shown actual size.

OM-CP-IFC300 docking station, 2 m (6') USB cable and Windows® software, \$70, sold separately and required to operate data logger. Shown actual size.

The user can set the alarm limits in the range required for the goods to be maintained. The warning limits can be set to alert the user when the temperature is nearing a high or low alarm limit, so that proper action can be taken to ensure the integrity of the goods.

The OM-CP-CRYO-TEMP is equipped with three LED's. The green LED will blink every 15 seconds while the recorder is logging data. The yellow LED will blink every 3 seconds when the temperature has breached the warning limits. The red LED will blink every 3 seconds when the temperature alarm limits have been exceeded.

The OM-CP-CRYO-TEMP is the ideal temperature monitoring solution for any application involving ultra low temperature recording.

Specifications

Temperature Sensor:

NTC Thermistor

Temperature Measurement

Range: -86 to 35°C (-122 to 95°F)
recommended, may be used up to 55°C (131°F)

Temperature Resolution:
0.1°C

Calibrated Accuracy:
±1.0°C

Specified Accuracy Range:
-80 to 0°C (-122 to 32°F)

Readings: 32,767

Recording Interval:
5 seconds to 30 minutes,
selectable in software

Start Modes: Immediate start,
delay start or manual start
with magnetic switch



OM-CP-IFC300, \$70, Windows software displays data in graphical or tabular format.



OM-CP-CRYO-TEMP, \$199, shown actual size.

Programmable Start Delay:

Up to 30 days from PC launch or manual start

Temperature Alarm: Software programmable high and low alarm limits, high and low warning limits; each setpoint may be individually enabled or disabled

Alarm Delay: Software programmable time delay for warning/alarm limits; logger will not indicate out of range status until the temperature has been out of range for a set period of time

Status Indicators:

- Green:** Blinks to indicate safe conditions during logging
- Yellow:** Blinks to indicate warn limits have been exceeded
- Red:** Blinks to indicate alarm criteria (limits/delay) have been exceeded

Password Protection:

An optional password may be programmed into the device to restrict access to configuration options; data may be read out without the password

Calibration:

Digital calibration is available to the user through software

Calibration Date:

Automatically recorded within device

Power: 3.6V lithium battery (included), factory replaceable only

Battery Life:

- 2 Years:** Typical @ 25°C (77°F), 1 min reading intervals
- 1 Year:** Typical @ -80°C (176°F), 1 min reading intervals

Time Accuracy: ±2 minutes/month max at 20 to 30°C (68 to 86°F); ±5 minutes/month max at -80°C (176°F)

Data Format: Date and time stamped °C, °F, K, °R

Computer Interface:

USB docking station to PC; 38,400 baud

Software:

WIN98/NT/2000/XP/VISTA 32-bit, (VISTA 32-bit version only; VISTA 64-bit is not supported)

Operating Environment:

-86 to 35°C (-122 to 95°F) may be used up to 55°C (131°F); 0 to 100% RH

Dimensions:

83 H x 54 W x 11 mm D (3.3 x 2.1 x 0.4")

Ingress Protection/IP Rating:

IP64 (splash resistant, not submersible)

Enclosure: ABS plastic, white, polycarbonate labeling

Weight: 40 g (1.4 oz)

AVAILABLE FOR FAST DELIVERY!

To Order (Specify Model Number)

Model No.	Price	Description
OM-CP-CRYO-TEMP	\$199	Ultra-low temperature data logger
OM-CP-CRYO-TEMP-CERT	259	Ultra-low temperature data logger with NIST calibration certificate
OM-CP-IFC300	70	Windows software, docking station and 2 m (6') USB interface cable

Operator's manual is included with the OM-CP-IFC300 Windows software, docking station and USB cable, (required to operate the data logger and sold separately).

Ordering Example: OM-CP-CRYO-TEMP, ultra-low temperature data logger and OM-CP-IFC300, Windows software with docking station and USB cable, \$199 + 70 = \$269.

omega.co.uk[®]

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

www.omega.co.uk



UNITED STATES

www.omega.com

1-800-TC-OMEGA
Stamford, CT.

UNITED KINGDOM

www.omega.co.uk

Manchester, England
0800-488-488
+44-(0)161-777-6611

CANADA

www.omega.ca

Laval(Quebec)
1-800-TC-OMEGA

FRANCE

www.omega.fr

0800-466-342

GERMANY

www.omega.de

Deckenfronn, Germany
0800-8266342

BENELUX

www.omega.nl

0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485, Ethernet and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters