

# SMARTSTIX™ I/O FOR THE XL SERIES OCS



All models shown smaller than actual size.



HE559DIQ816, \$365



HE559DIM610, \$195

HE559 Series  
Starts at  
**\$195**



\* Digital models only.

- Expands Analog and Digital I/O of Any OCS Using a CsCAN Network
- May be Used Locally or Remotely
- Extremely Compact
- Removable Screw Terminals

## A New I/O for OCS

SmartStix™ I/O is a new terminal-block style I/O designed for use with the the XL series Operator Control Station (OCS). It can be used to expand the I/O capacity of any OCS, and it is very cost effective as remote I/O. SmartStix I/O connects to any OCS CsCAN™ network port to provide the best I/O selection for the application. And, output modules feature Electronic Short-Circuit Protection (ESCP).

## Compact, DIN-Rail Mounted

SmartStix I/O is extremely compact, providing 16 and 32 point digital I/O in a package only 39 mm (1.5") deep and a footprint of 50 H x 116 W mm (2 x 4.5") or 50 H x 177 W mm (2 x 7"). With its small footprint, SmartStix I/O takes up very little panel space whether located in the main control panel or tucked away in a remote location. SmartStix I/O has a barrier style terminal strip and can be mounted on a DIN-Rail. Plus, removable terminals make field replacement fast and convenient.

## Expands I/O Capacity, Local or Remote

SmartStix I/O easily expands the I/O capacity of any OCS utilizing the CsCAN network port available with every model. It is especially cost effective when added to an XL Series OCS. SmartStix I/O offers fast response times without sacrificing robustness, with no need for a costly I/O interface unit. In addition to its peer-to-peer capabilities, CsCAN is used as a highly efficient method of distributing SmartStix I/O up to 1829 m (6000')\* away.

\* Maximum distance is 457 m (1500') per segment, with up to 1829 m (6000') possible using repeaters.

## Easy to Set Up

SmartStix require minimal time and complexity to configure. Just assign a unique ID, connect the 5-wire shielded cable and you will be up and running in no time.

## SPECIFICATIONS

- Bus Protocol:** CsCAN (control station controller area network)
- Bus Connector:** 5-position terminal strip
- Maximum Distance:** 457 m (1500') per segment; 4 segments max
- Maximum Number of Total Nodes:** 253
- Module Configuration Method:** Module ID set using two rotary switches
- LED Indication:** I/O status (one per point); power, module status, network status
- Output Protection:** Electronic short-circuit protection (16 and 32 output modules only)
- Product Certifications:** CE (all models), UL (digital only)
- ANALOG INPUTS**
- Input Ranges:** ±5V, ±10 Vdc, 4 to 20 mA, ±20 mA DC
- Resolution:** 14 bits
- Accuracy@ 25°C:** 0.1%



HE559DIQ816, \$365



HE559DIM610, \$195

**Input Impedance:** 1 M $\Omega$  (voltage range), 150  $\Omega$  (mA range)

**Isolation:** 1000 Vdc IEC61010-1 300 VRMS

**Maximum Continuous Overload:** 150 Vac ( $\pm 10V$ ),  $\pm 30$  mA ( $\pm 20$  mA), clamped at  $\pm 6V$

**DIGITAL INPUTS**

**Rated Input Current:** 7 mA

**Rated Voltage:** 11 to 25 Vdc

**ON Voltage Level:** 19 Vdc or less

**OFF Voltage Level:** 6 Vdc or less

**Input Characteristics Bidirectional**

**Isolation Method:** Photo coupler

**OFF to ON Response:** 0 to 3 ms or less

**ON to OFF Response:** 0 to 3 ms or less

**ANALOG OUTPUTS**

**Output Ranges:**  $\pm 5$ ,  $\pm 10$  Vdc, 4 to 20 mA,  $\pm 20$  mA DC

**Resolution:** 14 bits

**Accuracy@ 25°C:** 0.1%

**Load Resistance:** 600 min (voltage), 500 max (mA)

**Isolation:** 1000 Vdc, IEC61010-1 300 VRMS

**Output Characteristic:** Sourcing

**DIGITAL OUTPUTS**

**Operating Voltage:** 24 Vdc

**Rated Load Voltage:** 24 Vdc

**Output Type:** Sourcing

**Maxload Current:** 0.5 A max per output 3 A per common

**OFF to ON Response:** 2 mS

**ON to OFF Response:** 2 mS

**RELAY OUTPUTS**

**Rated Load Voltage:** 24 Vdc, 220 Vac

**Minimum Load Voltage/Current:** 5 Vdc/1 mA

**Maximum Load Current (Resistive):** 2.0 A per channel, 5.0 A per common

**OFF to ON Response:** 10 mS max

**ON to OFF Response:** 12 mS max

**Output Type:** NO

**Dimensions (Approx):**

**32 I/O, Analog I/O or Relay Output:** 176 L x 48 D x 50 mm H (7 x 1.9 x 2")

**16 I/O (Not Relay):** 115 L x 48 D x 50 mm H (4.5 x 1.9 x 2")

**To Order (Specify Model Number)**

**MOST POPULAR MODELS HIGHLIGHTED!**

DIGITAL I/O		
MODEL NO.	PRICE	DESCRIPTION
HE559DIM610	\$195	16 DC inputs (24 Vdc positive/negative logic) I/O expander for CsCAN with removable field terminals
HE559DIM710	330	32 DC inputs (24 Vdc positive/negative logic) I/O expander for CsCAN with removable field terminals
HE559DIQ816	365	16 DC inputs (24 Vdc positive/negative logic) plus 16 DC outputs (pos logic) 0.5 A I/O expander for CsCAN with removable field terminals
HE559DQM602	235	16 relay outputs (250 Vac, 30 Vdc, 2 A) for CsCAN with removable field terminals
HE559DQM606	235	16 DC outputs (24 Vdc positive logic, 0.5 A) I/O expander for CsCAN with removable field terminals
HE559DQM706	399	32 DC outputs (24 Vdc, positive logic, 0.5 A) I/O expander for CsCAN with removable field terminals
ANALOG I/O		
HE559MIX577	580	4 analog inputs ( $\pm 10V$ , $\pm 20$ mA) 14-bit resolution plus 2 analog outputs ( $\pm 10V$ , $\pm 20$ mA) 14-bit resolution; channel-by-channel voltage/current selection for all channels; for CsCAN with removable field terminals

SmartStix I/O module comes with a 5-pin terminal style network connector. An optional M12 adaptor for M12 cable sets is available. SmartStix I/O have removable terminals and can be DIN-rail mounted.

Ordering Example: HE559DIM610, 16 DC input model, \$195.

# omega.co.uk®

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

[www.omega.co.uk](http://www.omega.co.uk)



#### UNITED STATES

[www.omega.com](http://www.omega.com)

1-800-TC-OMEGA  
Stamford, CT.

#### CANADA

[www.omega.ca](http://www.omega.ca)

Laval(Quebec)  
1-800-TC-OMEGA

#### GERMANY

[www.omega.de](http://www.omega.de)

Deckenfronn, Germany  
0800-8266342

#### UNITED KINGDOM

[www.omega.co.uk](http://www.omega.co.uk)

Manchester, England  
0800-488-488  
+44-(0)161-777-6611

#### FRANCE

[www.omega.fr](http://www.omega.fr)

0800-466-342

#### BENELUX

[www.omega.nl](http://www.omega.nl)

0800-099-33-44



## More than 100,000 Products Available!

### • Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

### • Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

### • pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

### • Data Acquisition

Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485, Ethernet and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

### • Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

### • Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters