

OM-CP-TEMP100, OM-CP-TEMP101 and OM-CP-TEMP110 Temperature Data Loggers

Part of the NOMAD® Family

\$79

Basic Unit



- ✓ Miniature Size
- ✓ Memory Size: 32,768 Readings
- ✓ Programmable Start Time or Push Button Start/Stop (Push Button Only on OM-CP-TEMP100)
- ✓ User Calibration Through Software
- ✓ Real Time Operation

The OM-CP-TEMP100, OM-CP-TEMP101 and OM-CP-TEMP110 are miniature, battery powered, stand-alone, temperature data loggers. These all-in-one compact, portable, easy-to-use devices will measure and record up to 32,768 temperature measurements. They can be started and stopped directly from your computer or through an externally accessible push button (push button start/stop only on OM-CP-TEMP100). These data loggers are a major leap forward in both size and performance. The real time clock ensures that all data is time and date stamped. The storage medium is non-volatile solid state memory, providing maximum data security even if the battery becomes discharged. Its small size allows it to fit almost anywhere.

Data retrieval is simple. Plug it into an empty COM port and our easy-to-use software does the rest. The software converts your PC into a real time strip chart recorder. Data can be printed in graphical or tabular format and can be exported to a text or Microsoft Excel file.

Specifications

Temperature Sensor:

Semiconductor

Temperature Accuracy:

±0.5°C (0 to 50°C)


Temperature Resolution: 0.1°C

Temperature Range:


-40 to 80°C (-40 to 176°F)

Temperature Calibration:

Digital calibration is available through software




OM-CP-TEMP100, \$109, OM-CP-TEMP101, \$79, and OM-CP-TEMP110, \$199, data loggers are shown larger than actual size



OM-CP-TEMP110, \$99, Windows software displays data in graphical or tabular format.



OM-CP-TEMP100, \$109, OM-CP-TEMP101, \$79, and OM-CP-TEMP110, \$199, data loggers are shown larger than actual size



OM-CP-IFC110, \$99, Windows software displays data in graphical or tabular format.

Calibration Date: Automatically recorded within device to alert user when calibration is required
Recording Interval: 2 sec to 12 hrs selectable through software
Alarm: Programmable high and low limits; alarm is activated when temperature goes outside limits (OM-CP-TEMP100 and OM-CP-TEMP101 only)
Real Time Recording: Device may be used with PC to monitor and record data in real time
Green Visual Indicator: LED flashes selected reading rate when device is recording data
Red Visual Indicator: LED flashes at one second interval indicating alarm condition (OM-CP-TEMP100 and OM-CP-TEMP101 only)
Power: 3.6 V lithium battery included
Battery Life:
OM-CP-TEMP100 and OM-CP-TEMP101: 1 year at 1 min reading rate.
OM-CP-TEMP110: 10 years at 15 min reading rate.

Time Accuracy: \pm minute/month when RS-232 port is not in use
Data Format: Date and time stamped, $^{\circ}\text{C}$, $^{\circ}\text{F}$, $^{\circ}\text{K}$, $^{\circ}\text{R}$
Weight:
OM-CP-TEMP100 and OM-CP-TEMP101: 30 g (1 oz)
OM-CP-TEMP110 60: g (2 oz)
Computer Interface: PC serial, RS-232C COM or USB
Communications:
OM-CP-TEMP100 and OM-CP-TEMP101: 2400 baud
OM-CP-TEMP110: 57600 baud
Software: WIN98/NT/2000/XP/VISTA 32-bit (VISTA 32-bit version only; VISTA 64-bit is not supported)
Operating Environment: -40 to 80 $^{\circ}\text{C}$ (-40 to 176 $^{\circ}\text{F}$)
 5 to 95% RH non-condensing
Dimensions:
OM-CP-TEMP100 and OM-CP-TEMP101: 36 H x 56 W x 16 mm D (1.4 x 2.2 x 0.6")
OM-CP-TEMP110: 43 H x 69 W x 20 mm D (1.7 x 2.7 x 0.8")

MOST POPULAR MODELS HIGHLIGHTED!

To Order (Specify Model Number)		
Model No.	Price	Description
OM-CP-TEMP100	\$109	Temperature data logger with start/stop push button
OM-CP-TEMP100-CERT	169	Temperature data logger with start/stop push button with NIST calibration certificate
OM-CP-TEMP101	79	Temperature data logger with 1 year battery life
OM-CP-TEMP101-CERT	139	Temperature data logger with 1 year battery life with NIST calibration certificate
OM-CP-TEMP110	199	Temperature data logger with 10 year battery life
OM-CP-TEMP110-CERT	259	Temperature data logger with 10 year battery life with NIST calibration certificate
OM-CP-IFC110	99	Windows software and 1.2 m (4') RS-232 cable with DB9F termination
OM-CP-IFC200	119	Windows software and 3.7 m (12') USB interface cable
OM-CP-BAT105	12	Replacement 3.6 V lithium battery

Operator's manual and RS-232 cable are included with the **OM-CP-IFC110** Windows software (software is required to operate the data logger and is sold separately).

*Only model **OM-CP-TEMP101** is CE approved.

Ordering Example: OM-CP-TEMP100-CERT temperature data logger with NIST calibration certificate and OM-CP-IFC110 Windows software and RS-232 cable, \$169 + 99 = \$268.

omega.co.uk®

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

www.omega.co.uk



UNITED STATES

www.omega.com

1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca

Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de

Deckenpfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk

Manchester, England
0800-488-488
+44-(0)161-777-6611

FRANCE

www.omega.fr

0800-466-342

BENELUX

www.omega.nl

0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers, Plug-in Cards, Signal Conditioners, USB, RS232, RS485, Ethernet and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters