

SINGLE CONDUCTOR HOOK-UP WIRE

IRRADIATED PVC INSULATION



HW7000 Series
Starts at
\$41
100' Spool



- **Operating Temperature:**
-55 to 105°C (-67 to 221°F)
-UL AWM 1430
-55 to 105°C (-67 to 221°F)
-UL AWM 3317
-55 to 105°C (-67 to 221°F)
-CSA AWM I
A/B FT1
-55 to 105°C (-67 to 221°F)
-MIL-W-16878E
-55 to 80°C (-67 to 176°F)
-UL AWM 1429
- 600V (MIL), 150V (UL, CSA)
- 1000V (MIL), 300V (UL, CSA)
- Stranded Tinned Copper Conductor
- Color-Coded, Irradiated PVC (XLPVC) Insulation



A "tougher" version of PVC insulation, irradiated PVC (exposed to electron beam radiation) has better abrasion and cut resistance than ordinary PVC and can be used more readily in soldering applications.

SPECIFICATIONS

- UL AWM Style 1429
- UL AWM Style 1430
- UL AWM Style 3317
- CSA AWM I A/B FT1
- CSA REW XLPVC FT1
- MIL-W-16878E, Type B
- MIL-W-16878E, Type C

COLOR CHART

1	White	7	Brown
2	Black	8	Orange
3	Red	9	Gray
4	Green	10	Violet
5	Yellow		
6	Blue		

To Order (Specify Model Number)

MOST POPULAR MODELS HIGHLIGHTED!

MIL-W16878E TYPE B: 105°C (221°F), 600V CSA AWM I A/B FT1: 105°C (221°F), 150V UL 1429: 80°C (176°F), 150V						
MODEL NO.	100'	PRICE 1000'	AWG NO.	WIRE TYPE	INSULATION THICKNESS mm (in)	NOMINAL OD mm (in)
HW7053-(*)-(**)	\$41	\$173	26	7/34	0.25 (0.010)	1.02 (0.040)
HW7054-(*)-(**)	46	205	24	7/32	0.25 (0.010)	1.14 (0.045)
HW7054/19-(*)-(**)	54	219	24	19/36	0.25 (0.010)	1.14 (0.045)
HW7055-(*)-(**)	51	214	22	7/30	0.25 (0.010)	1.30 (0.051)
HW7055/19-(*)-(**)	57	227	22	19/34	0.25 (0.010)	1.32 (0.052)
HW7056-(*)-(**)	65	256	20	7/28	0.25 (0.010)	1.50 (0.059)
HW7056/19-(*)-(**)	74	292	20	19/32	0.25 (0.010)	1.52 (0.060)
HW7057-(*)-(**)	92	336	18	7/26	0.25 (0.010)	1.78 (0.070)
HW7057/19-(*)-(**)	109	400	18	19/30	0.25 (0.010)	1.78 (0.070)
HW7058/19(*)-(**)	98	500	16	19/29	0.25 (0.010)	1.98 (0.078)
MIL-W-16878E TYPE C: 105°C (221°F), 1000V UL 1430, CSA REW XLPVC: 105°C (221°F), 300V						
HW7130-(*)-(**)	\$84	\$245	24	7/32	0.41 (0.016)	1.42 (0.056)
HW7131-(*)-(**)	95	296	22	7/30	0.41 (0.016)	1.57 (0.062)
HW7132-(*)-(**)	98	341	20	7/28	0.41 (0.016)	1.78 (0.070)
HW7133-(*)-(**)	115	475	18	7/26	0.41 (0.016)	2.08 (0.082)
HW7134-(*)-(**)	170	595	16	19/29	0.41 (0.016)	2.34 (0.092)

* Specify Color by entering color code from the chart. ** Specify Length "-100" or "-1000".

Ordering Example: HW7057-1-100, 30 m (100') spool of 18 stranded (19 x 30), irradiated PVC insulation hook up wire, white, \$92.
HW7132-2-100, 30 m (100') spool of 20 stranded (7 x 28), irradiated PVC insulation hook up wire, black, \$98.

omega.co.uk[®]

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

www.omega.co.uk



UNITED STATES

www.omega.com

1-800-TC-OMEGA
Stamford, CT.

UNITED KINGDOM

www.omega.co.uk

Manchester, England
0800-488-488
+44-(0)161-777-6611

CANADA

www.omega.ca

Laval(Quebec)
1-800-TC-OMEGA

FRANCE

www.omega.fr

0800-466-342

GERMANY

www.omega.de

Deckenfronn, Germany
0800-8266342

BENELUX

www.omega.nl

0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485, Ethernet and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters