



NEMA TYPE 4X STAINLESS STEEL 30.5 mm PUSHBUTTON ENCLOSURES



- 0.075" Stainless Steel Type 304
- Seams Continuously Welded and Ground Smooth
- Captivated Cover Screws Thread Into Sealed Wells
- 4-Way Pushbutton Holes Accept All Brands of Oil-Tight Pushbuttons, Switches and Pilot Lights
- Hole Diameter is 30.5 mm (1.20")
- Immediate Removal of is Permitted
- Oil-Resistant Door Gasket
- Can Be Special Ordered in Type 316 Stainless Steel

Application

Designed to house standard pushbuttons, switches and pilot lights in wet and hosed down areas and in corrosive atmospheres.

Finish


#4 brushed finish on all exterior surfaces.

Industry Standards

NEMA Type 4, 4X, 12 & 13
UL Listed Type 4, 4X, & 12
CSA Type 4, 4X & 12
IEC 60529 IP 66




SCE-9PBSS,
shown smaller than
actual size.




Dimensions: in (mm)

NOTE:
*B - 12.7 (0.50) ONE COLUMN OF PUSHBUTTONS



SECTION A-A



STANDARD 4-WAY

To Order (Specify Model Number)		MOST POPULAR MODELS HIGHLIGHTED!		
TYPE 4X STAINLESS STEEL 30.5 mm PUSHBUTTON ENCLOSURES				
MODEL NO.	HEIGHT (in) (A)	WIDTH (in) (B)	DEPTH (in) (C)	
SCE-1PBSS	3.50	3.25	2.75	
SCE-2PBSS	5.75	3.25	2.75	
SCE-3PBSS	8.00	3.25	2.75	
SCE-4PBSS	10.25	3.25	2.75	
SCE-4PBXSS	10.00	4.00	4.75	
SCE-4SPBSS	7.25	6.25	3.00	
SCE-6PBSS	9.50	6.25	3.00	
SCE-9PBSS	9.50	8.50	3.00	
SCE-12PBSS	11.75	8.50	3.00	
SCE-16PBXSS	11.75	10.75	4.75	

Ordering Example: SCE-1PBSS, Type 4X stainless steel 30.5 mm pushbutton enclosure.

omega.co.uk[®]

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

www.omega.co.uk



UNITED STATES

www.omega.com

1-800-TC-OMEGA
Stamford, CT.

UNITED KINGDOM

www.omega.co.uk

Manchester, England
0800-488-488
+44-(0)161-777-6611

CANADA

www.omega.ca

Laval(Quebec)
1-800-TC-OMEGA

FRANCE

www.omega.fr

0800-466-342

GERMANY

www.omega.de

Deckenfronn, Germany
0800-8266342

BENELUX

www.omega.nl

0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485, Ethernet and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters