

In-Transit Temperature Recorder Part of the NOMAD® Family

OM-CP-TRANSITEMP-EC-13

Buy 12, Get 1 FREE!



- ✓ Sold as a Baker's Dozen (Buy 12 and Get 1 Free)
- ✓ Ultra Low-Cost
- ✓ Single-Use
- ✓ Used Data Loggers Can be Returned and Refurbished to "Like New" Condition
- ✓ Unparalleled Quality and Performance
- ✓ Convenient Size
- ✓ Push-Button Start
- ✓ User-Selectable Reading Rate
- ✓ Programmable Alarm
- ✓ Instantaneous Out-of-Range Alarm Indication



OM-CP-TRANSITEMP-EC shown as Baker's Dozen and shown smaller than actual size.




OM-CP-TRANSITEMP-EC

The OM-CP-TRANSITEMP-EC is a low-cost temperature recorder designed to allow the user to easily monitor temperature fluctuations over time during shipment or storage of goods. Each logger can only be started once to monitor temperature during one application (single use). Used data loggers can either be discarded or returned to be refurbished (for a small fee) to "like new" condition so they can be used again. This all-in-one, compact, portable, easy-to-use

device will measure and record up to 8191 measurements per channel. The storage medium is non-volatile solid state memory, providing maximum data security even if the battery becomes discharged. The device can be started by holding down a recessed pushbutton. Once started, a green LED indicator light will blink twice to indicate that the device is active. A second red LED indicator will blink at 3-second intervals if the temperature goes above or below the selected alarm settings.

The OM-CP-TRANSITEMP-EC makes data retrieval quick and easy. Simply plug it in to an available COM port and our user-friendly software will do the rest. The software converts your PC into a real-time strip chart recorder. Data can be printed in graphical or tabular format and exported to a text or Microsoft Excel file.



Specifications

Temperature Sensor: Semiconductor

Temperature Range:
-20 to 70°C (-4 to 158°F)

Temperature Resolution: 0.1°C

Calibrated Accuracy:
±0.5°C (-10 to 40°C)
±1.0°C (-20 to 70°C)

Memory: 8191 readings (>85 days at 1 reading/15 minutes)

Recording Interval: 1 reading every 5 seconds to 1 every 30 minutes, selectable in software

Start Time: Pushbutton start or programmable start time and date up to 30 days in advance

Data Format: Date and time stamped °C, °F

Time Accuracy: ±2 minutes per month at 25°C

Temperature Alarm: Programmable temperature alarm with high and low limits selectable in software; when logged data reaches or exceeds either limit, red LED blinks every 10 seconds

Activity Indicator: Green LED blinks every 10 seconds to indicate device has been started; the red LED will blink if an alarm condition exists

Power: 3V lithium coin cell included, 2 year shelf life

Battery Life: 90 days typical at 25°C, 1-minute reading intervals

Computer Interface: PC serial or RS232C COM (interface cable required) 38,400 baud

Software: XP SP3/Vista/7 and 8 (32-bit and 64-bit)

Operating Environment:

-20 to 70°C (-4 to 156°F)
0 to 90% RH non-condensing

Dimensions: 44 W x 67 L x 16 Dia mm (1.7 x 2.6 x 0.6")

Weight: 25 g (0.9 oz)

Material: ABS plastic

Buy 12, Get 1 FREE!

To Order Visit omega.com/om-cp-transitemp-ec-13 for Pricing and Details

Model No.	Description
OM-CP-TRANSITEMP-EC-13	Thirteen single use in-transit temperature recorder, sold as a baker's dozen (13 loggers for the price of 12)
OM-CP-IFC103	Windows software and 1.2 m (4') RS232 cable with DB9F termination

Operator's manual and RS232 cable are included with the **OM-CP-IFC103** Windows software (required to operate the data logger and sold separately). Used data loggers can be returned and refurbished to like-new condition for additional cost. Contact our Customer Service Department for details.

Ordering Example: OM-CP-TRANSITEMP-EC-13 single use in-transit temperature recorder (baker's dozen) and OM-CP-IFC103 Windows software and RS232 cable.

omega.co.uk[®]

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

www.omega.co.uk



UNITED STATES

www.omega.com

1-800-TC-OMEGA
Stamford, CT.

UNITED KINGDOM

www.omega.co.uk

Manchester, England
0800-488-488
+44-(0)161-777-6611

CANADA

www.omega.ca

Laval(Quebec)
1-800-TC-OMEGA

FRANCE

www.omega.fr

0800-466-342

GERMANY

www.omega.de

Deckenfronn, Germany
0800-8266342

BENELUX

www.omega.nl

0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485, Ethernet and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters