

pH and Temperature Data Logger with LCD Display

OM-CP-PHTEMP2000

\$599



Optional

- ✓ Large LCD Display
- ✓ Works with OMEGA® PHE-4200 Series of pH Probes
- ✓ Real-Time Operation
- ✓ Programmable Engineering Units
- ✓ NIST Traceable Calibration
- ✓ Automatic Temperature Compensation
- ✓ Programmable Start-Time

The OM-CP-PHTEMP2000 is a battery powered, stand alone pH and temperature data logger with an LCD.

The OM-CP-PHTEMP2000 will directly connect to many commonly used pH, ORP and ISE electrodes through a female BNC connector mounted on its side. Temperature compensation is done automatically by connecting an RTD to the unit. The storage medium is non-volatile solid state memory, providing maximum data security even if the battery becomes discharged.

The OM-CP-PHTEMP2000 makes data retrieval quick and easy. Simply plug it into an empty com port and our user-friendly software does the rest.

SPECIFICATIONS

TEMPERATURE

Input: 100Ω Pt RTD

Measurement Range: -40 to 110°C (-72 to 230°F, 80 to 145 Ω)

Resolution: 0.01°C (0.001 Ω)

Calibrated Accuracy: ±0.15°C @ 25°C ambient (±0.015 Ω)

Input Connection: Removable screw terminal; 2-, 3- or 4-wire interface

PH/ORP/ISE

Input Connection: Female BNC

Measurement Range:

-2.00 to 16.00 pH

Resolution: 0.01 pH (0.001 pH)


pH Accuracy: ±0.01 pH

pH EMI Susceptibility: <0.2 pH @ 3V/M, 80 MHz to 1 GHz

ORP/ISE Accuracy: ±0.1 mV

ORP/ISE Susceptibility: <10 mV @ 3V/M, 80 MHz to 1 GHz

Input Impedance: 10¹² Ω typical



OM-CP-PHTEMP2000, \$599, shown smaller than actual size.

PR-11-2-100-1/4-6-E RTD probe, \$66, shown smaller than actual size.

PHE-4201 general-purpose pH electrode, \$62, shown smaller than actual size.

Windows Software shows data in graphical format

Start Modes: Software programmable immediate start or delay start up to six months in advance

Real-Time Recording: May be used with PC to monitor and record data in real time

DOT-MATRIX LCD

Dimensions:

35 H x 63 mm W (1.375 x 2.5")

Text: Configurable channel text size

Indicators: Power, status, memory

Backlight: Configurable w/auto shut-off and contrast adjustment

Memory: 131,071 readings per channel

Reading Rate: 1 reading every 2 seconds to 1 every 24 hours

Calibration: Digital calibration through software

Battery Type: 9V lithium or alkaline battery (included); user replaceable

Battery Life: 1 year battery life at 1 minute reading rate with display off; 30 days typical with continuous display use; optional AC adaptor available

Data Format: Date and time stamped °C, °F, K, R, Ω; pH, V, mV, engineering units specified through software

Time Accuracy: ±1 minute/month (at 25°C; RS232 cable not in use)

Computer Interface: PC serial or USB (interface cable required); 115,200 baud

Software: Windows 98/ME/NT/2000/XP/VISTA (VISTA 32-bit version only; VISTA 64-bit is not supported)

Operating Environment: -5 to 50°C (23 to 122°F), 0 to 95% RH (non-condensing)

Dimensions: 84 H x 122 W x 32 mm D (3.3 x 4.8 x 1.25")

Weight: 440 g (16 oz)

AVAILABLE FOR FAST DELIVERY!

To Order (Specify Model Number)

Model No.	Price	Description
OM-CP-PHTEMP2000	\$599	pH and temperature data logger with LCD display
OM-CP-PHTEMP2000-CERT	719	pH and temperature data logger with LCD display and NIST calibration certificate
OM-CP-IFC110	99	Windows software and 1.2 m (4') RS232 cable with DB9F termination
OM-CP-IFC200	119	Windows software and 3.7 m (12') USB interface cable
OM-CP-BAT103	20	Replacement 9V lithium battery
OM-CP-110-PWR-2000	13	110 Vac power adaptor
OM-CP-220-PWR-2000	13	220 Vac power adaptor
PHE-4201	62	General purpose pH electrode
PR-11-2-100-1/4-6-E	66	General purpose 100Ω RTD probe, 6" sheath, 1/4" diameter

Comes complete with operator's manual and 9V battery. OM-CP-IFC110, Windows software and RS232 cable (required to operate the data logger) sold separately.

Ordering Example: OM-CP-PHTEMP2000, pH and temperature data logger and OM-CP-IFC110, Windows software and 1.2 m (4') RS232 cable, \$599 + 99 = \$698.

omega.co.uk[®]

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

www.omega.co.uk



UNITED STATES

www.omega.com

1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca

Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de

Deckenfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk

Manchester, England
0800-488-488
+44-(0)161-777-6611

FRANCE

www.omega.fr

0800-466-342

BENELUX

www.omega.nl

0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485, Ethernet and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters