


High-Performance Analog and Digital I/O Boards

OME-PCI-1800H/L and OME-PCI-1802H/L: 330 KS/s 12-Bit Series

\$759
Basic Unit



OME-PCI-1800H,
\$759, shown smaller
than actual size

- ✓ PCI Bus
- ✓ 12-Bit 330 KHz A/D Converter
- ✓ OME-PCI-1800H, OME-PCI-1800L: 16 Single-Ended/ 8 Differential Inputs, 2K Word FIFO
- ✓ OME-PCI-1802H, OME-PCI-1802L: 32 Single-Ended/16 Differential Inputs, 8K Word FIFO
- ✓ 330 KSamples/s for Single Channel or Multiple Channels
- ✓ Trigger Methods: Software Trigger, Pacer Trigger, External Trigger
- ✓ External Triggers: Post-Trigger, Pre-Trigger, External Pacer Trigger
- ✓ OME-PCI-1800L, OME-PCI-1802L Programmable Low-Gain: 0.5, 1, 2, 4, 8
- ✓ 16 Digital Input and 16 Digital Output Channels
- ✓ OME-PCI-1800H,

OME-PCI-1802H Programmable High-Gain: 0.5, 1, 5, 10, 50, 100, 500, 1000

- ✓ Two Optional 12-Bit Independent Programmable DACs; 2 MHz Throughput per Channel (Max)
- ✓ 2.7M Word/High-Speed Data Transfer Rate
- ✓ Includes Software Development Kit
- ✓ Half-Size Board

The OME-PCI-1800 Series is a family of high-performance data acquisition boards for the PCI bus. It features continuous, 330 kHz, gap-free data acquisition under DOS and Windows.

The OME-PCI-1800 family has two 12-bit D/A output channels, 16 digital input channels, and 16 digital output channels. The OME-PCI-1800H and OME-PCI-1800L provide 16 single-ended or 8 differential inputs.

The OME-PCI-1802H and OME-PCI-1802L provide 32 single-ended or 16 differential inputs. The suffix "H" denotes a high-gain model and the "L" denotes a low-gain model. The boards feature advanced scanning features. The scanning mechanism not only scans the different input channels at vastly different rates, but also at different gains. Even in multichannel scan mode, the sampling rates can be maintained at 330 KS/s.

The OME-PCI-1800 Series also has some outstanding features, including:

- Data transfer rate of digital I/O is up to 5.4 MB
- Throughput of D/A is up to 2 MHz (max)
- Three flexible external trigger modes such as post-trigger, pre-trigger, middle trigger
- True "plug & play" under DOS and Windows
- On-board FIFO

OME-PCI-1800 Series System Expansion

Several daughter boards are available that can expand the analog and digital I/O capability of the OME-PCI-1800 Series high-performance data acquisition boards. These include: OME-DB-1825, OME-DB-8225, OME-DB-8025, OME-DB-889D, OME-DB-16P, OME-DB-16R.

OME-DB-889D 16-Channel Analog Multiplexer Board

The OME DB-889D is an expansion multiplexer/amplifier board for use with OME-PCI-1800H/L boards. Each OME-DB-889D multiplexes 16 differential analog input channels into one analog input of the data acquisition board. The high-grade instrumentation amplifier provides software programmable gains of 0.5, 1, 5, 10, 50, 100, 500, and 1000. Thermocouple measurements are handled easily with the OME-DB-889D. The board includes cold-junction sensing and compensation circuitry that provides a scaling of 24.4 mV/°C. Biasing resistors are included for open thermocouple detection. The OME-DB-889D can be cascaded to a total of 128 channels of voltage measurements or 112 channels of thermocouple measurement.

OME-DB-16P 16-Channel Isolated Digital Input Board

The OME-DB-16P is a 16-channel isolated digital input daughter board for any of the OME-PCI-1802H/1802L/1800H/1800L/1602/1602F/1202H/1202L/1002H/1002L PCI-bus multifunction boards. The optically isolated inputs of the OME-DB-16P consist of a bi-directional OPTO-coupler with a resistor for current sensing. The OME-DB-16P can be used to sense DC signals from TTL levels up to 24 V and also a wide range of AC signals. The OME-DB-16P can also be used to isolate the computer from large common-mode voltages, ground loops and voltage spikes that often occur in industrial environments.

OME-DB-16R 16-Channel Relay Output Board

The OME-DB-16R 16-channel relay output board consists of 16 Form C relays for efficient switching of loads by programmed control.

| OME-PCI-1800L & 1802L Analog Input Ranges | | | |
|---|-------------|--------------|------------|
| Gains | Bipolar (V) | Unipolar (V) | Throughput |
| 0.5 | ±10 V | 0 to 10 V | 330 KS/s |
| 1 | ±5 V | 0 to 10 V | 330 KS/s |
| 2 | ±2.5 V | 0 to 5 V | 330 KS/s |
| 4 | ±1.25 V | 0 to 2.5 V | 330 KS/s |
| 8 | ±0.625 V | 0 to 1.25 V | 330 KS/s |

| OME-PCI-1800H & 1802H Analog Input Ranges | | | |
|---|-------------|--------------|------------|
| Gains | Bipolar (V) | Unipolar (V) | Throughput |
| 0.5 | ±10V | 0 to 10 V | 40 KS/s |
| 1 | ±5V | 0 to 10 V | 40 KS/s |
| 5 | ±1V | 0 to 1 V | 40 KS/s |
| 10 | ±0.5V | 0 to 1 V | 40 KS/s |
| 50 | ±0.1V | 0 to 0.1 V | 10 KS/s |
| 100 | ±0.05V | 0 to 0.1 V | 10 KS/s |
| 500 | ±0.01V | 0 to 0.01 V | 1 KS/s |
| 1000 | ±0.005V | 0 to 0.01 V | 1 KS/s |

The OME-DB-16R can be used with any of the OME-PCI-1802H/1802L/1800H/1800L/1602/1602F/1202H/1202L/1002H/1002L PCI-bus multifunction boards. The relays are energized by applying a 5 V signal to the appropriate relay channel on the 20-pin flat cable connector. Sixteen annunciator LEDs, one for each relay, light when their associated relay is activated. To avoid overloading the PC's power supply, this board provides a screw terminal connection for a power supply.

Software Development Kit

All data acquisition boards are supplied with a standard software development kit for Windows 98/NT/2000/XP. The software development kit includes DLL files for programming in C, C++, or other high-level languages, and OCX files for Visual Basic or Active X programming. LabVIEW drivers are also included.

Specifications

ANALOG INPUT SPECIFICATIONS

Input Channels:

OME-PCI-1802H/L, 32 SE/16 Diff
OME-PCI-1800H/L, 16 SE/8 Diff

Resolution: 12 bits

Conversion Rate: 330 KS/s

Input Impedance:

10,000 MΩ/6 pf


Overvoltage Protection: ±35 V

Accuracy: 0.01% of reading, ±1 bit

On Board FIFO:

OME-PCI-1800 H/L: 2K

OME-PCI-1802 H/L: 8K



OME-DB-16R, \$149, shown smaller than actual size



OME-DB-16P, \$99, shown smaller than actual size

D/A OUTPUTS

Channels: 2

Type: 12-bit double buffers

Linearity: 0.06% FS

Settling Time: 0.4 ms

Output Range: ± 5 or ± 10 V

Output Driving: ± 5 mA

DIGITAL I/O

Input: 16 channels; TTL levels

Input Low:


$V_{IL} = 0.8$ V max

$I_{IL} = 4$ mA

Input High:

$V_{IH} = 2$ V min

$I_{IH} = -20$ μ A max



OME-PCI-1800H, \$759,
shown smaller than
actual size

Output: 16 channels; TTL levels

Output Low:

$V_{OL} = 0.5$ V max

$I_{OL} = 4$ mA max

Output High:

$V_{OH} = 2.7$ V min

$I_{OH} = -400$ μ A max

TIMER

Internal Pacer Timer:

16-bit, 8 MHz input

External Pacer Timer:

16-bit, 8 MHz input

Machine Independent Timer:

16-bit, 8 MHz input

GENERAL ENVIRONMENTAL

Power Requirements:

5 V @ 350 mA (max)

Operating Temperature:

0 to 50°C (32 to 122°F)

Storage Temperature:


-20 to 70°C (-4 to 158°F)

Humidity: 0 to 90% RH

non-condensing

Dimensions: 190 L x 105 mm H
(7.5 x 4.1")

OMEGACARESM extended warranty program
is available for models shown on this page.
Ask your sales representative for full details
when placing an order. OMEGACARESM
covers parts, labor and equivalent loaners



OME-DB-889D, \$359, shown
smaller than actual size

MOST POPULAR MODELS HIGHLIGHTED!

To Order (Specify Model Number)

| Model Number | Price | Description |
|----------------|-------|--|
| OME-PCI-1800H | \$759 | 16-channel, high-gain, 12-bit analog and digital I/O board (2K word FIFO) |
| OME-PCI-1800L | 759 | 16-channel, low-gain, 12-bit analog and digital I/O board (2K word FIFO) |
| OME-PCI-1802H | 849 | 32-channel, 330 KS/s, high-gain, 12-bit analog and digital I/O board (8K word FIFO) |
| OME-PCI-1802L | 849 | 32-channel, 330 KS/s, low-gain, 12-bit analog and digital I/O board (8K word FIFO) |
| OME-DB-1825/1 | 99 | Screw terminal board for analog input channels for OM-PCI-1802H/L, with 1 meter cable |
| OME-DB-1825/2 | 109 | Screw terminal board for analog input channels for OM-PCI-1802H/L, with 2 meter cable |
| OME-DB-8225/1 | 89 | Screw terminal board for analog input channels for OM-PCI-1800H/L, with 1 meter cable |
| OME-DB-8225/2 | 99 | Screw terminal board for analog input channels for OM-PCI-1800H/L, with 2 meter cable |
| OME-DB-8025 | 69 | Screw terminal board for digital I/O, includes two 1 m cables |
| OME-DB-889D | 359 | 16-channel analog multiplexer board, includes 1 m cable |
| OME-DB-16P | 99 | 16-channel isolated digital input board, includes 1 m cable |
| OME-DB-16R | 149 | 16-channel SPDT relay board, includes 1 m cable |
| OME-ADP-20/PCI | 39 | 20-pin extender (extends the dual 20-pin digital I/O flat cable connectors on the board to the PC slot window, includes two 20-pin cables) |

Each OME-PCI-1800 Series data acquisition board includes complete operator's manual on CD ROM and software development kit.

Ordering Example: OME-PCI-1802H 32-channel high-gain data acquisition board, OME-DB-8225/1 screw terminal board and cable and OMEGACARESM 1-year extended warranty for OME-PCI-1802H (adds 1 year to standard 1-year warranty), \$849 + 89 + 80 = \$1018.

omega.co.uk®

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

www.omega.co.uk



UNITED STATES

www.omega.com

1-800-TC-OMEGA

Stamford, CT.

CANADA

www.omega.ca

Laval(Quebec)

1-800-TC-OMEGA

GERMANY

www.omega.de

Deckenpfronn, Germany

0800-8266342

UNITED KINGDOM

www.omega.co.uk

Manchester, England

0800-488-488

FRANCE

www.omega.fr

088-466-342

CZECH REPUBLIC

www.omegaeng.cz

Karviná, Czech Republic

596-311-899

BENELUX

www.omega.nl

0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters