


OM-CP-RHTEMP1000 Humidity and Temperature Data Logger Part of the NOMAD® Family



\$399

Basic Unit



- ✓ Real Time Operation
- ✓ User Calibration through Software
- ✓ Dew Point/Vapor Concentration Calculated in Software

This OM-CP-RHTEMP1000 humidity and temperature data logger is a water proof (temperature measurement only), battery powered, stand-alone device used for automatically recording temperatures from -40 to 80°C. This all-in-one compact, portable, easy to use device will measure and record up to 21,845 temperature and 21,845 humidity measurements.

The OM-CP-RHTEMP1000 is a major leap forward in both size and performance. Its real time clock ensures that all data is time and date stamped. The storage medium is non-volatile solid state memory, providing maximum data security even if the battery becomes discharged. Its small size allows it to fit almost anywhere. Data retrieval is simple. Plug it into an empty COM port and the easy to use Windows software does the rest. The software converts your PC into a real time strip chart recorder. Data can be printed in tabular format and can also be exported to a text or Microsoft Excel file.

Specifications TEMPERATURE CHANNEL PERFORMANCE

Temperature Sensor: Semiconductor
Temperature Measurement Range: -40 to +80°C (-40 to 176°F)¹
Temperature Resolution: 0.1°C
Calibrated Accuracy: ±0.5°C
Specified Accuracy Range: 0 to +50°C

HUMIDITY CHANNEL PERFORMANCE

Humidity Sensor: Solid state semiconductor^{4,5}
Humidity Measurement Range: 0 to 100% RH

OM-CP-RHTEMP1000, \$399, data logger shown larger than actual size

Humidity Resolution: 0.5% RH
Calibrated Accuracy: ±3 %RH (±2 %RH typical at 25°C)
Specified Accuracy Range: 10 to 80 %RH +10 to + 40°C^{2,3}

Humidity Response Time: 90% of change in 60 seconds in slow moving air
General Specifications
Readings: 21,845 readings/channel

Temperature/Humidity Calibration: Digital calibration is available through software
Calibration Date: Automatically recorded within device

Recording Interval: 30/minute to 2 day selectable through software
Start Time: Start time & date are programmable through software, up to 6 months in advance

Real Time Recording: Device may be used with PC to monitor and record data in real time
Power: 3.6 V lithium battery (included)

Battery Life: 1 year typical at 25°C

Time Accuracy: ±1 minute per month at 20°C, RS-232 port not in use

Data Format: Date and time stamped, °C, °F, °K, °R %RH, mg of water vapor concentration,
Weight:

Aluminum: 145 g (5 oz);
 Stainless steel: 285 g (10 oz)

Computer Interface: PC serial, RS-232C COM or USB (interface cable required)

Software: WIN98/NT/2000/XP/VISTA 32-bit (VISTA 32-bit version only; VISTA 64-bit is not supported)

Operating Environment: -40 to 80°C¹ (-40 to 176°F)
 0 to 100% RH non-condensing when case is properly sealed

Dimensions: 25 mm dia x 137 mm L (1.00 x 5.40")

Material: Aluminum or stainless steel

ALL MODELS AVAILABLE FOR FAST DELIVERY!

To Order (Specify Model Number)		
Model No.	Price	Description
OM-CP-RHTEMP1000	\$399	Humidity and temperature data logger (aluminum)
OM-CP-RHTEMP1000-SS	449	Humidity and temperature data logger (stainless steel)
OM-CP-IFC110	99	Windows software and 1.2 (4') RS-232 cable with DB9F termination
OM-CP-IFC200	119	Windows software and 3.7 (12') USB interface cable
OM-CP-BAT102	10	Replacement 3.6 V lithium battery

Operator's manual and RS-232 cable are included with the OM-CP-IFC110 Windows software (software sold separately). (software is required to operate the data logger and is sold separately). NIST calibration for temperature only.

¹ The recommended operating temperature is 0 to +80°C
² Humidity accuracy is not specified in condensing environments
³ Extended exposure to > 90%RH results in a temporary 3 %RH error
⁴ The sensor is light sensitive-bright light may effect measurement
⁵ Submerging the sensor in any liquid may cause permanent damage

Ordering Example: OM-CP-RHTEMP1000-CERT humidity and temperature data logger with NIST calibration certificate and OM-CP-IFC110 Windows software and RS-232 cable, \$399 + 60 + 99 = \$558.

omega.co.uk[®]

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

www.omega.co.uk



UNITED STATES

www.omega.com

1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca

Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de

Deckenfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk

Manchester, England
0800-488-488
+44-(0)161-777-6611

FRANCE

www.omega.fr

0800-466-342

BENELUX

www.omega.nl

0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485, Ethernet and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters