


32-Channel Single-Ended Isolated Analog Input Board

OME-PISO-813

\$339
Basic Unit



- ✓ PCI Bus
- ✓ 12-Bit A/D
- ✓ 32 Single-Ended Analog Input Channels
- ✓ 3,000 Vdc Photo-Isolation Protection
- ✓ Analog Input Ranges:
Bipolar: ± 10 V, ± 5 V, ± 2.5 V, ± 1.25 V, ± 0.625 V
Unipolar: 0 to 10 V, 0 to 5 V, 0 to 2.5 V, 0 to 1.25 V, 0 to 0.625 V
- ✓ Programmable Gain Control (1, 2, 4, 8, 16)
- ✓ A/D Trigger Mode: Software Trigger
- ✓ A/D Data Transfer Mode: Polling



OME-PISO-813, \$339, shown smaller than actual size

Specifications

ANALOG INPUTS
Channels: 32 single-ended
Resolution: 12-bits
Conversion Rate: 10 KS/s max
Input Impedance: 10 M Ω
Overvoltage Protection: ± 35 V
Accuracy: 0.01% of reading ± 1 bit
Linearity: ± 1 bit
Sample & Hold: on chip
Zero Drift: ± 25 ppm/ $^{\circ}$ C of FS max
Power Requirements: +5 V @ 850 mA max
A/D Trigger Mode: Software trigger
A/D Data Transfer Mode: Polling

GENERAL ENVIRONMENTAL

Operating Temperature: 0 to 50 $^{\circ}$ C (32 to 122 $^{\circ}$ F)
Storage Temperature: -20 to 70 $^{\circ}$ C (-4 to 158 $^{\circ}$ F)
Humidity: 0 to 90% RH non-condensing
Dimensions: 180 L x 105 mm H (7.1 x 4.1")
Connector: 37-pin D-sub female

OMEGACARESM extended warranty program is available for models shown on this page. Ask your sales representative for full details when placing an order. OMEGACARESM covers parts, labor and equivalent loaners.

The OME-PISO-813 is an isolated 12-bit A/D board for the PCI bus for IBM or compatible PC. It features a 10 KHz data acquisition rate under DOS and Windows. The OME-PISO-813 provides 32 single-ended analog inputs and has 3000 Vdc photo-isolation from the PC (no channel-to-channel isolation).

Software Development Kit

The OME-PISO-813 is supplied with a standard software development kit for Windows 98/NT/2000/XP. The software development kit includes DLL files for programming in C, C++ or other high level languages and OCX files for Visual Basic or Active X programming. DasyLab and LabView drivers are also included.

AVAILABLE FOR FAST DELIVERY!

To Order (Specify Model Number)		
Model Number	Price	Description
OME-PISO-813	\$339	32-channel isolated analog input board
OME-DB-8325/1	79	Screw terminal board with signal conditioning circuitry (includes 1 m (3') D-sub 37-pin ribbon cable)
OME-DB-8325/2	89	Screw terminal board with signal conditioning circuitry (includes 2 m (6.5') D-sub 37-pin ribbon cable)
OME-DB-37	69	Direct connect 37-pin terminal board
OME-DN-37	79	DIN rail mount I/O connector block with 37-pin D-sub connector, includes 1 m (3') cable

Each OME-PISO-813 data acquisition board includes complete operator's manual on CD ROM and software development kit.

Ordering Example: OME-PISO-813 32-channel isolated analog input board, OME-DB-8325/1 screw terminal board with 1 m cable and OMEGACARESM 1 year extended warranty for OME-PISO-813 (adds 1 year to standard 1 year warranty), \$315 + 70 + 31 = \$416.

omega.co.uk[®]

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

www.omega.co.uk



UNITED STATES

www.omega.com

1-800-TC-OMEGA
Stamford, CT.

UNITED KINGDOM

www.omega.co.uk

Manchester, England
0800-488-488
+44-(0)161-777-6611

CANADA

www.omega.ca

Laval(Quebec)
1-800-TC-OMEGA

FRANCE

www.omega.fr

0800-466-342

GERMANY

www.omega.de

Deckenfronn, Germany
0800-8266342

BENELUX

www.omega.nl

0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485, Ethernet and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters