


OMB-DBK4

2-Channel Dynamic Signal-Input Card for OMB-DAQBOARD-2000 Series and OMB-LOGBOOK

Model OMB-DBK4
\$999



OMB-DBK4, \$999, 2-channel dynamic signal-input card, shown smaller than actual size

- ✔ Offers a Per-Channel Programmable Gain Amplifier for ± 50 mV, ± 500 mV, or ± 5 V FS Input
- ✔ Includes a Built-In Current Source for ICP Transducer Biasing
- ✔ Offers Per-Channel Anti-Aliasing Filters
- ✔ Provides Per-Channel Simultaneous Sample and Hold
- ✔ Accommodates Either AC or DC Coupled Signals
- ✔ Both Dynamic Analog Inputs Sampled Within 50 ns of Each Other

The 2-channel OMB-DBK4 dynamic signal-input card enables OMB-LOGBOOK and OMB-DAQBOARD-2000 Series data acquisition systems to accommodate inputs from piezoelectric transducers, such as accelerometers or microphones, as well as from various other dynamic signal sources. Each OMB-DBK4 card is equipped with two BNC connectors and footprints for two user-installed Microdot connectors, permitting it to easily accommodate most transducer connections.

Up to 128 cards can be attached to one OMB-LOGBOOK or OMB-DAQBOARD-2000 Series, for a total of 256 dynamic signal inputs.

Architecture

The OMB-DBK4 provides per-channel, constant current source outputs, programmable gain amplifiers, programmable anti-aliasing filters, and sample and hold amplifiers.

Specifications

Channels: 2

Connectors: DB37 male, 1 BNC per channel, and footprints for one user-provided Microdot connector per channel

Current Source:

Output Impedance: >1.4 M Ω

Compliance: 27 V

Current Levels: 2 and 4 mA (jumper selectable)

Input Impedance: 150 K Ω

Input Ranges:

± 50 mV, ± 500 mV, and ± 5 V FS; additional full scale ranges

are available when combined with the OMB-LOGBOOK's or OMB-DAQBOARD-2000 Series on-board programmable A/D ranges

Coupling: AC and DC

AC High-Pass Filters:

Per-channel, 1-pole HPF with 10 Hz or 0.1 Hz cutoff, selectable via jumper

Input Signal/Noise:

>96 dB (BW=100 kHz)

Amplitude Accuracy:

± 0.5 dB passband center

Low-Pass Filter:

Software selectable, 12-pole Butterworth filter, with cutoff frequencies of 18 kHz, 9 kHz, 4.5 kHz, 2.25 kHz, 1.125 kHz, 562.5 Hz, 281.2 Hz, and 141.6 Hz; each channel can be configured for a different cutoff frequency

Power Consumption: 2750 mW

(When multiple OMB-DBK4 cards are used, an OMB-DBK32A auxiliary power supply may be required.)

Cables:

Use OMB-CA-37-x cable with OMB-LOGBOOK and OMB-DAQBOARD-2000 Series

AVAILABLE FOR FAST DELIVERY!

To Order (Specify Model Number)		
Model Number	Price	Description
OMB-DBK4	\$999	2-Channel Dynamic Signal-Input Card

Ordering Example: OMB-DBK4 2-channel dynamic signal-input card, \$999.

omega.co.uk®

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

www.omega.co.uk



UNITED STATES

www.omega.com

1-800-TC-OMEGA

Stamford, CT.

CANADA

www.omega.ca

Laval(Quebec)

1-800-TC-OMEGA

GERMANY

www.omega.de

Deckenpfronn, Germany

0800-8266342

UNITED KINGDOM

www.omega.co.uk

Manchester, England

0800-488-488

FRANCE

www.omega.fr

088-466-342

CZECH REPUBLIC

www.omegaeng.cz

Karviná, Czech Republic

596-311-899

BENELUX

www.omega.nl

0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters