



4-Range Portable Conductivity Meter Kits

CDH-280-KIT
\$627



Shown smaller than actual size.

CDH-280-KIT is supplied with meter, glass dip-style conductivity probe with cell constant of 1.0 and integral temperature sensor, sample bottle, calibration solution, battery, rugged carrying case and operator's manual.



AVAILABLE FOR FAST DELIVERY!

The CDH-280 conductivity meter is a basic, simple-to-operate instrument with four user-selectable ranges. It features automatic temperature compensation, a fixed 2%/°C temperature coefficient and a rugged splashproof enclosure. The CDH-280-KIT is a complete kit including a glass conductivity cell with an integral temperature sensor and cell constant of 1.0. The meter measures from a low range of 0 to 199.9 $\mu\text{S}/\text{cm}$ up to 0 to 199.9 mS/cm . Both dip and flow cells with cell constants from 0.1 to 10 are compatible with the CDH-280. These sensors are available with glass, epoxy or polymer bodies.

Specifications

Conductivity Range and Resolution:

0 to 199.9 $\mu\text{S}/\text{cm}$; 0 to 1.999 mS/cm ;
0 to 19.99 mS/cm ; 0 to 199.9 mS/cm

Accuracy: $\pm 1\%$ of reading (meter only)

Automatic Temperature Compensation:
0 to 50°C (32 to 122°F)

Reference Temperature: 25°C (77°F)

Temperature Coefficient: 2%/°C

Power: 9 V battery (included)

Dimensions: 100 L x 180 W x 44 mm D
(3.94 x 7.09 x 1.73")

Instrument Display: 12.7 mm (0.5") LCD

Weight: 365 g (0.8 lb)

To Order (Specify Model Number)

Model No.	Price	Description
CDH-280-KIT	\$627	Conductivity meter, glass dip-style conductivity probe with integral temperature sensor, K = 1.0 and carrying case
CDE-5001-GD1	156	Replacement conductivity probe, glass dip-style, K = 1.0 with ATC, platinum plates, 12 x 130 mm (0.5 x 5.1")
CDE-5002-PD1	140	Polymer dip-style probe, K = 1.0 with ATC, platinum plates, 12 x 130 mm (0.5 x 5.1")
CDE-5004-ED10	326	Epoxy dip-style probe, K = 10 with ATC, carbon plates, 26 D x 353 mm L (1 x 13.9")
CDE-5005-GF1	178	Glass flow cell, K = 1.0 with ATC, platinum plates, 13 x 166 mm (0.5 x 6.5") overall length, 5 mm (0.2") tubing connections, 33 mm (1.3") cell head, 4 mL minimum volume
CDE-5008-EF10	378	Epoxy flow cell, K = 10 with ATC, carbon plates, 26 x 203 mm (1.0 x 8.0") with 10.5 mm (0.4") tubing connections, 353 mm (13.9") overall length, 13 mL volume
CDE-5010-ED1	312	Epoxy dip-style probe, K = 1 with ATC, carbon plates, 26 x 250 mm L (1.0 x 9.8")
CDE-5011-ED01	290	Epoxy dip-style probe, K = 0.1 with ATC, carbon plates, 26 x 216 mm (1.0 x 8.5")
CDE-5012-EF1	366	Epoxy flow cell, K = 1.0 with ATC, carbon plates, 26 x 100 mm (1.0 x 3.9") with 10.5 mm (0.4") tubing connections, 250 mm (9.8") overall length, 26 mL volume
CDE-5014-GD01	160	Glass dip-style probe, K = 0.1 with ATC, platinum plates, 20 x 130 mm (0.8 x 5.1")
CDE-5019-ED1	140	Epoxy dip-style probe, K = 1.0 with ATC, carbon plates, 12 x 110 mm (0.5 x 4.3")
MN6104	3	Replacement 9V battery

CDH-280-KIT comes complete with meter, glass dip style conductivity probe with cell constant of 1.0 and integral temperature sensor, sample bottle, calibration solution, 9V battery, rugged carrying case, and operator's manual.

See page E-16 for recommended ranges vs cell constants.

Ordering Examples: CDH-280-KIT, portable conductivity meter and accessories, and CDE-5008-EF10, epoxy flow cell, \$627 + 378 = \$1005.

CDH-280-KIT, portable conductivity meter and accessories, CDE-5011-ED01, conductivity probe with cell constant of 0.1 cell, \$627 + 290 = \$917.

omega.co.uk[®]

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

www.omega.co.uk



UNITED STATES

www.omega.com

1-800-TC-OMEGA
Stamford, CT.

UNITED KINGDOM

www.omega.co.uk

Manchester, England
0800-488-488
+44-(0)161-777-6611

CANADA

www.omega.ca

Laval(Quebec)
1-800-TC-OMEGA

FRANCE

www.omega.fr

0800-466-342

GERMANY

www.omega.de

Deckenfronn, Germany
0800-8266342

BENELUX

www.omega.nl

0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485, Ethernet and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters