

MINI-FLOW SENSORS

FP-5070
\$684

All Models



- ✓ **New Higher Resolution Design**
- ✓ **Accurate Low Flow Measurements to 500 ml/min**
- ✓ **Easily interfaced, Open Collector Output**
- ✓ **Wide Temperature Range -30 to 120°C (-22 to 248°F)**



FP-5072-PV, \$684, shown larger than actual size.

The OMEGA® FP-5070 Mini-Flow sensor is ideal for precision low flow monitoring. The FP-5070 is available in four flow range configurations, covering a very wide range of flows. This allows for easy selection of the range that best fits your application. Typical applications include pilot plant installations, monitoring of critical flows in laboratories, fluid dispensing, bottling lines, and medical flow applications. Other successful applications include monitoring liquid ingredient additions, such as food dyes, in the food processing industry.

SPECIFICATIONS

Accuracy: ±2% of flowrate

Linearity: ±0.25% of flowrate

Reproducibility: ±0.25% of flowrate

Pressure Rating:

80 psig @ -30°C (-22°F);

45 psig @ 120°C (248°F)

Temperature Range:

-30 to 120°C (-22 to 248°F)

Viscosity Range: 0.2 to 20.0 cSt

Power: 5 to 24 Vdc @ 10 mA

maximum, 3-wire

Wetted Materials: PVDF, PTFE and FKM

Pressure Drop: 10 psid @ 50% flow,

26 psid @ 100% flow

Signal Output:

5 Volt, open collector pulse


Fluid Connections: ¼ FNPT

Cable Length: 7.5 m (25'), resistor required 10 kΩ recommended

Dimensions: 95 lay length x 66 H x 68 mm W (3.74 x 2.6 x 2.68")

Shipping Weight: 0.4 kg (0.8 lb)

Compatible Meters:
 DPF700 (page M-5), DPF70 (page M-22),
 FPM-5500 (page F-43), FPM-5750 (page F-41)



MOST POPULAR MODELS HIGHLIGHTED!

To Order (Specify Model Number)

Model No.	Price	Range (mL/min)	Range (GPM)	Nominal K Factor (pulses/mL)
FP-5072-PV	\$684	400 to 2800	0.150 to 0.740	1.502
FP-5073-PV	684	700 to 4200	0.185 to 1.110	0.874
FP-5074-PV	684	1300 to 6000	0.343 to 1.585	0.612
FP-5076-PV	684	3200 to 12000	0.845 to 3.170	0.330

Accessory

Model No.	Price	Description
DPF701	\$260	Rate or total panel meter

Comes complete with operator's manual.

Ordering Examples: FP-5074-PV, mini-flow sensor up to 6000 mL/min, \$684.

FP-5076-PV, mini-flow sensor up to 12000 mL/min, and DPF701, meter, \$684 + 260 = \$944.

Recommended Reference Book: Piping Calculations Manual, FW-304, \$100. See Section Y for Additional Books.



omega.co.uk[®]

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

www.omega.co.uk



UNITED STATES

www.omega.com

1-800-TC-OMEGA
Stamford, CT.

UNITED KINGDOM

www.omega.co.uk

Manchester, England
0800-488-488
+44-(0)161-777-6611

CANADA

www.omega.ca

Laval(Quebec)
1-800-TC-OMEGA

FRANCE

www.omega.fr

0800-466-342

GERMANY

www.omega.de

Deckenfronn, Germany
0800-8266342

BENELUX

www.omega.nl

0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485, Ethernet and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters