

OMB-DBK41

10-Slot Expansion Module

for OMB-LOGBOOK and OMB-DAQBOARD-2000 Series



Model OMB-DBK41

\$879



The OMB-DBK41, \$879, analog expansion module accommodates various signal conditioning expansion cards in one system



The OMB-DBK41, \$879, provides slots for up to 10 analog expansion cards

- ✓ Accepts up to Ten OMB-DBK Analog Expansion Cards
- ✓ Features Analog Backplane, Eliminating the Need for a Cascaded Ribbon Cable
- ✓ Enables Easy Card Installation
- ✓ Features Rugged All Metal Construction for Portable Applications

The OMB-DBK41 analog expansion module allows OMEGA's OMB-LOGBOOK and OMB-DAQBOARD-2000 Series data acquisition systems to be expanded with any combination of up to ten OMB-DBK series analog expansion cards.

The OMB-DBK41's metal enclosure features an analog backplane into which the OMB-DBK series expansion cards can be easily installed.

The OMB-DBK41 features industrial-strength Velcro-style tabs that enable you to mount a OMB-LOGBOOK and a notebook PC on top of it.

Power Requirements

OMB-DBK series analog cards housed within the OMB-DBK41 can obtain their power from your OMB-LOGBOOK or OMB-DAQBOARD-2000 Series internal power supply, or the OMB-CDK10 battery and power supply module. However, depending on the combination and number of cards installed within the unit, the OMB-DBK32A or OMB-DBK33 optional power supply card may sometimes be required for adequate power.

The OMB-DBK32A or OMB-DBK33 can obtain its power from a number of sources: an included AC adapter, an optional OMB-DBK30A rechargeable battery/excitation module, OMB-DBK34 battery/UPS module, or any 9 to 20 Vdc source, such as an automobile battery.

Packaging

You can stack the OMB-DBK41 beneath an OMB-LOGBOOK

portable data acquisition module via included fastener panels, which are available with an optional screw-in handle. The result is a compact and securely connected data acquisition system that you can conveniently carry from one application site to another.

SPECIFICATIONS

Connector: DB37 male, mates with P1 pinout on the OMB-LOGBOOK or OMB-DAQBOARD-2000 Series

Card Capacity: 10 positions

Power Indicator: LED powered by OMB-DAQBOARD-2000 Series 5 Vdc

Dimensions:

253 x 286 x 91 mm (9.75 x 11 x 3.5")
253 x 494 x 91 mm (9.75 x 19 x 3.5")
with optional OMB-DBK-1 rack mount kit installed

Weight: 1.8 kg (4 lb) with no cards installed

ALL MODELS AVAILABLE FOR FAST DELIVERY!

| To Order (Specify Model Number) | | |
|---------------------------------|-------|---------------------------------|
| Model Number | Price | Description |
| OMB-DBK41 | \$879 | 10-Slot Analog Expansion Module |

Ordering Example: OMB-DBK41 is a 10-slot analog expansion module, \$879.

omega.co.uk[®]

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

www.omega.co.uk



UNITED STATES

www.omega.com

1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca

Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de

Deckenfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk

Manchester, England
0800-488-488
+44-(0)161-777-6611

FRANCE

www.omega.fr

0800-466-342

BENELUX

www.omega.nl

0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485, Ethernet and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters