

# THERMAL DISPERSION FLOW SWITCHES

FSW-6000/7000 Series  
Starts at

**\$456**



FSW-6212, \$456, shown smaller than actual size.

- ✔ **Simple to Install and Low Cost**
- ✔ **No Moving Parts—Maintenance Free Reliability**
- ✔ **Optimal Temperature Compensation—Unaffected by Temperature Gradient**
- ✔ **Can Operate in Temperatures up to 120°C (248°F) with Sanitary Option**
- ✔ **300 Bar (4300 psi) Maximum Working Pressure**
- ✔ **Chain of 8 LEDs—Integrated Flow Rate/Setpoint Indication**
- ✔ **Can Be Used as a Level Switch**

The FSW-6000/7000 Series are thermal flow switch monitors designed to monitor flow status and also used to detect level of liquids, air and gas. A chain of 8 LEDs gives the user a visual indication of the flow rate. In addition, there is

also a dichromatic LED, which shows the switch point status of the unit. The sensing element and connection of the FSW-6000/7000 Series are made with 316 SS and can be coated with PTFE as an option. The standard enclosure is glass-filled nylon and is also available in an aluminum enclosure for hazardous environments. The FSW-6000/7000 Series can be made with a great variety of process connections such as threaded, flange, or sanitary.

The FSW-6000/7000 Series line of thermal flow switch monitors is based on the principle of thermal dispersion. A typical configuration uses two platinum Resistance Temperature Detectors (RTDs) set within the tip of the sensor. One RTD is heated a few degrees above the temperature of the medium and the other RTD is used as a reference, sensing the actual process temperature. The second RTD also monitors the temperature of the medium, as any changes in temperature must be compensated for in the first RTD. As the process medium flows over the tip of the sensor it disperses some of the

heat from the first RTD. The temperature change between the two RTD's signals the probe's electronics and the switch changes state once the setpoint has reached.

The FSW-6000/7000 Series may be installed in a pipe or tank using the thread or connection provided. Use only the hexagon when tightening to achieve a seal, do not use the body. The body should be rotated after tightening to leave the cable gland in suitable orientation. The FSW-6000/7000 Series is not affected by its fixing position so it may be installed at any angle around the pipe. However, it is recommended that with horizontal pipe runs the sensor should be installed on the side, into the middle of the pipe. In vertical pipes, the FSW-6000/7000 Series should be installed when there is flow in an upward direction against gravity. Care should be taken when installing the sensor that the probe extends clear of the pipe's internal wall and is fully immersed into the flow. In pipes with smaller diameters, some care should also be taken so that the sensor is not screwed too far into the line.

**SPECIFICATIONS**

**Accuracy:** ±10% of setpoint

**Repeatability:** ±1% of setpoint

**Power Supply:**

**FSW-6000:** 85 to 240 Vac (50/60 Hz)

**FSW-7000:** 24 Vdc ±10%

**Temperature Range:**

**Process:** -20 to 80°C (-4 to 176°F)

[sanitary option to 120°C (248°F) for CIP]

**Operating:** -20 to 60°C (-4 to 140°F)

**Max Pressure:** 300 bar (4351 psi)

**Protection Class:** NEMA 4 (IP65)

**Wetted Materials:** 316 SS

**Enclosure Material:** Glass filled nylon standard or aluminum die cast option

**Process Connection:**

½ to 1½ NPT, Tri-Grip™, or flange

(others available, consult Flow Engineering Department)

**Output:** 250 Vac SPDT 5 A relay

**Switch Point Adjustment:** Potentiometer

**Bargraph:**

**Green LED:** Flow rate above setpoint

**Yellow LED:** Flow is at above setpoint

**Red LED:** Flow is below setpoint

**Switch Point Status:**

**Red LED:** No flow

**Green LED:** Flow

**Response Time:** 1 to 10 seconds

**Max Start up Delay:** 12 seconds

**Switching Range:**

3 cm/s to 3 m/s (0.09 to 9.84 ft/sec)

(liquid), 5 cm/sec to 15 m/sec

(0.16 to 49 ft/sec) (gas)

**Dimensions:**

**Nylon Head:** 88 Dia x 80 mm H (3.5 x 2.5" H)

**Aluminum Head:** 88 Dia x 108 mm H (3.5 x 4.25")

**Insertion Length:** 1", 2 and 3" standard, for other lengths consult Flow Engineering

**Weight:** Approx 680 g (1.5 lb)

**AVAILABLE FOR FAST DELIVERY!**

<b>To Order (Specify Model Number)</b>					
Model No.	Price	Description	Process Connection	Enclosure	Insertion Length
<b>FSW-6212</b>	<b>\$456</b>	Thermal dispersion flow switch, 85 to 240 Vac power	¾ NPT	Glass filled nylon, ½ NPT conduit, cable gland, and 2 m (6.5') cable	51 mm (2") for 1 to 4" pipe
<b>FSW-7112</b>	<b>456</b>	Thermal dispersion flow switch, 24 Vdc power	½ NPT	Glass filled nylon, ½ NPT conduit, cable gland, and 2 m (6.5') cable	51 mm (2") for 1 to 4" pipe
<b>FSW-7111</b>	<b>456</b>	Thermal dispersion flow switch, 24 Vdc power	½ NPT	Glass filled nylon, ½ NPT conduit, cable gland, and 2 m (6.5') cable	35 mm (1⅜") for ½ to 1" pipe

**Accessories**

Model No.	Price	Description
<b>70A-1</b>	<b>\$20</b>	Continuous tone alarm
<b>TX4-100</b>	<b>35</b>	4-conductor wire, 30.5 m (100') spool
<b>U24Y175</b>	<b>169</b>	24 Vdc power supply

Recommended Reference Book:  
Valve Handbook,  
**FW-306, \$125.**   
See Section Y for Additional Books

**Build to Order Models**

Model No.	Price	Description
<b>FSW-6(*)(**)(***)</b>	<b>\$432</b>	Flow switch, 85 to 240 Vac power; specify connection (*), enclosure (**) and insertion length (***)
<b>FSW-7(*)(**)(***)</b>	<b>432</b>	Flow switch, 24 Vdc power; specify connection (*), enclosure (**) and insertion length (***)

**Options**

Ordering Suffix	Add'l Price	Description
<b>Process Connection (*)</b>		
<b>1</b>	<b>N/C</b>	½ NPT thread
<b>2</b>	<b>N/C</b>	¾ NPT thread
<b>3</b>	<b>N/C</b>	1 NPT thread
<b>5</b>	<b>\$150</b>	1.5" Tri-Grip™
<b>6</b>	<b>300</b>	2" ANSI flange, 15016 316 SS
<b>Enclosure (**)</b>		
<b>1</b>	<b>\$24</b>	Glass filled nylon with ½ NPT conduit, cable gland, and 2 m (6.5') cable
<b>2</b>	<b>84</b>	Aluminum die cast with ½ NPT conduit
<b>3</b>	<b>90</b>	Aluminum die cast with cable gland
<b>Insertion Length (***)</b>		
<b>1</b>	<b>N/C</b>	35 mm (1⅜")
<b>2</b>	<b>N/C</b>	50 mm (2")
<b>3</b>	<b>N/C</b>	75 mm (3")



Comes complete with operator's manual.

To order ECTFE/ETFE element coating, add suffix **"-ETFE"** to model number and **\$180** to price.

**Ordering Examples:** **FSW-6212**, flow switch, 85 to 240 Vac power, ¾ NPT fitting, glass filled nylon, 51 mm (2") insertion length, and **70A-1**, alarm, \$456 + 20 = **\$476**.

**FSW-7113**, flow switch, 24 Vdc power, ½ NPT fitting, glass filled nylon, 75 mm (3") insertion length, **\$456**.

**FSW-6000 flow switches are available with 1.5" Tri-Grip™ (Tri-Clamp® compatible) connection for sanitary applications.**

# omega.co.uk<sup>®</sup>

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

[www.omega.co.uk](http://www.omega.co.uk)



#### UNITED STATES

[www.omega.com](http://www.omega.com)

1-800-TC-OMEGA  
Stamford, CT.

#### UNITED KINGDOM

[www.omega.co.uk](http://www.omega.co.uk)

Manchester, England  
0800-488-488  
+44-(0)161-777-6611

#### CANADA

[www.omega.ca](http://www.omega.ca)

Laval(Quebec)  
1-800-TC-OMEGA

#### FRANCE

[www.omega.fr](http://www.omega.fr)

0800-466-342

#### GERMANY

[www.omega.de](http://www.omega.de)

Deckenfronn, Germany  
0800-8266342

#### BENELUX

[www.omega.nl](http://www.omega.nl)

0800-099-33-44



## More than 100,000 Products Available!

### • Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

### • Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

### • pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

### • Data Acquisition

Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485, Ethernet and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

### • Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

### • Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters