

# WIRELESS TRANSMITTERS AND RECEIVERS



## 48-CHANNEL WIRELESS DIN RAIL RECEIVER WITH 4 ANALOG OUTPUT AND ALARMS

UWTC-REC4

£184



UWTC-REC4, £184, shown actual size.

- ✓ Works with Up to 48 Wireless Transmitters
- ✓ Four 0 to 5 Vdc, 0 to 10 Vdc or 4 to 20 mA Analogue Outputs
- ✓ Interface Directly to PLCs, Chart Recorders and Data Loggers
- ✓ Standard DIN Rail Enclosure
- ✓ Built-in Programmable Alarms for Each Channel
- ✓ Field Programmable via USB
- ✓ Included Software Turns a PC Into a Multi-Channel Meter, Chart Recorder or Data Logger

### Works with:

- UWTC—Thermocouple
- UWRTD—RTD
- UWRH—Humidity
- UWIR—Infrared Temperature
- UWPH—pH
- UWPC—Process Voltage/Current Wireless Transmitters



The UWTC-REC4 wireless DIN rail receiver can work with up to 48 wireless transmitters, displaying their data in real time on your PC. The UWTC-REC4 also has four independent analog outputs, which can be user-programmed as a retransmission signal from any input

channel, driving a PLC or data logger. The UWTC-REC4 is compatible with the full line of UW wireless transmitters from Omega; choose from thermocouple, RTD, %RH, infrared (non-contact) temperature, pH, as well as process voltage/current models.

The standard DIN rail mount design provides for easy mounting, and fast connections to other DIN rail equipment, including PLCs. The optional iDRN-PS-1000 power supply can power up to three UWTC-REC4 units, which can give you up to 144 wireless input channels, and 12 analogue outputs.

### Specifications

**Power:** 12 to 24 Vdc @ 250 mA

**Analogue Output:** 4 independent, non-isolated, retransmission 0 to 5 Vdc, 0 to 10 Vdc or 4 to 20 mA

**Alarms (Programmable):** One per channel, rising/falling activation

**Alarm Type:** Open drain, 100 mA max

**Power, Output, Alarm Connection:** Screw terminals

**Operating Ambient:** 0 to 55°C (32 to 131°F), 90% RH non-condensing

**Radio Frequency (RF) Transceiver Carrier:** ISM 2.4 GHz, direct sequence spread spectrum

**RF Data Packet Standard:** IEEE 802.15.4, open communication architecture

**Enclosure:** DIN rail (plastic)

**Dimensions:** 93 H x 39 W x 125 mm D (3.64 x 1.55 x 4.93")

Convenient DIN rail mount design simplifies installation and operation with PLCs and other instrumentation.

HE-XE102, £298, sold separately.


RAIL-35-1, £6.70, sold separately.



Shown smaller than actual size.

**Note:** The UWTC-REC4 can be powered directly by the PLC or data logger you are connecting to and will not require an additional power source if the instrument has 12 to 24 Vdc @ 250 mA available for external devices. If your instrument does not have a power source available for external devices you will need to add an additional power supply (iDRN-PS-1000, £101) to power the wireless receiver. This power supply can power up to 3 UWTC-REC4 receivers. Visit [omega.co.uk/wireless](http://omega.co.uk/wireless) for more information.

## Interfaces Directly with PLCs and Multi-Channel Data Loggers to Form a Complete Wireless Measurement and Control System!



**UWTC-2-NEMA**, thermocouple transmitter, £111.

**RD8802CD**, £1335.

**UWIR-2-NEMA**, infrared temperature transmitter, £117.

**RD9912**, £2145.

**UWRH-2-NEMA**, humidity/temperature transmitter, £157.

**HE-XE102**, programmable logic controller, £298.

**UWTC-2**, thermocouple connector, £90.

*Patents and Patents Pending*

Typical system shown above includes 4 wireless transmitters with one **UWTC-REC4-MA** wireless receiver with analog outputs, and XL Series PLC, £298.

**AVAILABLE FOR FAST DELIVERY!**

To Order (Specify Model Number)		
Model No.	Price	Description
<b>UWTC-REC4-(*)</b>	<b>£184</b>	48-channel DIN rail receiver with 4 analog outputs and alarms
<b>iDRN-PS-1000</b>	<b>101</b>	Power supply (switching) 95 to 240 Vac input, 24 Vdc output @ 850 mA (power 3 units)
<b>RAIL-35-1</b>	<b>6.70</b>	35 mm (1.4") DIN rail, 1 m (3.3') length
<b>RAIL-35-2</b>	<b>10</b>	35 mm (1.4") DIN rail, 2 m (6.6') length

Comes complete with measurement/data logging software, USB programming cable, and operator's manual.

\* Specify analogue output signal: "V1" for 0 to 5 Vdc; "V2" for 0 to 10 Vdc, "TC" for Type K thermocouple, or "MA" for 4 to 20 mA signal.

**Ordering Example: UWTC-REC4-MA**, 48-channel DIN rail receiver with four 4 to 20 mA outputs and alarms, £184.

# omega.co.uk<sup>®</sup>

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

[www.omega.co.uk](http://www.omega.co.uk)



#### UNITED STATES

[www.omega.com](http://www.omega.com)

1-800-TC-OMEGA  
Stamford, CT.

#### UNITED KINGDOM

[www.omega.co.uk](http://www.omega.co.uk)

Manchester, England  
0800-488-488  
+44-(0)161-777-6611

#### CANADA

[www.omega.ca](http://www.omega.ca)

Laval(Quebec)  
1-800-TC-OMEGA

#### FRANCE

[www.omega.fr](http://www.omega.fr)

0800-466-342

#### GERMANY

[www.omega.de](http://www.omega.de)

Deckenfronn, Germany  
0800-8266342

#### BENELUX

[www.omega.nl](http://www.omega.nl)

0800-099-33-44



## More than 100,000 Products Available!

### • Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

### • Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

### • pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

### • Data Acquisition

Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485, Ethernet and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

### • Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

### • Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters