




INDUSTRIAL pH INSTRUMENTATION & ELECTRONICS

Retractable Lock-N-Load ALPHA[®] pH/ORP Electrode Assemblies

LK Series
\$800
 Basic System



The retractable Lock-N-Load sensor assemblies are all you need to install a pH or ORP electrode into any pipeline. This is the first assembly that doesn't require ball valves, cables or costly, complex hardware to quickly insert or remove an electrode from a pipeline without interrupting the process. The simplicity of its design is what makes it unique. A quarter turn, a pull, and the electrode assembly is sealed from line pressure. The sensor can be removed to check calibration. It's safer to, because the end cap seals from the outside, unlike other insertion assemblies that rely upon valves and cables. Constructed of CPVC, PVDF or stainless steel allows this assembly to be used in waste water or process control. A wide selection of pH and ORP electrodes is available for the retractable sensor assembly. The electrodes feature a sealed gel-filled reference with an annular ceramic junction.



LKPHE-3592-10, \$97, electrode.



Shown smaller than actual size.

Lock-n-load assembly shown with PHCN-37 pH controller, \$395, see page D-22.

MOST POPULAR MODEL HIGHLIGHTED!

To Order (Specify Model Number)

Retractable Lock-N-Load Assembly

Model No.	Price	Material	Thread Size	Pressure Rating	Temperature Range °C (°F)
LK-CP	\$520	CPVC	1½ MNPT	100 psi	-5 to 80 (32 to 176)
LK-K	649	PVDF	1½ MNPT	100 psi	-5 to 100 (123 to 212)
LK-SS	779	316SS	1 MNPT	150 psi	-5 to 120 (123 to 248)



End cap seal and electrode, shown within pipe line. A quarter turn, and a pull seals the electrode assembly from line pressure.



Electrode can be easily replaced or re-calibrated without interfering with the process.

In-Line Flow Cell

MOST POPULAR MODELS HIGHLIGHTED!

Model No.	Price	Material	Pressure Rating	Temp. Rating °C (°F)	Electrode	Ports
LKFC-CP	\$118	CPVC	100 psi	-5 to 80 (23 to 176)	1½ NPT	2 NPT
LKFC-K	520	PVDF	100 psi	-5 to 100 (23 to 212)	1½ NPT	1 NPT
LKFC-SS	520	316SS	150 psi	-5 to 120 (23 to 248)	1 NPT	1 NPT

Flow Cell Installation Reducer Adaptors Reducer for Reducing CPVC and 316 SS Ports.

Model No.	Price	Material	Flow Cell Size	Port Size
LKFC-CP-1	\$20	CPVC	2" male socket	½ FNPT
LKFC-CP-2	20	CPVC	2" male socket	¾ FNPT
LKFC-CP-3	20	CPVC	2" male socket	1 FNPT
LKFC-CP-4	20	CPVC	2" male socket	1½ FNPT
LKFC-SS-1	90	316 SS	1 MNPT	½ FNPT
LKFC-SS-2	90	316 SS	1 MNPT	¾ FNPT

Temperature Compensator

Model No	Price	Description
LKTC-CP-10-(*)	\$45	CPVC ATC for use with LKFC-CP flow cell
LKTC-K-10-(*)	45	PVDF ATC for use with LKFC-K flow cell
LKTC-SS-10-(*)	45	316 SS ATC for LKFC-SS flow cell

* For temperature compensation specify: "PT100" for 100 Ω platinum RTD; "PT1000" for 1000 Ω platinum RTD; or "TH700" for 700 Series thermistor.

Electrodes

Model No.	Price	Description
LKPHE-3592-10	\$97	General purpose, single junction, temperature range -5 to 100°C, pH range 0 to 12
LKPHE-4576-10	94	High pH, single junction, temperature range -5 to 100°C, pH range 0 to 14
LKPHE-3781-10	109	Ideal for organic compounds which react with silver, double junction, temperature range -5 to 100°C, pH range 0 to 12
LKPHE-4739-10	114	Ideal for organic compounds which react with silver, double junction, temperature range -5 to 100°C, pH range 0 to 14
LKORE-9686-10	124	General purpose ORP, platinum band, single junction, temperature range -5 to 100°C
LKORE-9880-10	134	ORP ideal for compounds which react with silver, platinum band, double junction, temperature range -5 to 100°C

Comes complete with operator's manual.

All electrodes supplied with 3.3 m (10') cable and spade lug connections standard.

To order with BNC connector, add suffix "-BNC" to model number, and \$10 to price.

Ordering Example: LK-CP, retractable Lock-N-Load assembly, LKFC-CP, in-line flow cell, LKFC-CP-1, flow cell reducer adaptor, LKPHE-3592-10, general purpose pH electrode, LKTC-CP-10-PT100, CPVC ATC with 100 Ω RTD, \$520 + 118 + 20 + 97 + 45 = \$800.

omega.co.uk[®]

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

www.omega.co.uk



UNITED STATES

www.omega.com

1-800-TC-OMEGA
Stamford, CT.

UNITED KINGDOM

www.omega.co.uk

Manchester, England
0800-488-488
+44-(0)161-777-6611

CANADA

www.omega.ca

Laval(Quebec)
1-800-TC-OMEGA

FRANCE

www.omega.fr

0800-466-342

GERMANY

www.omega.de

Deckenfronn, Germany
0800-8266342

BENELUX

www.omega.nl

0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485, Ethernet and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters