



HANDHELD ROTATING VANE ANEMOMETER

HHF141
£535
 All Models



- ✓ High Accuracy (±1.0% of Reading)
- ✓ Rugged Metal Probe and Vane
- ✓ Ultra Low Sensitivity Down to 0.2 m/s (40 fpm)
- ✓ Vane sensors work in temperatures -20 to 100°C
- ✓ Minimum and Maximum Velocity Capture
- ✓ Analogue Voltage Output and Communication Options

The OMEGA® HHF141 rotating vane anemometer is a high-quality instrument providing highly accurate air velocity measurements in harsh environments via a user-friendly and intuitive interface. Applications include manufacturing, laboratory, computer rooms, environmental control, flow hood monitoring, and other applications where precise air measurement is required.

SPECIFICATIONS Ranges

HHF141A: 25 mm (1") probe, 60 to 6800 FPM (0.3 to 35.00 MPS)

HHF141B: 70 mm (2¾") probe, 40 to 7800 FPM (0.2 to 40.00 MPS)

Accuracy: ±1.0% of reading ±1-digit

Resolution: 1 FPM or 0.01 MPS

Display: 12.7 mm (0.5") LCD, 4-digits, with LED backlight

Operating Temp:

Instrument: 0 to 50°C (32 to 125°F)

Probe: -20 to 100°C (-4 to 212°F)

Power Supply: 3 "AA" alkaline batteries (included)

Battery Life: Approximately 150 hours

Dimensions:

Instrument: 165 x 83 x 38 mm (6.5 x 3.25 x 1.5")

HHF140A: 25 mm (1") diameter head

HHF140B: 70 mm (2.75") diameter head

Cable: 1.5 m (5')

Outputs (Optional): USB or 0 to 5 Vdc



AVAILABLE FOR FAST DELIVERY!

To Order (Specify Model Number)		
Model No.	Price	Description
HHF141A	£535	Handheld anemometer kit with 25 mm (1") dia probe
HHF141B	535	Handheld anemometer kit with 70 mm (2¾) dia probe

Accessories

Model No.	Price	Description
HHF140B-RP	£235	Replacement 70 mm (2¾") vane probe
HHF140A-RP	235	Replacement 25 mm (1") vane probe and 1.5 m (5') cable
HHF140B-CABLE	30	Replacement 1.5 m (5') connector cable
HHF140-USB-CABLE	30	Replacement USB cable
HHF140-V-CABLE	30	Replacement analogue output cable
MN1500-4	2	Package of 4 "AA" replacement batteries
OP-8	62	Reference Book: Industrial Flow Measurement

Comes complete with vane probe [25 or 70 mm (1 or 2¾") depending on model], 3 extension rods (flexible, straight and with handle), 1.5 m (5') cable, 3 "AA" alkaline batteries, hard carrying case, and operator's manual.

For units with a protective boot and splash proof seals add suffix "-PB" to model number and £37 to price.

For units with USB communications add suffix "-USB" to model number and £131 to price.

For units with a 0 to 5 Vdc voltage output add suffix "-V" to model number and £151 to price.

Ordering Examples: HHF141B-USB, anemometer with 70 mm (2¾") vane and USB communications £535 + 131 = £666.

HHF141A-V, anemometer with 25 mm (1") vane and a voltage output £535 + 151 = £686.



UNITED STATES

www.omega.com

1-800-TC-OMEGA

Stamford, CT.

CANADA

www.omega.ca

Laval(Quebec)

1-800-TC-OMEGA

GERMANY

www.omega.de

Deckenpfronn, Germany

0800-8266342

UNITED KINGDOM

www.omega.co.uk

Manchester, England

0800-488-488

FRANCE

www.omega.fr

088-466-342

CZECH REPUBLIC

www.omegaeng.cz

Karviná, Czech Republic

596-311-899

BENELUX

www.omega.nl

0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters