

ULTRASONIC LEVEL SENSORS

LVU-150-R
Starts at
\$275

Single Switch
Mounting Assemblies
Available at:
omega.com/lvu150




- ✓ Not Sensitive to Changes In Viscosity, Density, or Conductivity
- ✓ SPST Relay Standard
- ✓ Resists Vapor and Turbulence
- ✓ NEMA 6 (IP68) Submersible Sensor and Cable

OMEGA's ultrasonic sensors deliver accurate and reliable liquid level detection with an SPST mechanical relay output. The technology provides a high level of ultrasonic sensitivity, including resistance to vapor and turbulence. The ultrasonic sensor utilizes a fork-shaped sensor which contains two piezoelectric crystals, one of which acts as the ultrasonic transmitter, and the other as a receiver. If the air gap between the points of the fork fills with liquid, the sonic wave passes from one crystal to the other.

SPECIFICATIONS

Accuracy: ±1 mm (0.04") in water
Repeatability: ±0.5 mm (0.02") in water
Dead Band Hysteresis: 1 mm in water
Voltage Input: 12 to 36 Vdc
Current Output: 25 mA max.
Relay:
 GP: 120 Vac/Vdc @ 1 A
 CE: 60 Vac/Vdc @ 1 A
Switch Mode:
 Selectable, NO or NC states
Wetted Materials: Polypropylene (PP) or Perfluoroalkoxy (PFA)
Temp. Rating: -40 to 90°C (-40 to 194°F)
Max Pressure Rating: PP:150 psi @ 25°C (76°F) derated @ 1.667 psi per °C above 25°C (76°F)
Loop Resistance: 600 ohm @ 24 Vdc
Standard Cable Length: 3 m (10')
Max Cable Length: 305 m (1000')
Dimensions:
 76.2 or 114.3 L x 26.7 mm Dia. (3.0 or 4.5 x 1.05") (¾" NPT)
Enclosure Rating: NEMA 6 (IP68) submersible sensor and cable



MOST POPULAR MODELS HIGHLIGHTED!

To Order (Specify Model Number)				
Model No.	Price	Description	Material	Size (in)
LVU-150-R	\$275	Ultrasonic sensor	PP	3 x ¾ NPT
LVU-151-R	385	Ultrasonic sensor	PFA	3 x ¾ NPT
LVU-152-R	285	Ultrasonic sensor	PP	4.5 x ¾ NPT
LVU-153-R	385	Ultrasonic sensor	PFA	4.5 x ¾ NPT
GE-2427	105	Reference Book: Ultrasound and Elastic Waves		

Comes complete with operator's manual and 3 m (10') cable.

Two extended cable lengths available. For 7.62 m (25') add suffix "-25" to model number, and add \$20 for PP models, or add \$75 for PFA models. For 15.24 m (50') add suffix "-50" to model number, and \$40 for PP models, or add \$150 for PFA models.

Ordering Examples: LVU-150-R, polypropylene ultrasonic sensor, 3 x ¾ NPT, \$275. LVU-153-R, PFA ultrasonic sensor, 4.5 x ¾ NPT, \$385.

omega.co.uk[®]

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

www.omega.co.uk



UNITED STATES

www.omega.com

1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca

Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de

Deckenfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk

Manchester, England
0800-488-488
+44-(0)161-777-6611

FRANCE

www.omega.fr

0800-466-342

BENELUX

www.omega.nl

0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485, Ethernet and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters